


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
1K	2		L2	REVISED PER ECO-11-005150	03MAY11	RK	HMR

FINISHED CABLE DATA		
CONDUCTORS	WIRE AWG	24 AWG Solid
	Ø RANGE in mm)	0,485<=Ø<0,546
	MATERIAL	COPPER
	PLATING	BARE
	ELONGATION	15% PER EN 50288-1
INSULATION	MATERIAL	POLYETHYLENE
	OVERALL DIAMETER	1,00
DRAIN WIRE	Ø RANGE	0,4 - 0,55
	MATERIAL	COPPER
	PLATING	TINNED
	ELONGATION	15% PER EN 50288-1
BINDER	POLYESTER TAPE	OPTIONAL
INDIVIDUAL PAIR SCREEN	MATERIAL	-
OVERALL SHIELD	FOIL MATERIAL	PLASTIC LAMINATED ALUMINUM FOIL
OVERALL SHIELD	BRAID MATERIAL	-
	PLATING	-
	COVERAGE	-
	ELONGATION	-
JACKET	MATERIAL	PVC
	OVERALL DIAMETER (D)	6,1 ±0.3 mm
PULLING FORCE	MAX.	100 N

1. REFER TO PRODUCT SPEC 108-93018 FOR ADDITIONAL REQUIREMENTS.
2. BASENR SPECIFIC PRINT LEGEND INFO:
AWG24 PR04 CAT5E PVC F/UTP SOLID
3. CABLE COLORED TYPES UPON REQUEST.



WHITE	500 m	REEL	219413-8
WHITE	305 m	REEL BOX	219413-7
WHITE	1000 m	REEL	219413-3
WHITE	305 m	PULL BOX	219413-2
WHITE	305 m	REEL	219413-1
COLOUR	LENGTH (METRES)	PACKAGE	PART NUMBER

DIMENSIONS: mm		DWN L. de Dios 28AUG03	TE Connectivity		
		CHK A. Puell 28AUG03			
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD J. Sanabra 28AUG03	NAME CABLE, CAT5E, PR4, F/UTP, PVC, 24AWG, SOLID		
		PRODUCT SPEC			
MATERIAL	FINISH	APPLICATION SPEC	SIZE A3		
		WEIGHT			
CUSTOMER DRAWING		SCALE NTS	SHEET 1	OF 1	
		REV L2			