






1. DIMENSIONS ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.
2. MATERIAL: HOUSING — POLYCARBONATE, CLEAR
TERMINAL — PHOSPHOR BRONZE, PLATED
WITH $1.27\mu\text{m}$ [.000050] MINIMUM THICK
GOLD IN LOCALIZED GOLD PLATE AREA,
GOLD FLASH OVER THE REMAINDER, OVER
 $2.54\mu\text{m}$ [.000100] MINIMUM THICK NICKEL
UNDERPLATE.
SHIELD — COPPER ALLOY WITH $1.27\mu\text{m}$ [.000050]
MINIMUM SEMI-BRIGHT (SATIN) NICKEL.
3. PLUG WILL ACCEPT 24 TO 28 AWG STRANDED
WIRE, 0.74–0.99 [.029–.039] DIAMETER,
WITH A 5.08 [.200] DIAMETER MAXIMUM
JACKET.
4. TERMINATED DIMENSION 6.15 [.242]
MAXIMUM.
5. 500 ASSEMBLIES PER PACKAGE.
6. 100 ASSEMBLIES PER PACKAGE.
7. 25 ASSEMBLIES PER PACKAGE.
8. SEE RESTRICTED CUSTOMER DRAWING
5–569532–5.
9. PACKAGED 10,000 ASSEMBLIES PER
POLYBAG.

		5-569532-5
		5-569532-4
		5-569532-3
		5-569532-2
		5-569532-1
PACKAGED		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. HALL 300CT2006		 TE Connectivity	
		CHK C. DOOLEY 300CT2006			
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME MODULAR PLUG ASSEMBLY, 8 POSITION, SHIELDED, ROUND CABLE, STRANDED WIRE	
		APVD C. DOOLEY 300CT2006			
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC 108-1163			
MATERIAL		APPLICATION SPEC 114-6016			
FINISH		WEIGHT -		SIZE A2	CAGE CODE 00779
				DRAWING NO C-569532	RESTRICTED TO -
CUSTOMER DRAWING				SCALE 4:1	SHEET 1 of 1
				REV F1	