


<b>TECHNICAL DATASHEET</b>	Code	<b>72001PU</b>
	Version	<b>1</b>
	Date	<b>2009-05-18</b>
<b>2 PR CAT5E SF/UTP 24AWG PUR</b>	Page	<b>1/3</b>

## STANDARDS

- ISO/IEC 11801 2nd edition (September 2002) and ISO/IEC 24702
- EN 50173 – 1 (November 2002)
- TIA/EIA-568-B.2 (May 2001)

## CABLE CONSTRUCTION



### Conductor

Material	Solid bare copper ETP
Diameter	AWG 24

### Insulation

Material	Polypropylene
Diameter over insulated conductor	1.1 ± 0.05 mm

### Pair

Pair	2 twisted insulated conductors, non bonded
Number of pairs	4, all twisted together
Colour code pair 1	White / Blue & Blue
Colour code pair 2	White / Orange & Orange

### Insulating foil

Material	Polyester
----------	-----------

### Shielding foil

Material	Laminated Aluminium / Polyester 40/12
Position aluminium	Outside

### Braid

Material	Solid tinned copper
Coverage	Minimum 80 %

<b>TECHNICAL DATASHEET</b>	Code	<b>72001PU</b>
	Version	<b>1</b>
	Date	<b>2009-05-18</b>
<b>2 PR CAT5E SF/UTP 24AWG PUR</b>	Page	<b>2/3</b>

**Sheath:**

Material	PUR halogen free and flame retardant
Diameter	6.0 +/- 0.3 mm
Wall thickness	0.8 mm
Colour	Black

**ELECTRICAL CHARACTERISTICS**

**Low frequency and D.C.**

D.C. resistance conductor	< 93.8	Ω/km
D.C. loop resistance	< 19.0	Ω/100m
Resistance unbalance	< 2	%
D.C. insulation resistance	> 5000	MΩ.km
Dielectric strength cond. – cond. (2 sec.)	2.5	kV D.C.
Mutual capacitance	< 56	nF/km
Capacitance unbalance	< 1600	pF/km

**High frequency**

Velocity of propagation @ 4 – 100 MHz	≥ 0.6 c
Skew @ 1 – 100 MHz	≤ 40 ns/100m
Propagation delay @ 1 – 100 MHz	≤ 534 + 36/Vf ns/100m
Mean characteristic impedance (Zcm) @ 100 MHz	100 ± 5 Ω
Input impedance 1-100MHz	100 ± 15 Ω

Frequency	Insertion loss dB/100m (max)	NEXT (dB)	ELFEXT (dB)	Return Loss (dB)
0.772	-	67		19.4
1	3.2	65.3	63.8	20
4	6.0	56.3	51.8	23
10	9.5	50.3	43.8	25
16	12.1	47.2	39.7	25
20	13.6	45.8	37.8	25
25	15.3	44.3	35.8	24.3
31.25	17.1	42.9	33.9	23.6
62.5	24.8	38.3	27.9	21.5
100	32	35.3	23.8	20.1

**MECHANICAL CHARACTERISTICS**

Elongation at break conductor	≥ 10 %
Elongation at break insulation	≥ 100 %
Elongation at break sheath	≥ 100 %
Tensile strength sheath	≥15 Mpa

<b>TECHNICAL DATASHEET</b>	Code	<b>72001PU</b>
	Version	<b>1</b>
	Date	<b>2009-05-18</b>
<b>2 PR CAT5E SF/UTP 24AWG PUR</b>	Page	<b>3/3</b>

#### **ENVIRONMENTAL AND OVERALL CHARACTERISTICS**

Maximum operating voltage	450 V D.C. and 300 V A.C.
Maximum continuous current per conductor (@25 °C)	1.4 A rms
Maximum pulling tension	40 N
Minimum setting/bending radius	30 / 60 mm
Temperature range during installation	0 / +50 °C
Temperature range during operation	-20 / +80 °C
Halogenfree	IEC 60754-1
Oil resistance	IEC 60811-2-1
Flame propagation	FT2
UL	AWM 20549



Belden CDT believes this product to be in compliance with the environmental regulations EU RoHS (Directive 2002/95/EC, 27 January 2003); this is valid for all material produced after the RoHS compliant date for this product.