



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: SU2200XLA

SmartOnline 2.2kVA On-Line Double-Conversion UPS, Tower, 110/120V NEMA outlets



Highlights

- 2200VA / 2.2kVA / 1600 watt on-line double-conversion tower UPS
- 110/120V +/-2% output at 50/60Hz, high efficiency economy mode option
- Expandable runtime, Hot-swappable battery modules
- USB, RS232 & EPO ports; support for SNMP/WEB card options
- Front panel status LEDs with detailed load and battery metering
- 2 independently switchable output load banks
- NEMA 5-20P input; L5-20R & 5-15/20R outlets

Description

Tripp Lite's Smart Online SU2200XLa on-line, double conversion UPS protects critical server, networking or telecommunications equipment from blackouts, brownouts, voltage fluctuations and surges in an attractive all-black upright tower form factor. Large capacity 2200VA/1600W UPS continuously converts incoming AC to DC, then back to perfect sine wave AC output at 120V AC (+/-2%). Removes harmonic distortion, fast electrical impulses, frequency fluctuations and other hard-to-solve power problems not addressed by other UPS systems. True sine wave output and zero transfer time offers guaranteed compatibility with all equipment types. Includes 7 UPS supported outlets. 2 three-outlet load banks can be independently controlled via software interface to selectively reboot remote equipment or automatically shed less critical loads to extend battery runtime for the most critical equipment. Battery support can be extended with the addition of external battery packs. Includes slot for internal SNMP/web card, plus DB9 enhanced serial monitoring port for unattended shutdown, remote control and monitoring of UPS system and power data. Network management interfaces support simultaneous communications via USB port, DB9 serial port and SNMPWEBCARD slot. HID-compliant USB interface enables integration with built-in power management and auto shutdown features of Windows and Mac OS X. Includes Tripp Lite's PowerAlert UPS Power Management Software. Compatible with Tripp Lite's Watchdog Service Monitoring and Control Software.

Package Includes

- SU2200XLa On-line Double-Conversion UPS System
- PowerAlert Software and cabling
- Instruction manual with warranty information
- EPO (Emergency Power Off) cabling

Features

- True on-line, double conversion UPS provides a constant, pure sine wave AC output
- Maintains continuous operation through blackouts, brownouts, voltage fluctuations and surges with zero transfer time
- Zero transfer time, on-line, double-conversion and economy-mode operation supported
- Removes harmonic distortion, electrical impulses, frequency variations and other hard-to-solve power problems
- Accepts input voltages between 80V and 150V (65V to 150V at loads under 70%), regulating output to 120V AC +/-2%
- 2200VA/1600W output capacity with 7 total outlets (6 NEMA5-15/20R and 1 L5-20R)
- Two built-in individually switchable load banks, each with three outlets, can be controlled via software interface to selectively reboot remote equipment or automatically shed less critical loads to extend battery runtime for the most critical equipment
- Standard internal battery set provides 14 min. runtime at half load and 4.5 min. at full load

- Runtime is expandable with BP48V24-2U (limit 1) or BP48V60RT3U (multi-pack compatible) external battery packs
- Some external battery configurations require the use of Tripp Lite's [External Battery Configuration Software](#) (see manual)
- Attractive all-black upright tower format
- Simultaneous communications via HID-compliant USB port, serial port, and SNMP/web card slot
- HID-compliant USB interface enables integration with built-in power management and auto shutdown features of Windows and Mac OS X
- DB9 serial network interface supports RS-232 and contact closure messaging
- Slot for optional SNMP/web card (part #: SNMPWEBCARD)
- Included PowerAlert UPS Power Management Software and cabling provides monitoring of in-depth site power conditions, full UPS status and fault warnings, output load level and load bank power control
- Compatible with Tripp Lite's WatchDog Service Monitoring and Control Software (part# WATCHDOGSW)
- Fault tolerant electronic bypass maintains utility output during a variety of UPS fault conditions
- Diagnostic LEDs
- \$250,000 [Ultimate Lifetime Insurance](#) coverage for connected equipment(USA & Canada only)
- 2-year product warranty

Specifications

OUTPUT	
Output Volt Amp Capacity (VA)	2200
Output kVA capacity (kVA)	2.2
Output Watt Capacity (watts)	1600
Output kW capacity	1.6
Output power factor	0.7
Crest Factor	3:1
Nominal Output Voltage(s) Supported	110V; 120V
Nominal Voltage details	120V default
Frequency compatibility	50 / 60 Hz
Frequency compatibility details	Output frequency matches input nominal on startup, defaults to 60 Hz on cold-start
Output voltage regulation (line mode)	+/- 2%
Output voltage regulation (Economy line mode)	+/- 10%
Output voltage regulation (Battery mode)	+/- 2%
Built-in UPS output receptacles	6 5-15/20R outlet(s); 1 L5-20R outlet(s)
Built-in controllable switched load banks	Two switchable three-outlet 5-15/20R load banks
Output AC waveform (AC mode)	Sine wave
Output AC waveform (battery mode)	Pure Sine wave

INPUT	
Rated input current (at maximum load)	16A (120V), 17.6A (110V)
Nominal Input Voltage(s) Supported	110V AC; 120V AC
UPS input connection type	5-20P
Input circuit breaker	30A
UPS Input cord length (ft.)	10
UPS Input cord length (m)	3
Recommended Electrical Service	20A 120V
BATTERY	
Full load runtime (minutes)	4.5 min. (1600w)
Half load runtime (minutes)	14 min. (800w)
Expandable battery runtime	Extended runtime supported via optional external battery packs
External battery pack compatibility	BP48V24-2U (limit 1); BP48V60RT-3U (multi-pack compatible)
DC system voltage (VDC)	48
Battery recharge rate (included batteries)	Less than 5 hours from 10% to 90%
Replacement battery cartridge (internal UPS battery replacement)	RBC48-SUTWR
Battery Access	Battery access door
Battery replacement description	Hot-swappable, user replaceable batteries
VOLTAGE REGULATION	
Voltage regulation description	Online, double-conversion power conditioning
Overvoltage correction	2% output voltage regulation during overvoltages to 150
Undervoltage correction	2% output voltage regulation during undervoltages to 80
Severe undervoltage correction	2% output voltage regulation during undervoltages to 65 (under 70% load only)
LEDS ALARMS & SWITCHES	
LED Indicators	14 LEDs indicate line power, online mode, economy/bypass mode, on-battery, overload, battery low, replace battery and fault status information - includes 4-LED meter display for load and battery charge level
Alarms	Audible alarm indicates UPS startup, power-failure, low-battery, overload, UPS fault and remote shutdown conditions

Alarm cancel operation	Power-fail alarm can be silenced using alarm-cancel switch
Switches	2 switches control off/on power status and alarm-cancel/self-test operation
SURGE / NOISE SUPPRESSION	
UPS AC suppression joule rating	570
UPS AC suppression response time	Instantaneous
UPS Dataline suppression	1 line TEL/DSL (1 in / 1 out); 10/100Base T Ethernet
EMI / RFI AC noise suppression	Yes
PHYSICAL	
Installation form factors supported with included accessories	Tower
Primary form factor	Tower
UPS / Power Module dimensions in primary form factor (height x width x depth / inches)	10.2 x 9 x 19.5
UPS / Power Module dimensions in primary form factor (height x width x depth / cm)	26 x 22.9 x 49.5
UPS / Power Module weight (lbs)	52.7
UPS / Power Module weight (kg)	23.9
UPS Shipping dimensions (height x width x depth / inches)	15.2 x 13 x 24
UPS Shipping dimensions (height x width x depth / cm)	38.7 x 33 x 61
Shipping weight (lbs)	59.5
Shipping weight (kg)	27
UPS housing material	Steel
Cooling method	Fan
ENVIRONMENTAL	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC mode BTU / hr. (full load)	812.9

AC economy mode BTU / hr. (full load)	347.2
Battery mode BTU / hr. (full load)	885.6
AC economy mode efficiency rating (100% load)	94%
Audible Noise	< 45 dB at front side 1m
COMMUNICATIONS	
Communications interface	USB (HID enabled); DB9 Serial; Contact closure; EPO (emergency power off); Slot for SNMP/Web interface
Network monitoring port description	Supports detailed monitoring of UPS and site power conditions; DB9 port supports RS232 and contact closure communications
PowerAlert software	Included
Communications cable	USB and DB9 cabling included
WatchDog compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
LINE / BATTERY TRANSFER	
Transfer time	No transfer time (0 ms.) in online, double-conversion mode
Low voltage transfer to battery power (setpoint)	80V (100% load), 65V (
High voltage transfer to battery power (setpoint)	150
SPECIAL FEATURES	
Cold Start (startup in battery mode during a power failure)	Cold-start operation supported
High availability UPS features	Automatic inverter bypass; Hot swappable batteries
Green & high efficiency features	High efficiency economy mode operation; Individually controllable load banks; Schedulable daily hours of economy mode operation
CERTIFICATIONS	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category A (EMI)
WARRANTY	
Product Warranty Period (U.S., Canada & Puerto Rico)	2-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 Ultimate Lifetime Insurance

Related Items

Optional Products

Product Type	Related Model	Description	Qty.
Extended Warranties	WEXT3-2200-3000	3-Year Extended Warranty - For Smart Line-Interactive and Online Tower or Rack models, 2200-3000VA	1

Extended Warranties	WEXT5-2200-3000	5-Year Extended Warranty - For Smart Line-Interactive and Online Tower or Rack models, 2200-3000VA or less	1
External Battery Packs	BP48V24-2U	BP48V242U - External Battery Pack for UPS System	1
External Battery Packs	BP48V60RT-3U	External Battery Pack and Cable. 3U, Expandable, Blue 2-Point Connector	1
Power Cables	P007-006	6-ft. Heavy-Duty 14AWG Power cord (IEC-320-C13 to NEMA 5-15P)	1
Power Cables	P007-010	10-ft. Heavy-Duty 14AWG Power cord (IEC-320-C13 to NEMA 5-15P)	1
Power Cables	P044-06I	6-inch 12AWG Heavy Duty Power Adapter cord (NEMA-L5-20R to NEMA-5-20P)	1
Power Cables	P045-010	10-ft. 12AWG Heavy-Duty Power cord (IEC-320-C19 to NEMA L5-20P)	1
Power Cables	P049-010	10-ft. 12AWG Heavy Duty Power cord (IEC-320-C19 to NEMA 5-20P)	1
Power Cables	PDUNV	Basic PDU / Power Distribution Unit - Safe, reliable power distribution for critical networking equipment	1
Power Distribution	PDU1220T	Basic PDU / Power Distribution Unit - Safe, reliable power distribution for critical networking equipment	1
Power Distribution	PDUB20	Dual source Power Distribution Unit / PDU with Manual Transfer Switch enables Hot-swappable UPS Replacement in Critical Network Applications	1
Power Distribution	PDUMH20	Metered PDU / Power Distribution Unit- Safe, reliable power distribution with digital current meter	1
Power Distribution	PDUMH20AT	Metered PDU with ATS - Power Distribution Unit with dual-input Auto Transfer Switching	1
Power Distribution	PDUMH20ATNET	Switched, Metered PDU with ATS - Power Distribution Unit with dual-input Auto Transfer Switching, individual outlet control and SNMP network interface	1
Power Distribution	PDUMNH20	Monitored PDU / Power Distribution Unit supports real-time remote monitoring of load level, voltage and frequency with options for remote environmental and security monitoring	1
Power Distribution	PDUMNV20	Monitored PDU / Power Distribution Unit supports real-time remote monitoring of load level, voltage and frequency with options for remote environmental and security monitoring	1
Power Distribution	PDUMV20	Metered PDU / Power Distribution Unit - Safe, reliable power distribution with digital current meter	1
Power Distribution	PDUMV20NET	Switched, Metered PDU with Remote Monitoring - 0U Vertical Rackmount Power Distribution Unit for Networks with Individually Switchable Outlets, Current Metering, Remote Monitoring and Control	1
Power Distribution	PDUV20	Safe, reliable power distribution for critical networking equipment	1
Shutdown Cable Kits	AS400CABLE KIT	Power Management Tools - UPS Communication Cable Kit for System i / AS400 / iSeries Servers	1
SNMP Accessories	ENVIROSENSE	Monitors temperature, humidity and contact-closure inputs. (Requires SNMPWEBCARD or switched PDU.)	1
SNMP Accessories	SNMPWEBCARD	For remote monitoring and control via SNMP, Web, or Telnet.	1
UPS Accessories	MODBUSCARD	For remote monitoring and control via MODBUS protocol	1
UPS Accessories	RELAYIOCARD	Programmable Relay I/O Card	1

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=3594.

Copyright © 2011 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.