



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: SU3000RTXR3U

SmartOnline 3kVA On-Line Double-Conversion UPS, 3U Rack/Tower, 110/120V NEMA outlets, XR runtime

Highlights



- 3000VA / 3kVA / 2400 watt on-line double-conversion 3U rack/tower UPS
- 110/120V +/-2% output at 50/60Hz, high efficiency economy mode option
- Oversize internal batteries, Expandable runtime, Hot-swap battery modules
- USB, RS232 & EPO ports; support for SNMP/WEB card options
- Front panel status LEDs with detailed load and battery metering
- 2 independently switchable output load banks
- NEMA L5-30P input; L5-30R, 5-15/20R & 5-15R outlets

Description

3000VA / 3kVA online, double-conversion UPS system for critical server, network and telecommunications equipment. "XR" configuration offers twice the battery capacity as comparable "XL" version. 3U rackmount form factor with an installed depth of 26 inches (66cm). Expandable battery runtime with optional BP72V15-2U (limit 1) and BP72V28RT3U (multi-pack compatible) external battery packs. Full time sine wave 110 or 120V output with +/-2% voltage regulation. Online, double-conversion Uninterruptible Power Supply (UPS) actively converts raw incoming AC power to DC, then re-converts output back to completely regulated, filtered AC output. Operates continuously without using battery power during brownouts to 65V and overvoltages to 150V. Highly efficient operation in optional economy mode setting, saves BTU heat output and energy costs. NEMA L5-30P input plug. NEMA 5-15R, NEMA 5-15/20R and NEMA L5-30R output receptacles. Network-grade AC surge and noise suppression. Zero transfer time between AC and battery operation. Network management interfaces support simultaneous communications via USB port, DB9 serial port and SNMPWEBCARD slot. Includes USB and DB9 serial ports. Built-in DB9 port offers both enhanced RS-232 enabled monitoring data, plus contact closure monitoring ability. HID-compliant USB interface enables integration with built-in power management and auto shutdown features of Windows and Mac OS X. Supports simultaneous detailed monitoring of equipment load levels, self-test data and mains power conditions via all 3 network interfaces. Includes PowerAlert monitoring software and complete cabling. Emergency Power Off (EPO) interface. Integrated two bank PDU switching supports load shedding and remote-reboot of connected equipment. Multi-stage metered current monitoring and battery charge status LEDs. LED display panel easily rotates for better viewing in rackmount or tower configurations. Dataline surge suppression for dialup, DSL or network ethernet connection. Mains power and voltage regulation LEDs. Audible Alarm. Self-test. Fault-tolerant auto-bypass mode. 4 post rackmount accessories included; 2-9USTAND tower kit and 2POSTRMKITWM 2-post rackmount accessories available. Field replaceable, hot swappable internal batteries and external battery packs. Attractive all-black UPS design. 2-year warranty and \$250,000 [connected equipment insurance](#); extended warranty and service contracts available.

Package Includes

- SU3000RTXR3U SmartOnline High Power Density UPS System
- PowerAlert Software CD and cabling
- Owner's manual with warranty information

Features

- SmartOnline high power density UPS system is ideal for critical voice, data, medical and industrial network applications
- Special "XR" version offers larger internal batteries for longer runtimes than standard "XL" model

- True online, double-conversion UPS provides perfectly regulated sine wave output within 2% of 110/120V (user selectable) under all usage conditions
- Maintains continuous operation through blackouts, voltage fluctuations and surges with zero transfer time
- Removes harmonic distortion, fast electrical impulses, frequency variations and other hard to solve power problems not addressed by other UPS types
- Corrects line voltage conditions as low as 65V and as high as 150V back to selectable 110/120V (+/-2%) values
- Highly efficient operation in optional economy mode setting, saving BTU heat output and energy costs
- Standard internal battery set offers 30 minutes runtime at half load (1200W) and 12 minutes at full load (2400W)
- Optional BP72V15-2U external battery pack increases runtime (limit 1)
- Optional BP72V28RT-3U external battery pack increases runtime (multi-pack compatible)
- Some external battery configurations require the use of Tripp Lite's [External Battery Configuration Software](#) (see manual)
- Compact rackmount form factor installs using only 3 rack spaces (3U) with a maximum installed depth of 26 inches
- Ships with all mounting accessories for 4 post rackmount installation
- Optional 2POSTRMKITWM enables 2 post rackmount installation
- Optional 2-9USTAND accessory enables small-footprint upright tower placement
- Fault tolerant electronic bypass maintains utility output during a variety of UPS fault conditions
- Network interfaces support simultaneous communications via built-in USB, DB9 serial/contact-closure and SNMPWEBCARD slot
- HID compliant USB interface enables integration with built-in power management and auto shutdown features of Windows and Mac OS X
- Included PowerAlert UPS monitoring software supports safe unattended shutdown, monitoring and control via local connected servers, plus any number of additional servers over IP
- UPS interface supports on-battery, low-battery, power-restored, AC-voltage, DC-voltage, output current monitoring, battery charge current, battery capacity, AC line frequency, timed inverter shutoff, activate self-test, load bank output power control and remote reboot, UPS nominal voltage adjustment and UPS line to battery power voltage setpoints
- Built-in Emergency Power Off (EPO) interface with cable
- NEMA L5-30P input plug/NEMA 5-15/20R & NEMA L5-30R output receptacles
- Integrated 2 bank switched PDU enables remote outlet management for load shedding or remote reboot of individual load banks (each bank has four outlets)
- Front panel LEDs offer current monitoring and battery charge level information
- UPS ships fully assembled in full compliance with DOT regulations, no time consuming connection of internal batteries by user required
- Single line TEL/DSL or network ethernet line surge suppression
- 2 year manufacturer's product warranty, \$250,000 [Ultimate Lifetime Insurance](#)

Specifications

OUTPUT	
Output Volt Amp Capacity (VA)	3000
Output kVA capacity (kVA)	3
Output Watt Capacity (watts)	2400
Output kW capacity	2.4
Output power factor	0.8
Crest Factor	3:1
Nominal Output Voltage(s) Supported	110V; 120V
Nominal Voltage details	120V default
Frequency compatibility	50 / 60 Hz
Frequency compatibility details	Output frequency matches input nominal on startup, defaults to 60 Hz on cold-start

Output voltage regulation (line mode)	+/- 2%
Output voltage regulation (Economy line mode)	+/- 10%
Output voltage regulation (Battery mode)	+/- 2%
Built-in UPS output receptacles	4 5-15R outlet(s); 4 5-15/20R outlet(s); 1 L5-30R outlet(s)
Built-in controllable switched load banks	Two switchable four-outlet load banks, (bank 1 - four 5-15/20R, bank 2 - four 5-15R outlets)
Output circuit breaker	15A branch rated (x2) - each breaker protects 4 outlets, L5-30R is unbreakered
Output AC waveform (AC mode)	Sine wave
Output AC waveform (battery mode)	Pure Sine wave
INPUT	
Rated input current (at maximum load)	24A
Nominal Input Voltage(s) Supported	110V AC; 120V AC
UPS input connection type	L5-30P
Input circuit breaker	40A
UPS Input cord length (ft.)	10
UPS Input cord length (m)	3
Recommended Electrical Service	30A 120V
BATTERY	
Full load runtime (minutes)	12 min. (2400w)
Half load runtime (minutes)	30 min. (1200w)
Expandable battery runtime	Supports extended runtime with optional external battery packs
External battery pack compatibility	BP72V15-2U (limit 1); BP72V28RT-3U (multi-pack compatible)
DC system voltage (VDC)	72
Battery recharge rate (included batteries)	Less than 6 hours from 10% to 80%
Replacement battery cartridge (internal UPS battery replacement)	RBC96-3U (quantity 2)

Battery Access	Front panel battery access door
Battery replacement description	Hot-swappable, user replaceable batteries
VOLTAGE REGULATION	
Voltage regulation description	Online, double-conversion power conditioning
Overvoltage correction	2% output voltage regulation during overvoltages to 150
Undervoltage correction	2% output voltage regulation during undervoltages to 80
Severe undervoltage correction	2% output voltage regulation during undervoltages to 65 (under 70% load only)
LEDS ALARMS & SWITCHES	
LED Indicators	14 LEDs indicate line power, online mode, economy/bypass mode, on-battery, overload, battery low, replace battery and fault status information; 4-LED meter displays load and battery charge levels; LED panel rotates for viewing in rack/tower formats
Alarms	Audible alarm indicates UPS startup, power-failure, low-battery, overload, UPS fault and remote shutdown conditions
Alarm cancel operation	Power-fail alarm can be silenced using alarm-cancel switch
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation
SURGE / NOISE SUPPRESSION	
UPS AC suppression joule rating	480
UPS AC suppression response time	Instantaneous
UPS Dataline suppression	1 line TEL/DSL (1 in / 1 out); 10/100Base T Ethernet
EMI / RFI AC noise suppression	Yes
PHYSICAL	
Installation form factors supported with included accessories	4 post 19 inch rackmount (mounting rail kit included)
Installation form factors supported with optional accessories	2 post rackmount (2POSTRMKITWM); Tower (2-9USTAND)
Optional mounting accessory notes	Wallmount installation not recommended
Primary form factor	Rackmount
UPS / Power Module dimensions in primary form factor (height x width x depth / inches)	5.2 x 17.8 x 26

UPS / Power Module dimensions in primary form factor (height x width x depth / cm)	13.3 x 45.1 x 66
Installed whole system total rack space height (rack spaces)	3U
Secondary form factor	Tower (requires 2-9U STAND)
UPS / Power Module weight (lbs)	111.3
UPS / Power Module weight (kg)	50.5
UPS Shipping dimensions (height x width x depth / inches)	11.2 x 23 x 31.5
UPS Shipping dimensions (height x width x depth / cm)	28.6 x 58.4 x 80
Shipping weight (lbs)	149.9
Shipping weight (kg)	68.1
UPS housing material	Steel
Cooling method	Fan
ENVIRONMENTAL	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius.
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius.
Relative Humidity	0 to 95%, non-condensing
AC mode BTU / hr. (full load)	1112.7
AC economy mode BTU / hr. (full load)	520.9
Battery mode BTU / hr. (full load)	1219.3
AC economy mode efficiency rating (100% load)	94%
COMMUNICATIONS	
Communications interface	USB (HID enabled); DB9 Serial; Contact closure; EPO (emergency power off); Slot for SNMP/Web interface
Network monitoring port description	Supports detailed monitoring of UPS and site power conditions; DB9 port supports RS232 and contact closure communications
PowerAlert software	Included
Communications cable	USB and DB9 cabling included

WatchDog compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
LINE / BATTERY TRANSFER	
Transfer time	No transfer time (0 ms.) in online, double-conversion mode
Low voltage transfer to battery power (setpoint)	80V (100% load), 65V (
High voltage transfer to battery power (setpoint)	150
SPECIAL FEATURES	
Cold Start (startup in battery mode during a power failure)	Cold-start operation supported
High availability UPS features	Automatic inverter bypass; Hot swappable batteries
Green & high efficiency features	High efficiency economy mode operation; Individually controllable load banks; Schedulable daily hours of economy mode operation
CERTIFICATIONS	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category A (EMI)
WARRANTY	
Product Warranty Period (U.S., Canada & Puerto Rico)	2-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 Ultimate Lifetime Insurance

Related Items

Optional Products

Product Type	Related Model	Description	Qty.
Extended Warranties	WEXT3-2200-3000	3-Year Extended Warranty - For Smart Line-Interactive and Online Tower or Rack models, 2200-3000VA	1
Extended Warranties	WEXT5-2200-3000	5-Year Extended Warranty - For Smart Line-Interactive and Online Tower or Rack models, 2200-3000VA or less	1
External Battery Packs	BP72V15-2U	BP72V15-2U - External Battery Pack for UPS System	1
External Battery Packs	BP72V28RT-3U	BP72V28RT-3U - External Battery Pack for UPS System	1
Power Distribution	PDU1215	Basic PDU / Power Distribution Unit - Safe, reliable power distribution for critical networking equipment	1
Power Distribution	PS7224	Tripp Lite Power Strip - Multiple outlets wherever you need them	1
Rackmount/Wallmount Kits	2POSTRMKITHD	Enables 2-Post Rackmount Installation of 3U and Larger UPS, Transformer and Battery Pack Components	1
Shutdown Cable Kits	AS400CABLE KIT	Power Management Tools - UPS Communication Cable Kit for System i / AS400 / iSeries Servers	1
SNMP Accessories	ENVIROSENSE	Monitors temperature, humidity and contact-closure inputs. (Requires SNMPWEBCARD or switched PDU.)	1
SNMP Accessories	SNMPWEBCARD	For remote monitoring and control via SNMP, Web, or Telnet.	1

Surge Protectors	DCATV	Network Surge Suppressor - Essential protection for TV/VCR coaxial lines	1
Surge Protectors	DNET1	Network Surge Suppressor - Essential protection for data and communication lines	1
Surge Protectors	DTEL2	Network Surge Suppressor - Essential protection for data and communication lines	1
Tower Stands	2-9USTAND	Enables Tower Placement of Rackmount UPS Systems	1
UPS Accessories	MODBUSCARD	For remote monitoring and control via MODBUS protocol	1

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=3080.

Copyright © 2011 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.