

Consolidation Point Boxes

specifications

Consolidation point boxes shall be used with low profile under floor systems and vertical and horizontal wall mount applications. The boxes shall accept up to 24 modules or 48 modules and be made of 16-gauge steel for long term durability. The box shall have top and bottom cable access with removable panels that include grommets to keep out debris.



technical information

Dimensions:	CUFMB24BL: 1.69"H x 10.85"W x 10.67"L (42.9mm x 275.6mm x 271.0mm) CUFB48BL: 1.63"H x 10.00"W x 14.88"D (41.5 x 254.0 x 377.9mm)
Mounting option:	Vertical or horizontal wall mounting or low profile raised floor system (minimum depth of 1.65")
Packaging:	CUFMB24BL: Box includes 24-port label and six Tak-Ty [®] Cable Ties CUFB48BL: Box includes 48-port label and six Tak-Ty [®] Cable Ties CUFF-KIT: Fiber Conversion Kit includes four Pan-Ty [®] Cable Ties, two adhesive fiber spools, two support brackets with screws to hold fiber cable, one grounding lug, one laser warning label, one fiber warning label and 24" spiral wrap

key features and benefits

Modularity	Accepts all Mini-Com [®] Modules; individual modules snap in and out
High density	24 port capacity on each side of box; total of 48 ports
Optional fiber conversion kits	Supports use in fiber applications
Removable panels	Allow Panduit T70 Raceway to be flush against panel for clean, wall mounted appearance
Durable	Made with 16 gauge rugged steel for long term durability
Center metal supports	Supports raised floor panels

applications

The consolidation point box is designed to work with SMED NEXUS[™] Under Floor Systems as a consolidation point, although it is also suitable for other under floor systems with a minimum depth of 1.65". The box can also be wall mounted vertically or horizontally as a consolidation point. Consolidation point boxes

save time and money by reducing the amount of time required to complete moves, adds and changes.

Troubleshooting is also simplified as the connections can be tested and certified before installation.

NEXUS[™] is a registered trademark of SMED International Corporation, Calgary, Alberta, Canada.

Consolidation Point Box

24-port consolidation point box: CUFMB24BL

48-port consolidation point box: CUFB48BL


Fiber conversion kit: CUFF-KIT

Mini-Com[®] Modules



See website (www.panduit.com) or catalog for complete listing of modules for copper, fiber, and audio video installations.

Consolidation Point Boxes





CUFMB24BL



CUFB48BL



B



Dimensions are in inches. [Dimensions in brackets are metric].

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT CANADA
Markham, Ontario
cs-cdn@panduit.com
Phone: 800.777.3300

PANDUIT EUROPE LTD.
London, UK
cs-emea@panduit.com
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.
Republic of Singapore
cs-ap@panduit.com
Phone: 65.6305.7575

PANDUIT JAPAN
Tokyo, Japan
cs-japan@panduit.com
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA
Guadalajara, Mexico
cs-la@panduit.com
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.
Victoria, Australia
cs-aus@panduit.com
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

For more information

Visit us at www.panduit.com

Contact Customer Service by email: cs@panduit.com
or by phone: 800.777.3300 and reference RKSP55

PANDUIT[®]

© 2010 Panduit Corp.
ALL RIGHTS RESERVED.

WW-RKSP55

10/2010