

Power Strips

PANDUIT®

SPECIFICATION SHEET

specifications

Power outlet units shall be single-phase with standard IEC C-13, IEC C-19 or NEMA compliant receptacles using twist lock plug and shall be vertically or horizontally mounted. Power outlet units shall be 10, 16, 24 and 30 outlet options with 10 or 15 foot cords and shall have black powder-coated finish. The vertical or horizontal power outlet units shall have 15, 20 or 30 Amp circuits and be capable of mounting directly to the rack or cabinet using hardware or mounting discs.



technical information

Power strips:	CMRPSH15:	1.7"H x 19.00"W x 3.8"D (44mm x 483mm x 95mm), 1 RU
	CMRPSH20:	1.7"H x 19.00"W x 3.8"D (44mm x 483mm x 95mm), 1 RU
	CMRPSH20CM:	1.7"H x 19.00"W x 4.5"D (44mm x 483mm x 114mm), 1 RU
	RPSH163C13TL6:	3.5"H x 19.0"W x 1.6"D (88mm x 483mm x 41mm), 2 RU
	RPSH163C13TL6M:	3.5"H x 19.0"W x 1.6"D (88mm x 483mm x 41mm), 2 RU
	RPSH103C13TL6M:	1.7"H x 19.0"W x 1.6"D (43mm x 483mm x 41mm), 1 RU
	CMRPSV20:	38.5"H x 1.9"W x 1.3"D (978.9mm x 47mm x 33.1mm)
	CMRPSV20TL:	38.5"H x 1.9"W x 1.3"D (978.9mm x 47mm x 33.1mm)
	CMRPSVD20:	66.3"H x 1.9"W x 1.3"D (1683mm x 47mm x 33mm)
	CMRPSVD20TL:	66.3"H x 1.9"W x 1.3"D (1683mm x 47mm x 33mm)
	RPSV243520TL5:	66.3"H x 2.0"W x 2.0"D (1683mm x 51mm x 51mm)
	RPSV243620TL6:	66.3"H x 2.0"W x 2.0"D (1683mm x 51mm x 51mm)
	RPSV303C139TL6:	66.3"H x 2.0"W x 2.0"D (1683mm x 51mm x 51mm)
	RPSV303C139TL6M:	66.3"H x 2.0"W x 2.0"D (1683mm x 51mm x 51mm)

Power strips mounting: Horizontal power strips provide up to 16 outlets and mount to any EIA 19" rack or cabinet. Vertical power strips provide up to 24 outlets and do not occupy any rack spaces

Power strips packaging: All power strips include 10' power cords, plugs, mounting brackets and screws

key features and benefits

Scrolling power meter	Displays power factor, amps, volts and watts, providing critical information on current draw and improving power manageability for network reliability
Circuit breakers	Interrupts circuit over-current conditions minimizing potential power disruption for increased reliability
Twist lock plug	Maintains a secure connection and prevents accidental power interruption
Multiple mounting options	Enables positioning of power strips closer to active equipment eliminating the need for extension cords for greater system flexibility
Mounting discs	Allows tool-less mounting of power strips for faster installations
Dual circuit vertical solution	Designed for use with equipment requiring redundant power supplies

applications

The Panduit vertical and horizontal power strips offer a convenient way to distribute power to active equipment within racks and cabinets. Built-in power meters and circuit breakers provide critical power information and protection for improved network reliability. Mounting flexibility

allows quick and easy installation. When used with Panduit racks and cabinets, the user receives a complete networking solution that will satisfy data center requirements today and into the future.

www.panduit.com

Power Strips – 19" Horizontal

15 A:	CMRPSH15
20 A:	CMRPSH20
20 A with current meter:	CMRPSH20CM
30 A with 16 outlets:	RPSH163C13TL6 RPSH163C13TL6M
30 A with 10 outlets and current meter:	RPSH103C13TL6M

Power Strips – 20 A Vertical

39" single circuit:	CMRPSV20 CMRPSV20TL
66" dual circuit:	CMRPSVD20 CMRPSVD20TL

Power Strips – 30 A Vertical

66": 125 V	RPSV243520TL5
66": 250 V	RPSV243620TL6
66": 250 V	RPSV303C139TL6
66": 250 V current meter:	RPSV303C139TL6M

4 Post Racks 7'

#12-24 threaded rail:	CMR4P84
Cage nut rail:	CMR4P84CN

4 Post Racks 8'

#12-24 threaded rail:	CMR4P96
Cage nut rail:	CMR4P96CN

NET-ACCESS™ Cabinet

45 RU cabinet with side panels, front and rear doors:	CS1
45 RU cabinet with front and rear doors:	CS2
45 RU cabinet:	CS3

Power Strips



**CMRPSH15,
CMRPSH20,
CMRPSH20CM**




**RPSH163C13TL6
RPSH163C13TL6M**



**CMRPSV20
CMRPSV20TL**



RPSV243520TL5



RPSH103C13TL6M



**RPSV303C139TL6
RPSV303C139TL6M**



RPSV243620TL6



**CMRPSVD20
CMRPSVD20TL**

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT CANADA
Markham, Ontario
cs-cdn@panduit.com
Phone: 800.777.3300

PANDUIT EUROPE LTD.
London, UK
cs-emea@panduit.com
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.
Republic of Singapore
cs-ap@panduit.com
Phone: 65.6305.7575

PANDUIT JAPAN
Tokyo, Japan
cs-japan@panduit.com
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA
Jalisco, Mexico
cs-la@panduit.com
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.
Victoria, Australia
cs-aus@panduit.com
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

For more information

Visit us at www.panduit.com

Contact Customer Service by email: cs@panduit.com
or by phone: 800-777-3300 and reference RKSP25

PANDUIT[®]

©2009 Panduit Corp.
ALL RIGHTS RESERVED.
Printed in the U.S.A.

WW-RKSP25

7/2009