

PanView iQ™ (PViQ™) Panel Manager

specifications

The panel manager (PM) shall attach directly to the back of a PViQ™ Patch Panel (via a mounting bracket) to provide physical infrastructure management functionality to PViQ™ Patch Panels. Up to 50 PMs shall be able to be connected to one another via LAN connector ports. PM installations shall also require the installation of an included interface module to the front of PViQ™ Patch Panels for local configuration and user navigation.



technical information

Dimensions:	1.12"H x 4.80"W x 4.13"D (28.32mm x 121.92mm x 105.01mm)
Weight:	.65 lbs. (.30 kg)
Mounting:	Attaches to a PViQ™ Patch Panel using mounting bracket
Packaging:	Includes mounting bracket, ethernet cord, interface unit, and installation instructions

key features and benefits

Patch panel management	Provides manageability for each PViQ™ Patch Panel, offering full physical infrastructure management for network reliability, security, and lower total cost of ownership
Zero rack space	Eliminates need for additional rack space by attaching directly onto PViQ™ Patch Panels simplifying system design and lowering costs
Smart upgrades	Enables quick addition, removal, or replacement of modules to add management capabilities to the patch panels, simplifying field installations, upgrades, and maintenance while minimizing downtime
Interface unit	Snap into the front of the PViQ™ Patch Panel to enable patch cord tracing and diagnostic navigation using multi-function push buttons and LEDs, improving speed and accuracy of maintenance and troubleshooting
Port provisioning	Enables guided patching of PViQ™ interconnect patch cords to network equipment for local port mapping, reducing errors and minimizing time to complete moves, adds, and changes (MACs)

applications

Panduit's PViQ™ System Hardware, which includes intelligent patch panels, modules, and cabling, seamlessly feeds information directly into the Physical Infrastructure Manager™ (PIM™) Software Platform to provide continuous real-time patch field monitoring and visibility of physical infrastructure connectivity, for enhanced system reliability and security, and capacity management.

PViQ™ Panel Managers and Expansion Modules install directly to PViQ™ Patch Panels to enable the PIM™ Software Platform to read connectivity information. The PViQ™ Panel

Managers enable port provisioning for local mapping of network equipment for more efficient moves, adds, and changes. PViQ™ Expansion Modules connect to and utilize the processing capabilities of the PViQ™ Panel Managers to extend intelligence to additional ports in a cost-effective manner.

Interface units that come packaged with the PViQ™ Panel Managers and Expansion Modules add further built-in functionality such as patch cord tracing and maintenance operations, without the need for additional control equipment.

PanView iQ™ Intelligence Modules

Panel manager (PM):	PVQ-PM
Expansion module (EM):	PVQ-EM
NOTE: PM requires 12 volt power supply (not included).	

PanView iQ™ Patch Panels

Modular, intelligent, blank 24-port	
Flat unshielded:	PVQ-MIQPU24
Flat shielded:	PVQ-MIQPS24
Angled, unshielded:	PVQ-MIQAPU24
Angled, shielded:	PVQ-MIQAPS24

PanView iQ™ Fiber Trays

Open fiber tray:	PVQ-FMT
MTP^ singlemode fiber tray:	PVQ-FMTMTP-9
MTP^ multimode fiber tray:	PVQ-FMTMTP-ZX

PanView iQ™ Power Supply

12 volt power supply	
(North America):	PVQ-PS12VDC-S
(Europe):	PVQ-PS12VDC-E
(UK):	PVQ-PS12VDC-U
(Japan):	PVQ-PS12VDC-J

PanView iQ™ Expansion Port Cables

14":	PVQ-EPC14
20":	PVQ-EPC20
28":	PVQ-EPC28
35":	PVQ-EPC35
43":	PVQ-EPC43

PIM™ Software Platform and Modules

Base functionality	
module:	PIM-BASE
Connectivity management	
module:	PIM-CONNECT
Maintenance, support and warranty	
agreement:	PIM-CAMA
Software and documentation:	PIM-MEDIA


^MTP is a registered trademark of US Conec Ltd.

PanView iQ™ (PViQ™) Panel Manager


PanView iQ™ Test Data

Environmental Testing	
Operating Temperature (ambient)	0°C to 45°C (32°F to 113°F)
Operating Humidity	Up to 90%, non-condensing
Storage Temperature	-40°C to 70°C (-40°F to 158°F)
Storage Humidity	Up to 90%, non-condensing
Operating Altitude	-1000' to 10,000' (-305M to 3,048M)
Regulatory Compliance	
Designed to meet all international requirements	USA, Canada, European Union (CE Mark), Japan, Australia/N.Z.
Electromagnetic Compatibility	
Designed to meet all international requirements	USA, Canada, European Union (CE Mark), Japan, Australia/N.Z. FCC Part 15 Subpart B Class A limit; ICES-003, Issue-003:2004; VCCI Publication 2007; AS/NZS CISPR 22:2004; EN 55022:1998 +A1:2000 +A2:2003 Class A limit; EN 55024:1998 +A1:2001 +A2:2003
Safety Approvals	
Designed to meet all international requirements	USA, Canada, European Union (CE Mark), Japan, Australia/N.Z. IEC 60950-1:2001 CB Certificate, UL 60950-1:2003; CAN/CSA c22.2 No. 60950-1:2003; EN 60950-1/A11:2004


Panel Manager Module



Panel Manager Interface Unit



Mounting Bracket



Dimensions are in inches [Dimensions in brackets are metric]

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT CANADA
Markham, Ontario
cs-cdn@panduit.com
Phone: 800.777.3300

PANDUIT EUROPE LTD.
London, UK
cs-emea@panduit.com
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.
Republic of Singapore
cs-ap@panduit.com
Phone: 65.6305.7575

PANDUIT JAPAN
Tokyo, Japan
cs-japan@panduit.com
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA
Guadalajara, Mexico
cs-la@panduit.com
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.
Victoria, Australia
cs-aus@panduit.com
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

For more information

Visit us at www.panduit.com

Contact Customer Service by email: cs@panduit.com
or by phone: 800.777.3300 and reference PVSP36

PANDUIT®

©2011 Panduit Corp.
ALL RIGHTS RESERVED.
WW-PVSP36
Replaces SA-PVSP26
11/2011