

1189A Coax - Broadband CATV Coax Cable

For more Information
please call

1-800-Belden1

**Description:**

18 AWG solid .040" bare copper-covered steel conductor, gas-injected foam polyethylene insulation, Duobond® IV quad shield (60% and 40% coverage), PVC jacket.

Physical Characteristics (Overall)**Conductor**

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (in.)
1	18	Solid	BCCS - Bare Copper Covered Steel	.040

Insulation

Insulation Material:

Insulation Material	Dia. (in.)
Gas-injected FPE - Foam Polyethylene	.180

Outer Shield

Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Bonded Duofoil®	Tape	Bonded Aluminum Foil-Polyester Tape-Aluminum Foil	100
2		Braid	AL - Aluminum	60
3	Duofoil®	Tape	Aluminum Foil-Polyester Tape-Aluminum Foil	100
4		Braid	AL - Aluminum	40

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cable

Overall Nominal Diameter: 0.294 in.

Mechanical Characteristics (Overall)

Operating Temperature Range:	-40°C To +80°C
Bulk Cable Weight:	32 lbs/1000 ft.
Max. Recommended Pulling Tension:	162 lbs.
Min. Bend Radius (Install)/Minor Axis:	3 in.

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

NEC/(UL) Specification:	CATV, CM
CEC/C(UL) Specification:	CM
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes

1189A Coax - Broadband CATV Coax Cable

EU Directive 2003/11/EC (BFR):	Yes
--------------------------------	-----

CA Prop 65 (CJ for Wire & Cable):	Yes
-----------------------------------	-----

MII Order #39 (China RoHS):	Yes
-----------------------------	-----

Series Type:	Series 6
--------------	----------

Flame Test

UL Flame Test:	UL1685 UL Loading
----------------	-------------------

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Plenum Number:	1189AP
----------------	--------

Electrical Characteristics (Overall)**Nom. Characteristic Impedance:**

Impedance (Ohm)

75

Nom. Inductance:

Inductance (μH/ft)

.097

Nom. Capacitance Conductor to Shield:

Capacitance (pF/ft)

16.2

Nominal Velocity of Propagation:

VP (%)

83

Nominal Delay:

Delay (ns/ft)

1.2

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

28.0

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

4.8

Max. Attenuation:

Freq. (MHz)	Attenuation (dB/100 ft.)
-------------	--------------------------

5	.67
55	1.60
211	2.87
270	3.24
300	3.43
350	3.72
400	4.00
450	4.26
550	4.71
750	5.59
870	6.00
1000	6.54

Max. Operating Voltage - UL:

Voltage

300 V RMS

Minimum Structural Return Loss:

Description	Freq. (MHz)	Start Freq. (MHz)	Stop Freq. (MHz)	Min. SRL (dB)
-------------	-------------	-------------------	------------------	---------------

		5	1000	20
--	--	---	------	----

1189A Coax - Broadband CATV Coax Cable**Sweep Test****Sweep Testing:**

5 MHz - 1 GHz

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1189A 009U1000	1,000 FT	32.000 LB	WHITE		#18 GIFHDLDPPE DBL SH PVC
1189A 009U500	500 FT	16.500 LB	WHITE		#18 GIFHDLDPPE DBL SH PVC
1189A 0091000	1,000 FT	31.000 LB	WHITE	C	#18 GIFHDLDPPE DBL SH PVC
1189A 010U1000	1,000 FT	32.000 LB	BLACK		#18 GIFHDLDPPE DBL SH PVC .
1189A 010U500	500 FT	16.500 LB	BLACK		#18 GIFHDLDPPE DBL SH PVC
1189A 0101000	1,000 FT	31.000 LB	BLACK		#18 GIFHDLDPPE DBL SH PVC .
1189A 2901000	1,000 FT	31.000 LB	BEIGE, LIGHT		#18 GIFHDLDPPE DBL SH PVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 4 Revision Date: 05-06-2009

© 2012 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.