



For more Information
please call

1-800-Belden1



Description:

22 AWG stranded (7x30) tinned copper cond., Datalene® insulation, twisted pairs, overall Beldfoil® shield (100% coverage) plus a tinned copper braid (65% coverage), drain wire, aluminum interlocked armor, inner PVC jacket, UV resistant PVC outer jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material	Dia. (in.)
2	22	7x30	TC - Tinned Copper	.030

Insulation

Insulation Material:

Insulation Trade Name	Insulation Material
Datalene®	FHDPE - Foam High Density Polyethylene

Outer Shield

Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100.000
2		Braid	TC - Tinned Copper	65.000

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
22	7x30	TC - Tinned Copper

Outer Shield Drain Wire Diameter: .030

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Outer Jacket over Armor (y/n): Y

Outer Jacket Separator Material: PVC - Polyvinyl Chloride

Armor

Armor Type: Interlocked

Armor Material: Aluminum

Diameter over Armor: .550

Overall Cable

Overall Cabling Color Code Chart:

Number	Color
1	White/Blue Stripe & Blue/White Stripe
2	White/Orange Stripe & Orange/White Stripe

Overall Nominal Diameter: 0.650 in.

Mechanical Characteristics (Overall)

Installation Temperature Range: -20°C To +60°C

123107A Multi-Conductor - EIA Industrial RS-485 PLTC/CM

Operating Temperature Range: -40°C To +60°C

UL Temperature Rating: 60°C

Non-UL Temperature Rating: 60°C

Max. Recommended Pulling Tension: 205 lbs.

Min. Bend Radius (Install)/Minor Axis: 8.500 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 05/10/2006

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

Flame Test

UL Flame Test: UL1685 UL Loading

CSA Flame Test: FT4

Suitability

Sunlight Resistance: Yes

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)

120

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)

11.0

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/ft)

20.9

Nominal Velocity of Propagation:

VP (%)

78

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

14.7

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

1.8

Nom. Attenuation:

Description	Freq. (MHz)	Start Freq. (MHz)	Stop Freq. (MHz)	Attenuation (dB/100 ft.)
	1			.5

Max. Operating Voltage - UL:

Voltage

300 V RMS

Max. Recommended Current:

Current

123107A Multi-Conductor - EIA Industrial RS-485 PLTC/CM

2.7 Amps per conductor @ 25°C

Input/Unfitted Impedance:

Description	Freq. (MHz)	Start Freq. (MHz)	Stop Freq. (MHz)	Impedance (Ohm)
	1			

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
123107A 0101000	1,000 FT	237.000 LB	BLACK		3107A AL ARMOR PVC - SPECIAL
123107A 0105000	5,000 FT	1,035.000 LB	BLACK	C Z	3107A AIA PVC 300V

Notes:

C = CRATE REEL PUT-UP.

Z = FINAL PUT-UP LENGTH MAY VARY (+ OR -) 10% FOR SPOOLS OR REELS AND(+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.

Revision Number: 1 Revision Date: 08-08-2011

© 2012 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.