

1268A Multi-Conductor - Computer P.O.S. Cable



For more Information
please call

1-800-Belden1

**Description:**

22 AWG solid TC conductors, polyethylene insulation, twisted pairs, overall Beldfoil® shield (100% coverage) + TC braid (90% coverage), 22 AWG solid TC drain wire, PVC jacket.

Physical Characteristics (Overall)**Conductor****AWG:**

# Pairs	AWG	Stranding	Conductor Material
2	22	Solid	TC - Tinned Copper

Insulation**Insulation Material:**

Insulation Material
HDPE - High Density Polyethylene

Outer Shield**Outer Shield Material:**

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100
2		Braid	TC - Tinned Copper	90

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
22	Solid	TC - Tinned Copper

Outer Jacket**Outer Jacket Material:**

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cable

Overall Nominal Diameter: 0.270 in.

Pair**Pair Color Code Chart:**

Number	Color
1	Red & Blue
2	Black & Yellow

Mechanical Characteristics (Overall)

Operating Temperature Range:	-20°C To +60°C
UL Temperature Rating:	60°C (UL AWM Style 2582)
Bulk Cable Weight:	42 lbs/1000 ft.
Max. Recommended Pulling Tension:	68 lbs.
Min. Bend Radius (Install)/Minor Axis:	3 in.

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

NEC/(UL) Specification: CM

1268A Multi-Conductor - Computer P.O.S. Cable

CEC/C(UL) Specification:	CM
AWM Specification:	UL Style 2582 (150 V 60°C)
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	UL1685 UL Loading
----------------	-------------------

Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	1269A

Electrical Characteristics (Overall)**Nom. Characteristic Impedance:**

Impedance (Ohm)
100

Nom. Inductance:

Inductance (μH/ft)
.164

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)
15.5

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/ft)
27.5

Nominal Velocity of Propagation:

VP (%)
66

Nominal Delay:

Delay (ns/ft)
1.54

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
16.5

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
3.7

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100 ft.)
.3	.4
.6	.53
1.0	.65
1.5	.78

Max. Operating Voltage - UL:

Voltage

1268A Multi-Conductor - Computer P.O.S. Cable

300 V RMS

Max. Operating Voltage - Non-UL:**Voltage**

150 V RMS (UL AWM Style 2582)

Max. Recommended Current:**Current**

2.3 Amps per conductor @ 25°C

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1268A 0101000	1,000 FT	48.000 LB	BLACK	C	2 PR #22 HDPE SHLD PVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 05-14-2007

© 2012 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.