


## 1300SB Multi-Conductor - Category 5e ScTP Shipboard ABS Type Approved



For more Information  
please call

1-800-Belden1

**Description:**

24 AWG solid bare copper conductors, polypropylene insulation, overall Beldfoil® shield, 24 AWG stranded tinned copper drain wire, low smoke zero halogen jacket.

**Usage (Overall)****Suitable Applications:**

Shipboard LAN/Data, WI-FI, Wireless LAN, Outdoor Antenna, Radio, Broadband, RF, Where ABS Type Approval is Required

**Physical Characteristics (Overall)****Conductor****AWG:**

# Pairs	AWG	Stranding	Conductor Material
4	24	Solid	BC - Bare Copper

**Insulation****Insulation Material:**

Insulation Material	Wall Thickness (in.)	Dia. (in.)
PP - Polypropylene	.010	.042

**Outer Shield****Outer Shield Material:**

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100

**Outer Shield Drain Wire AWG:**

AWG	Stranding	Drain Wire Conductor Material
24	7x32	TC - Tinned Copper

**Outer Jacket****Outer Jacket Material:**

Outer Jacket Material
LSZH - Low Smoke Zero Halogen

**Overall Cable****Overall Nominal Diameter:**

0.260 in.

**Pair****Pair Color Code Chart:**

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

**Mechanical Characteristics (Overall)****Operating Temperature Range:**

-30°C To +105°C

**Bulk Cable Weight:**

32.400 lbs/1000 ft.

**Max. Recommended Pulling Tension:**

25 lbs.

**Min. Bend Radius (Install)/Minor Axis:**

1 in.

## 1300SB Multi-Conductor - Category 5e ScTP Shipboard ABS Type Approved

## Applicable Specifications and Agency Compliance (Overall)

## Applicable Standards &amp; Environmental Programs

NEC/(UL) Specification:	CMG-LS
CEC/C(UL) Specification:	CMG-LS
IEEE Specification:	Std. 45 clause 23
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	08/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Other Specification:	NEMA WC-63.1 Category 5e, UL 444, ABS Type Approval Certificate 05-HS500072A

## Flame Test

UL Flame Test:	UL1685 FT4 Loading, Limited Smoke
C(UL) Flame Test:	FT4, Limited Smoke
IEC Flame Test:	60332-1, 60332-3-22 (Category A)
IEEE Flame Test:	1202

## Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Sunlight Resistance:	Yes

## Electrical Characteristics (Overall)

## Nom. Mutual Capacitance:

Capacitance (pF/ft)

15

Maximum Capacitance Unbalance (pF/100 m): 330

## Nominal Velocity of Propagation:

VP (%)

70

## Maximum Delay:

Delay (ns/100 m)

538 @ 100MHz

## Max. Delay Skew:

Delay Skew (ns/100 m)

45

## Maximum Conductor DC Resistance:

DCR @ 20°C (Ohm/100 m)

9.38

## Max. Operating Voltage - UL:

Voltage

300 V RMS

## Maximum DCR Unbalanced:

DCR Unbalance @ 20°C (%)

## 1300SB Multi-Conductor - Category 5e ScTP Shipboard ABS Type Approved

3

## Electrical Characteristics-Premise (Overall)

Premise Cable Electrical Table 1:

Freq. (MHz)	Max. Attenuation (dB/100 m)	Min. NEXT (dB)	Min. PSNEXT (dB)	Min. ACR (dB)	Min. PSACR (dB)	Min RL (dB)	Min. SRL (dB)
1	2.0	65.3	62.3	60.3	60.3	20.0	20.0
4	4.1	56.3	53.3	49.2	49.2	23.0	23.0
8	5.8	51.8	48.8	43.0	43.0	24.5	24.5
10	6.5	50.3	47.3	40.8	40.8	25.0	25.0
16	8.2	47.3	44.3	36.1	36.1	25.0	25.0
20	9.3	45.8	42.8	33.5	33.5	25.0	25.0
25	10.4	44.3	41.3	30.9	30.9	24.3	24.3
31.25	11.7	42.9	39.9	28.2	28.2	23.6	23.6
62.5	17.0	38.4	35.4	18.4	18.4	21.5	21.5
100	22.0	35.3	32.3	10.3	10.3	20.1	20.1

Premise Cable Electrical Table 2:

Freq. (MHz)	Input (Unfitted) Imp. (Ohms)	Fitted Impedance	Min. ELFEXT (dB)	Min. PSELFEXT (dB)
1	100 ± 15	100 ± 15	63.8	60.8
4	100 ± 15	100 ± 15	51.7	48.7
8	100 ± 15	100 ± 15	45.7	42.7
10	100 ± 15	100 ± 15	43.8	40.8
16	100 ± 15	100 ± 15	39.7	36.7
20	100 ± 15	100 ± 15	37.7	34.7
25	100 ± 15	100 ± 15	35.8	32.8
31.25	100 ± 15	100 ± 15	33.9	30.9
62.5	100 ± 15	100 ± 15	27.8	24.8
100	100 ± 15	100 ± 15	23.8	20.8

## Notes (Overall)

**Notes:** RJ-45 Compatible. Jacket sequentially marked at 2 ft. intervals.

## Related Documents:

No related documents are available for this product

## Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1300SB 0101000	1,000 FT	35.000 LB	BLACK	C	4 PR #24 PP FS FRNHPO

**Notes:**

C = CRATE REEL PUT-UP.

Revision Number: 4    Revision Date: 06-17-2009

© 2012 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.