

1306SB Composite - Video with Power Pair



For more Information
please call

1-800-Belden1

**Description:**

Coax: 18 AWG solid bare copper conductor, foam polyethylene insulation, bare copper braid shield (95% coverage), LSZH jacket. Pair: 18 AWG stranded bare copper conductor, polypropylene insulation, LSZH jacket. Coax and pair in Siamese configuration.

Usage (Overall)**Suitable Applications:**

Security Composite Communications Cable for CCTV plus Audio or PTZ (Pan/Tilt/Zoom) CCTV Control Applications in Marine Shipboard and Offshore use

Coax**Physical Characteristics****Conductor****AWG:**

# Coax	AWG	Stranding	Conductor Material	Dia. (in.)
1	18	Solid	BC - Bare Copper	0.040

Insulation**Insulation Material:**

Insulation Material	Dia. (in.)
FPE - Foam Polyethylene	0.180

Inner Shield**Inner Shield Material:**

Type	Inner Shield Material	% Coverage (%)
Braid	BC - Bare Copper	95

Applicable Specifications and Agency Compliance**Suitability**

Suitability - Indoor: Yes

Suitability - Outdoor: Yes

Sunlight Resistance: Yes

Electrical Characteristics**Nom. Characteristic Impedance:**

Impedance (Ohm)
75

Nom. Inductance:

Inductance (μH/ft)
0.097

Nom. Capacitance Conductor to Shield:

Capacitance (pF/ft)
16.300

Nominal Velocity of Propagation:

VP (%)
83.000

Nominal Delay:

Delay (ns/ft)

1306SB Composite - Video with Power Pair

1.220

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

6.400

Nom. Inner Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

3.100

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100 ft.)
1.000	0.200
5.000	0.450
10.000	0.640
50.000	1.460
100.000	2.100
200.000	3.000
400.000	4.300
700.000	5.800
900.000	6.700
1000.000	7.100

Max. Operating Voltage - UL:

300 V RMS

Twisted Pair

Physical Characteristics

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material	Dia. (in.)
1	18	7x26	BC - Bare Copper	0.046

Insulation

Insulation Material:

Insulation Material	Dia. (in.)
PP - Polypropylene	0.059

Twisted Pair Color Code Chart:

Number	Color
1	Black and Red

Applicable Specifications and Agency Compliance

Suitability

Suitability - Indoor: Yes

Suitability - Outdoor: Yes

Sunlight Resistance: Yes

Electrical Characteristics

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)

24.000

Physical Characteristics (Overall)

Conductor

Outer Shield

Outer Shield Material:

Outer Shield Material

Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Material

LSZH - Low Smoke Zero Halogen

Overall Cable

Overall Nominal Diameter: 0.275 x 0.514 in.

Mechanical Characteristics (Overall)

Operating Temperature Range: -30°C To +75°C

Bulk Cable Weight: 66.700 lbs/1000 ft.

Max. Recommended Pulling Tension: 114.000 lbs.

Min. Bend Radius (Install)/Minor Axis: 2.750 in.

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

NEC/(UL) Specification: CMG-LS

NEC Articles: 800

CEC/C(UL) Specification: CMG-LS

IEEE Specification: Std. 45 Clause 23

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 08/01/2005

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

Other Specification: UL444, ABS Type Approval Certificate 05-HS500072D

RG Type: 6/U

Flame Test

UL Flame Test: UL1685 FT4 Loading, Limited Smoke

C(UL) Flame Test: FT4, Limited Smoke

IEC Flame Test: 60332-1, 60332-3-22 (Category A)

IEEE Flame Test: 1202

Suitability

Suitability - Indoor: Yes

Suitability - Outdoor: Yes

Sunlight Resistance: Yes

Plenum/Non-Plenum

Plenum (Y/N): No

Electrical Characteristics (Overall)**Max. Operating Voltage - UL:****Voltage**

300 V RMS

Related Documents:

No related documents are available for this product

Put Ups and Colors:

1306SB Composite - Video with Power Pair

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1306SB 0101000	1,000 FT	76.000 LB	BLACK	C	1 #18 PR, 1 RG-6/U COAX
1306SB 010500	500 FT	37.000 LB	BLACK	C	1 #18 PR, 1 RG-6/U COAX

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 6 Revision Date: 02-20-2009

© 2012 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.