# **Detailed Specifications & Technical Data**

**ENGLISH MEASUREMENT VERSION** 



## 1311A Multi-Conductor - Speaker Cable

For more Information please call

1-800-Belden1



## **Description:**

12 AWG stranded (7x24x34) high-conductivity bare copper conductors, PO insulation, PVC jacket. Sequential footage marking every two feet.

#### **Usage (Overall)**

Suitable Applications: Speaker Cable, Direct Burial, Indoor/Outdoor Home Theater, In-Wall Speaker,

**Outdoor Speaker** 

## **Physical Characteristics (Overall)**

#### Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material	Dia. (in.)
2	12	7x24x34	High Conductivity BC - Bare Copper	.102

#### Insulation

**Insulation Material:** 

Insulation Material	Dia. (in.)
PO - Polyolefin	.140

#### **Outer Shield**

**Outer Shield Material:** 

<b>Outer Shield Material</b>
Unshielded

#### **Outer Jacket**

**Outer Jacket Material:** 



#### **Overall Cable**

**Overall Cabling Color Code Chart:** 

Number	Color
1	Black
2	Red

Overall Nominal Diameter: 0.352 in.

#### **Mechanical Characteristics (Overall)**

Operating Temperature Range:	-20°C To +75°C
UL Temperature Rating:	75°C
Bulk Cable Weight:	67 lbs/1000 ft.
Max. Recommended Pulling Tension:	152 lbs.
Min. Bend Radius (Install)/Minor Axis:	3.500 in.

#### **Applicable Specifications and Agency Compliance (Overall)**

## **Applicable Standards & Environmental Programs**

NEC/(UL) Specification:	CL3, CM
CEC/C(UL) Specification:	CM

Page 1 of 3 01-06-2012

# **Detailed Specifications & Technical Data**

#### **ENGLISH MEASUREMENT VERSION**



## 1311A Multi-Conductor - Speaker Cable

EU Directive 2000/53/EC (ELV):	Yes	
EU Directive 2002/95/EC (RoHS):	Yes	
EU RoHS Compliance Date (mm/dd/yyyy):	07/01/2005	
EU Directive 2002/96/EC (WEEE):	Yes	
EU Directive 2003/11/EC (BFR):	Yes	
CA Prop 65 (CJ for Wire & Cable):	Yes	
MII Order #39 (China RoHS):	Yes	
Flame Test		
UL Flame Test:	UL1581 Vertical Flame and FT-1 Flame Test	
CSA Flame Test:	FT1	
Suitability		
Suitability - Indoor:	Yes	
Suitability - Outdoor:	Yes	
Plenum/Non-Plenum		
Plenum (Y/N):	No	
Plenum Number:	6000UE	

## **Electrical Characteristics (Overall)**

Nom. Inductance:

Inductance (µH/ft) .15

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)
22.3

Nominal Velocity of Propagation:

**VP (%)** 66

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft) 1.6

Max. Operating Voltage - UL:

Voltage 300 V RMS

Max. Recommended Current:

Current
17 Amps per conductor @ 25°C

#### **Related Documents:**

No related documents are available for this product

## **Put Ups and Colors:**

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1311A 0081000	1,000 FT	74.000 LB	GRAY	С	2 #12 PE FRPVC
1311A 008500	500 FT	36.500 LB	GRAY	С	2 #12 PE FRPVC
1311A 0101000	1,000 FT	74.000 LB	BLACK	С	2 #12 PE FRPVC
1311A 010500	500 FT	36.500 LB	BLACK	С	2 #12 PE FRPVC
1311A 1SL1000	1,000 FT	74.000 LB	WHITE 1SL	С	2 #12 PE FRPVC
1311A 1SL500	500 FT	36.500 LB	WHITE 1SL	С	2 #12 PE FRPVC

Notes:

C = CRATE REEL PUT-UP.

Page 2 of 3 01-06-2012

# **Detailed Specifications & Technical Data**

#### **ENGLISH MEASUREMENT VERSION**



#### 1311A Multi-Conductor - Speaker Cable

Revision Number: 1 Revision Date: 11-23-2011

© 2012 Belden, Inc All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.