

1319SB Multi-Conductor - Category 6 UTP - ABS Type Approved



For more Information
please call

1-800-Belden1



Description:

23 AWG solid bare copper conductors, polyolefin insulation, LSZH jacket with ripcord, descending footage marking every two feet.

Usage (Overall)

Suitable Applications:

Shipboard, Premise Horizontal Cable, Gigabit Ethernet, 100BaseTX, 100BaseVG ANYLAN, 155ATM, 622ATM, Cat 6, ABS Type Approval, WI-FI, Wireless LAN, Outdoor Antenna, Radio, Broadband

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material
4	23	Solid	BC - Bare Copper

Insulation

Insulation Material:

Insulation Material
PO - Polyolefin

Inner Jacket

Inner Jacket Material:

Inner Jacket Material	Nom. Dia. (in.)
LSZH - Low Smoke Zero Halogen	0.261

Inner Jacket Ripcord:

Yes

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
LSZH - Low Smoke Zero Halogen

Outer Jacket Ripcord:

No

Overall Cable

Overall Cabling Fillers:

Rod Center Member

Overall Nominal Diameter:

0.314 in.

Pair

Pair Color Code Chart:

Number	Color
1	White/Blue Stripe and Blue
2	White/Orange Stripe and Orange
3	White/Green Stripe and Green
4	White/Brown Stripe and Brown

Mechanical Characteristics (Overall)

Operating Temperature Range:	-30°C To +105°C
Bulk Cable Weight:	43 lbs/1000 ft.
Max. Recommended Pulling Tension:	40 lbs.
Min. Bend Radius (Install)/Minor Axis:	3 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMG-LS
CEC/C(UL) Specification:	CMG-LS
IEEE Specification:	Std. 45 clause 23
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	08/08/2006
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Other Specification:	NEMA WC-63.1 Category 6, UL 444, ABS Type Approval Certificate 06-HS184641G

Flame Test

UL Flame Test:	UL1685 FT4 Loading, Limited Smoke
CSA Flame Test:	FT4, Limited Smoke
IEC Flame Test:	60332-1, 60332-3-22 (Category A)
IEEE Flame Test:	1202

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Sunlight Resistance:	Yes

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Mutual Capacitance:

Capacitance (pF/ft)

15

Maximum Capacitance Unbalance (pF/100 m): 330

Nominal Velocity of Propagation:

VP (%)

70

Maximum Delay:

Delay (ns/100 m)

537 @ 100MHz

Max. Delay Skew:

Delay Skew (ns/100 m)

1319SB Multi-Conductor - Category 6 UTP - ABS Type Approved

45

Maximum Conductor DC Resistance:

DCR @ 20°C (Ohm/100 m)
8.2

Max. Operating Voltage - UL:

Voltage
300 V RMS

Maximum DCR Unbalanced:

DCR Unbalance @ 20°C (%)
5

Electrical Characteristics-Premise (Overall)

Premise Cable Electrical Table 1:

Freq. (MHz)	Max. Attenuation (dB/100 m)	Min. NEXT (dB)	Min. PSNEXT (dB)	Min. ACR (dB)	Min. PSACR (dB)	Min RL (dB)	Min. SRL (dB)
1	2.0	74.3	72.3	72.3	70.3	20.0	na
4	3.8	65.3	63.3	61.5	59.5	23.0	na
8	5.3	60.8	58.8	55.4	53.4	24.5	na
10	6.0	59.3	57.3	53.3	51.3	25.0	na
16	7.6	56.2	54.3	48.7	46.7	25.0	na
20	8.5	54.8	52.8	46.3	44.3	25.0	na
25	9.5	53.3	51.3	43.8	41.8	24.3	na
31.25	10.7	51.9	49.9	41.2	39.2	23.6	na
62.5	15.4	47.4	45.4	32.0	30.0	21.5	na
100	19.8	44.3	42.3	24.5	22.5	20.1	na
155	25.2	41.5	39.5	16.3	14.3	18.8	na
200	29.0	39.8	37.8	10.8	8.8	18.0	na
250	32.8	38.3	36.3	5.5	3.5	17.3	na

Premise Cable Electrical Table 2:

Freq. (MHz)	Input (Unfitted) Imp. (Ohms)	Fitted Impedance	Min. ELFEXT (dB)	Min. PSELFEXT (dB)
1	100 ± 15	100 ± 15	67.8	64.8
4	100 ± 15	100 ± 15	55.8	52.7
8	100 ± 15	100 ± 15	49.7	46.7
10	100 ± 15	100 ± 15	47.8	44.8
16	100 ± 15	100 ± 15	43.7	40.7
20	100 ± 15	100 ± 15	41.8	38.8
25	100 ± 15	100 ± 15	39.8	36.8
31.25	100 ± 15	100 ± 15	37.9	34.9
62.5	100 ± 15	100 ± 15	31.9	28.9
100	100 ± 15	100 ± 15	27.8	24.8
155	100 ± 22	100 ± 15	23.9	20.9
200	100 ± 22	100 ± 15	21.8	18.8
250	100 ± 32	100 ± 15	19.8	16.8

Notes (Overall)

Notes: RJ-45 Compatible. Jacket marked with descending footage at 2 ft. intervals.

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1319SB 0101000	1,000 FT	46.000 LB	BLACK	C	4 PR #23 PP FRNHPO FRNHPO
1319SB 0105000	5,000 FT	235.000 LB	BLACK		4 PR #23 PP FRNHPO FRNHPO

Notes:
C = CRATE REEL PUT-UP.

1319SB Multi-Conductor - Category 6 UTP - ABS Type Approved

Revision Number: 3 Revision Date: 10-06-2010

© 2012 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.