

1283S3 Coax - Banana Peel® Unjacketed VideoFLEX® Bundles



For more Information
please call

1-800-Belden1



Description:

20 AWG solid .032" bare copper conductors, foam FEP insulation, Duofoil® + tinned copper braid shield (95% coverage), Flam arrest® jackets in colors, 5 and 6 bundles in all black, center spline binder.

Usage (Overall)

Suitable Applications:

RGB, VGA, SVGA, XGA, SXGA, UXGA, HDTV, LCD, Plasma, Digital Signage, Component Video, Video Mult, Animation, Special effects. Suitable for use in Plenum spaces

Physical Characteristics (Overall)

Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (in.)
3	20	Solid	BC - Bare Copper	.032

Insulation

Insulation Material:

Insulation Material	Dia. (in.)
FFEP - Foam Fluorinated Ethylene Propylene	.133

Inner Shield

Inner Shield Material:

Layer #	Inner Shield Trade Name	Type	Inner Shield Material	Coverage (%)
1	Duofoil®	Tape	Aluminum Foil-Polyester Tape-Aluminum Foil	100
2		Braid	TC - Tinned Copper	95

Inner Jacket

Inner Jacket Material:

Inner Jacket Material	Nom. Dia. (in.)
Plenum Grade PVC - Polyvinyl Chloride	.196

Inner Jacket Color Code Chart:

Number	Color
1	Red
2	Green
3	Blue

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
Unjacketed

Overall Cable

Overall Cabling Fillers:

Bonded Spline

Overall Nominal Diameter:

0.422 in.

1283S3 Coax - Banana Peel® Unjacketed VideoFLEX® Bundles

Mechanical Characteristics (Overall)

Operating Temperature Range:	-20°C To +75°C
UL Temperature Rating:	60°C
Non-UL Temperature Rating:	75°C
Bulk Cable Weight:	93 lbs/1000 ft.
Max. Recommended Pulling Tension:	216 lbs.
Min. Bend Radius (Install)/Minor Axis:	6.500 in.

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

NEC/(UL) Specification:	CMP
CEC/C(UL) Specification:	CMP
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	06/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
RG Type:	59/U

Flame Test

UL Flame Test:	NFPA 262
----------------	----------

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes

Plenum/Non-Plenum

Plenum (Y/N):	Yes
Non-Plenum Number:	7794A

Electrical Characteristics (Overall)**Nom. Characteristic Impedance:**

Impedance (Ohm)

75

Nom. Inductance:

Inductance (μH/ft)

0.107

Nom. Capacitance Conductor to Shield:

Capacitance (pF/ft)

16.2

Nominal Velocity of Propagation:

VP (%)

83

Nominal Delay:

Delay (ns/ft)

1.22

1283S3 Coax - Banana Peel® Unjacketed VideoFLEX® Bundles

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

10.0

Nom. Inner Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

3.8

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100 ft.)
1	0.3
3.6	0.6
10	0.9
71.5	2.1
135	2.7
270	3.8
360	4.4
540	5.5
720	6.4
750	6.5
1000	7.6
1500	9.4
2500	12.4
3000	13.8

Max. Operating Voltage - UL:

Voltage

300 V RMS

Other Electrical Characteristic 1:

Impedance tested in accordance with ASTM D-4566 paragraph 43.2, option 2 using a 75 Ohm fixed bridge and termination.

Other Electrical Characteristic 2:

Return Loss Tested in Accordance With ASTM D-4566 Paragraph 45.3, Using a 75 Ohm Fixed Bridge and Termination.

Minimum Return Loss:

Start Freq. (MHz)	Stop Freq. (MHz)	Min. RL (dB)
5	850	23
851	3000	15

Sweep Test

Sweep Testing:

Sweep tested 5 MHz to 3 GHz.

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1283S3 0001000	1,000 FT	102.000 LB	NONE	C	3C20 RGB
1283S3 000250	250 FT	26.250 LB	NONE	C	3C20 RGB
1283S3 000500	500 FT	51.500 LB	NONE	C	3C20 RGB

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 09-30-2009

© 2012 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract,

1283S3 Coax - Banana Peel® Unjacketed VideoFLEX® Bundles

negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.