

1321SB Multi-Conductor - ABS Type Approved Fire Alarm Cable



For more Information
please call

1-800-Belden1

**Description:**

16 AWG solid bare copper conductors, ceramifiable silicone insulation, Beldfoil® shield, drain wire, LSZH jacket.

Usage (Overall)**Suitable Applications:**

ABS Type Approved, Fire Alarm, Shipboard, Circuit Integrity, CI, FPLR-CI, CMG-LS< IEEE 45 clause 23, IEC 60092-376 clause 17, 60092-351, 60754-1, 60754-2, 61034, UL1685 FT4 Loading, Limited Smoke, IEC, 60332-3-22 (Category A), 60332-1, 60331-23

Physical Characteristics (Overall)**Conductor****AWG:**

# Conductors	AWG	Stranding	Conductor Material
2	16	Solid	BC - Bare Copper

Insulation**Insulation Material:**

Insulation Material	Wall Thickness (in.)	Dia. (in.)
Silicone Rubber	.034	.120

Outer Shield**Outer Shield Material:**

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil®	Tape	Polyester Tape-Aluminum Foil	100

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
20	7x28	TC - Tinned Copper

Outer Jacket**Outer Jacket Material:**

Outer Jacket Material	Nom. Wall Thickness (in.)
LSZH - Low Smoke Zero Halogen	.045

Overall Cable**Overall Cabling Lay Length & Direction:**

Length (in.)	Twists (ft.)
3.7	3.2

Overall Cabling Color Code Chart:

Number	Color
1	Black
2	Red

Overall Nominal Diameter:

0.337 in.

Mechanical Characteristics (Overall)

Operating Temperature Range: -20°C To +105°C

UL Temperature Rating: 105°C

Max. Recommended Pulling Tension: 62.400 lbs.

1321SB Multi-Conductor - ABS Type Approved Fire Alarm Cable

Min. Bend Radius (Install)/Minor Axis:	3.400 in.
--	-----------

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

NEC/(UL) Specification:	CMG-LS, FPLR-CI
-------------------------	-----------------

NEC Articles:	760
---------------	-----

CEC/C(UL) Specification:	CMG-LS
--------------------------	--------

IEEE Specification:	Std. 45 clause 23
---------------------	-------------------

EU CE Mark:	Yes
-------------	-----

EU Directive 2000/53/EC (ELV):	Yes
--------------------------------	-----

EU Directive 2002/95/EC (RoHS):	Yes
---------------------------------	-----

EU RoHS Compliance Date (mm/dd/yyyy):	08/07/2006
---------------------------------------	------------

EU Directive 2002/96/EC (WEEE):	Yes
---------------------------------	-----

EU Directive 2003/11/EC (BFR):	Yes
--------------------------------	-----

CA Prop 65 (CJ for Wire & Cable):	Yes
-----------------------------------	-----

MII Order #39 (China RoHS):	Yes
-----------------------------	-----

Other Specification:	UL444, UL1424, ABS Type Approval Certificate 06-HS184641F
----------------------	---

Flame Test

UL Flame Test:	UL1685 FT4 Loading, Limited Smoke
----------------	-----------------------------------

C(UL) Flame Test:	FT4, Limited Smoke
-------------------	--------------------

IEC Flame Test:	60332-1, 60331-23, 60332-3-22 (Category A)
-----------------	--

IEEE Flame Test:	1202
------------------	------

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Suitability - Outdoor:	Yes
------------------------	-----

Sunlight Resistance:	Yes
----------------------	-----

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)**Nom. Capacitance Conductor to Conductor:**

Capacitance (pF/ft)

31

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/ft)

52

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

4.0

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

8.2

Max. Operating Voltage - UL:

Voltage

300 V RMS

Related Documents:

1321SB Multi-Conductor - ABS Type Approved Fire Alarm Cable

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1321SB 0021000	1,000 FT	62.000 LB	RED	C	1 FS PR #16 SIL FRNHPO
1321SB 0101000	1,000 FT	62.000 LB	BLACK	C	1 FS PR #16 SIL FRNHPO

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 2 Revision Date: 02-20-2009

© 2012 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.