


139463 Twinax - Blue Hose® Cable



For more Information
please call

1-800-Belden1

**Description:**

20 AWG stranded (7x28) tinned copper conductors, polyethylene insulation, overall Beldfoil® (100% coverage) plus a tinned copper braid shield (55% coverage), PVC inner jacket, steel interlocked armor, sunlight-resistant PVC outer jacket.

Physical Characteristics (Overall)**Conductor****AWG:**

# Pairs	AWG	Stranding	Conductor Material	Dia. (in.)
1	20	7x28	TC - Tinned Copper	.038

Insulation**Insulation Material:**

Insulation Material
PE - Polyethylene

Outer Shield**Outer Shield Material:**

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100
2		Braid	TC - Tinned Copper	55

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
20	7x28	TC - Tinned Copper

Outer Jacket**Outer Jacket Material:**

Outer Jacket Material
PVC - Polyvinyl Chloride

Outer Jacket Diameter:

Nom. Dia. (in.)
.238

Outer Jacket over Armor (y/n): Y

Armor

Armor Type: Interlocked

Armor Material: Steel

Armor Thickness: .025

Diameter over Armor: .453

Overall Cable

Overall Nominal Diameter: 0.563 in.

Pair**Pair Color Code Chart:**

Number	Color
1	Clear & Blue

Mechanical Characteristics (Overall)

Operating Temperature Range:	-40°C To +60°C
Bulk Cable Weight:	224 lbs/1000 ft.
Max. Recommended Pulling Tension:	205 lbs.
Min. Bend Radius (Install)/Minor Axis:	6.500 in.

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

NEC/(UL) Specification:	CM, CL2
CEC/C(UL) Specification:	CM, CMG FT4, HLBCD
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	10/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Customer Part Number Reference Specification:	Allen Bradley P/N 1770-CD

Flame Test

UL Flame Test:	UL1685 UL Loading
----------------	-------------------

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)**Nom. Characteristic Impedance:**

Impedance (Ohm)

78

Nom. Inductance:

Inductance (μH/ft)

0.12

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)

19.7

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/ft)

36

Nominal Velocity of Propagation:

VP (%)

66

Nominal Delay:

Delay (ns/ft)

1.54

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

9.5

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

4.1

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100 ft.)
1	0.6
10	2.1
50	5.0
100	7.5
200	11.0
400	16.0

Max. Operating Voltage - UL:

Voltage
300 V RMS

Other Electrical Characteristic 1:

DC Resistance Unbalanced: .77 Ohms/1000 ft Max

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
139463 J221000	1,000 FT	232.000 LB	BLUE, STRONG	C Z	9463 STEEL ARMORED PVC
139463 J224000	4,000 FT	948.000 LB	BLUE, STRONG		9463 STEEL ARMORED PVC
139463 J226000	6,000 FT	1,488.000 LB	BLUE, STRONG	C Z	9463 STEEL ARMORED PVC

Notes:

C = CRATE REEL PUT-UP.

Z = FINAL PUT-UP LENGTH MAY VARY (+ OR -) 10% FOR SPOOLS OR REELS AND(+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.

Revision Number: 1 Revision Date: 05-14-2007

© 2012 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.