


## 129463 Twinax - Blue Hose® Cable



For more Information  
please call

1-800-Belden1

**Description:**

20 AWG stranded (7x28) tinned copper conductors, polyethylene insulation, overall Beldfoil® (100% coverage) plus a 55% tinned copper braid shield (55% coverage), PVC inner jacket, aluminum interlocked armor, sunlight-resistant PVC outer jacket.

**Physical Characteristics (Overall)****Conductor****AWG:**

# Pairs	AWG	Stranding	Conductor Material	Dia. (in.)
1	20	7x28	TC - Tinned Copper	.038

**Insulation****Insulation Material:**

Insulation Material
PE - Polyethylene

**Outer Shield****Outer Shield Material:**

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100
2		Braid	TC - Tinned Copper	55

**Outer Shield Drain Wire AWG:**

AWG	Stranding	Drain Wire Conductor Material
20	7x28H	TC - Tinned Copper

**Outer Jacket****Outer Jacket Material:**

Outer Jacket Material
PVC - Polyvinyl Chloride

**Outer Jacket Diameter:**

Nom. Dia. (in.)
.238

**Armor**

**Armor Type:** Interlocked

**Armor Material:** Aluminum

**Armor Thickness:** .025

**Diameter over Armor:** .441

**Overall Cable**

**Overall Nominal Diameter:** 0.553 in.

**Pair****Pair Color Code Chart:**

Number	Color
1	Clear & Blue

**Mechanical Characteristics (Overall)**

Operating Temperature Range:	-40°C To +60°C
------------------------------	----------------

Bulk Cable Weight:	133 lbs/1000 ft.
--------------------	------------------

Max. Recommended Pulling Tension:	205 lbs.
-----------------------------------	----------

Min. Bend Radius (Install)/Minor Axis:	6.500 in.
--	-----------

### Applicable Specifications and Agency Compliance (Overall)

#### Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CM, CL2
-------------------------	---------

CEC/C(UL) Specification:	CM, CMG FT4, HLBCD
--------------------------	--------------------

EU Directive 2000/53/EC (ELV):	Yes
--------------------------------	-----

EU Directive 2002/95/EC (RoHS):	Yes
---------------------------------	-----

EU RoHS Compliance Date (mm/dd/yyyy):	10/01/2005
---------------------------------------	------------

EU Directive 2002/96/EC (WEEE):	Yes
---------------------------------	-----

EU Directive 2003/11/EC (BFR):	Yes
--------------------------------	-----

CA Prop 65 (CJ for Wire & Cable):	Yes
-----------------------------------	-----

MII Order #39 (China RoHS):	Yes
-----------------------------	-----

Customer Part Number Reference Specification:	Allen Bradley P/N 1770-CD
---	---------------------------

#### Flame Test

UL Flame Test:	UL1685 UL Loading
----------------	-------------------

#### Suitability

Sunlight Resistance:	Yes
----------------------	-----

#### Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

### Electrical Characteristics (Overall)

#### Nom. Characteristic Impedance:

Impedance (Ohm)
-----------------

78
----

#### Nom. Inductance:

Inductance (μH/ft)
--------------------

0.12
------

#### Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)
---------------------

19.7
------

#### Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/ft)
---------------------

36
----

#### Nominal Velocity of Propagation:

VP (%)
--------

66
----

#### Nominal Delay:

Delay (ns/ft)
---------------

1.54
------

#### Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
--------------------------

9.5
-----

#### Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
--------------------------

4.1
-----

**Nom. Attenuation:**

Freq. (MHz)	Attenuation (dB/100 ft.)
1	0.6
10	2.1
50	5.0
100	7.5
200	11.0
400	16.0

**Max. Operating Voltage - UL:**

Voltage
300 V RMS

**Other Electrical Characteristic 1:**

DC Resistance Unbalance: .77 Ohms/1000 ft Max

**Related Documents:**

No related documents are available for this product

**Put Ups and Colors:**

Item #	Putup	Ship Weight	Color	Notes	Item Desc
129463 J221000	1,000 FT	143.000 LB	BLUE, STRONG		9463 ALUM ARMORED PVC
129463 J226000	6,000 FT	954.000 LB	BLUE, STRONG		9463 ALUM ARMORED PVC

Revision Number: 2    Revision Date: 02-09-2010

© 2012 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.