


1409R Multi-Conductor - CMR Rated Cable



For more Information
please call

1-800-Belden1

**Description:**

24 AWG stranded (7x30) TC conductor, polyolefin insulation, individually shielded Beldfoil® (100% coverage) numbered/color-coded PVC jackets, jackets and shields bonded to strip simultaneously, overall Beldfoil shield and 18 AWG TC drain wire.

Physical Characteristics (Overall)**Conductor****AWG:**

# Pairs	AWG	Stranding	Conductor Material	Dia. (in.)
6	24	7x32	TC - Tinned Copper	.024

Insulation**Insulation Material:**

Insulation Material	Dia. (in.)
PO - Polyolefin	.040

Inner Shield**Inner Shield Material:**

Inner Shield Trade Name	Type	Inner Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100

Inner Shield Drain Wire AWG:

AWG
24

Inner Shield Drain Wire Stranding: 7x32

Inner Shield Drain Wire Conductor Material: TC - Tinned Copper

Inner Jacket**Inner Jacket Material:**

Inner Jacket Material	Nom. Dia. (in.)
PVC - Polyvinyl Chloride	.111

Outer Shield**Outer Shield Material:**

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
18	7x26	TC - Tinned Copper

Outer Jacket**Outer Jacket Material:**

Outer Jacket Material
PVC - Polyvinyl Chloride

Outer Jacket Ripcord: Yes

Overall Cable**Overall Cabling Color Code Chart:**

Number	Color
1	Brown

2	Red
3	Orange
4	Yellow
5	Green
6	Blue

Overall Nominal Diameter: 0.412 in.

Pair**Pair Color Code Chart:**

Number	Color
1	Red
2	Black

Pair Lay Length & Direction:

Lay Length (in.)	Twists/ft. (twist/ft)
1.750	6.900

Mechanical Characteristics (Overall)

Operating Temperature Range:	-30°C To +75°C
Bulk Cable Weight:	91 lbs/1000 ft.
Max. Recommended Pulling Tension:	121 lbs.
Min. Bend Radius (Install)/Minor Axis:	4.250 in.

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

NEC/(UL) Specification:	CMR
CEC/C(UL) Specification:	CMG
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	UL1666 Riser
CSA Flame Test:	FT4

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)**Nom. Characteristic Impedance:**

Impedance (Ohm)
50

Nom. Inductance:

Inductance (μH/ft)
.18

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)
31

1409R Multi-Conductor - CMR Rated Cable

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/ft)

58

Nominal Velocity of Propagation:

VP (%)

66

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

23.3

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

6

Ind. Pair Nominal Shield DC Resistance @ 20 Deg. C: 15.900 Ohm/1000 ft

Maximum Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

6

Max. Operating Voltage - UL:

Voltage

300 V RMS

Max. Recommended Current:

Current

1.05 Amps per conductor @ 25°C

Notes (Overall)

Notes: Pair jackets and shields bonded so both strip simultaneously. Beldfoil® provides high reliability with ease of termination.

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1409R 0101000	1,000 FT	100.000 LB	BLACK	C	6 #24 PR BFS PVC FS PVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 04-18-2008

© 2012 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.