Detailed Specifications & Technical Data

ENGLISH MEASUREMENT VERSION



1320SB Multi-Conductor - ABS Type Approved Fire Alarm Cable





For more Information please call

1-800-Belden1



Description:

18 AWG solid bare copper conductors, ceramifiable silicone insulation, Beldfoil® shield, drain wire, LSZH jacket.

Usage (Overall)

Suitable Applications:

ABS Type Approved, Fire Alarm, Shipboard, Circuit Integirty, CI, FPLR-CI, CMG-LS, IEEE 45 clause 23, IEC 60092-376 clause 17, 60092-351, 60754-1, 60754-2, 61034, UL1685 FT4 Loading, Limited Smoke, IEC 60332-3-22 (Category A), 60332-1, 60331-23

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
2	18	Solid	BC - Bare Copper

Insulation

Insulation Material:

Insulation Material	Wall Thickness (in.)	Dia. (in.)
Silicone Rubber	.034	.109

Outer Shield

Outer Shield Material:

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil®	Tape	Polyester Tape-Aluminum Foil	100

Outer Shield Drain Wire AWG:

	Stranding	Drain Wire Conductor Material
20	7x28	TC - Tinned Copper

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (in.)			
LSZH - Low Smoke Zero Halogen	.045			

Overall Cable

Overall Cabling Lay Length & Direction:

Length (in.)	Twists (ft.)
3.25	3.7

Overall Cabling Color Code Chart:

Number	Color
1	Black
2	Red

Overall Nominal Diameter: 0.314 in.

Mechanical Characteristics (Overall)					
	Operating Temperature Range:	-20°C To +105°C			
	UL Temperature Rating:	105°C			
	Max. Recommended Pulling Tension:	39.200 lbs.			

Page 1 of 3 01-06-2012

Detailed Specifications & Technical Data





1320SB Multi-Conductor - ABS Type Approved Fire Alarm Cable

oplicable Specifications and Agency Co					
Applicable Standards & Environmental Programs					
NEC/(UL) Specification:	CMG-LS, FPLR-CI				
NEC Articles:	760				
CEC/C(UL) Specification:	CMG-LS				
IEEE Specification:	Std. 45 clause 23				
EU CE Mark:	Yes				
EU Directive 2000/53/EC (ELV):	Yes				
EU Directive 2002/95/EC (RoHS):	Yes				
EU RoHS Compliance Date (mm/dd/yyyy):	08/07/2006				
EU Directive 2002/96/EC (WEEE):	Yes				
EU Directive 2003/11/EC (BFR):	Yes				
CA Prop 65 (CJ for Wire & Cable):	Yes				
MII Order #39 (China RoHS):	Yes				
Other Specification:	UL444, UL1424, ABS Type Approval Certificate 06-HS184641F				
lame Test					
UL Flame Test:	UL1685 FT4 Loading, Limited Smoke				
C(UL) Flame Test:	FT4, Limited Smoke				
IEC Flame Test:	60332-1, 60331-23, 60332-3-22 (Category A)				
IEEE Flame Test:	1202				
Suitability					
Suitability - Indoor:	Yes				
Suitability - Outdoor:	Yes				
Sunlight Resistance:	Yes				
Plenum/Non-Plenum					
Plenum (Y/N):	No				

Electrical Characteristics (Overall)

Nom. Capacitance	Conductor	to	Cond	uctor
------------------	-----------	----	------	-------

Capacitance (pF/ft)
28

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/ft)
52

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft) 6.6

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft) 8.2

Max. Operating Voltage - UL:

Voltage 300 V RMS

Related Documents:

Page 2 of 3 01-06-2012

Detailed Specifications & Technical Data





1320SB Multi-Conductor - ABS Type Approved Fire Alarm Cable

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1320SB 0021000	1,000 FT	50.000 LB	RED	С	1 FS PR #18 SIL FRNHPO
1320SB 0101000	1,000 FT	50.000 LB	BLACK	С	1 FS PR #18 SIL FRNHPO

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 2 Revision Date: 02-20-2009

© 2012 Belden, Inc All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.