

1502SB Multi-Conductor - Multimedia Control Cable



For more Information
please call

1-800-Belden1

**Description:**

22 AWG stranded (7x30) TC conductors, HDFPE insulation (data), STP (Data) w/Beldfoil®, TC drain wire;
 18 AWG (16x30) TC conductors, unshielded (power) pair, polypropylene insulation (power), LSZH Jacket.

Usage (Overall)**Suitable Applications:**

ABS Type Approved, Shipboard, Multi-Media Control, RS-422, RS-232, CMG-LS, IEEE 45 clause 23, IEC 60092-376 clause 17, 60092-351, 60754-1, 60754-2, 61034, UL1685 FT4 Loading, Limited Smoke, IEC 60332-3-22 (Category A), 60332-1, 60331-23

Physical Characteristics (Overall)**Conductor****AWG:**

# Conductors	# Pairs	AWG	Stranding	Conductor Material
2		22	7x30	TC - Tinned Copper
	1	18	16x30	TC - Tinned Copper

Insulation**Insulation Material:**

Insulation Trade Name	Insulation Material	Wall Thickness (in.)	AWG
Datalene®	HDFPE - High Density Foam Polyethylene (Data)	0.020	18
	PP - Polypropylene (Power)	0.007	22

Inner Shield**Inner Shield Material:**

Layer #	Inner Shield Trade Name	Type	Inner Shield Material	Coverage (%)	Stranding	Dia. (in.)	Conductor Material
22 AWG Pair	Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100			

Inner Shield Drain Wire AWG:

AWG	Stranding	Conductor Material
24	7x32	TC - Tinned Copper

Outer Shield**Outer Shield Material:**

Outer Shield Material
Unshielded

Outer Jacket**Outer Jacket Material:**

Outer Jacket Material	Nom. Wall Thickness (in.)
LSZH - Low Smoke Zero Halogen	.045

Outer Jacket Diameter:

Nom. Dia. (in.)
.255

Outer Jacket Ripcord:

Yes

Overall Cable**Overall Nominal Diameter:**

0.250 in.

Pair**Pair Color Code Chart:**

1502SB Multi-Conductor - Multimedia Control Cable

Number	Color
1	Blue & White
2	Red & Black

Pair Lay Length & Direction:

Lay Length (in.)	Twists/ft. (twist/ft)
2.000	6.000

Mechanical Characteristics (Overall)

Operating Temperature Range:	-30°C To +75°C
Non-UL Temperature Rating:	75°C
Bulk Cable Weight:	39 lbs/1000 ft.
Max. Recommended Pulling Tension:	59.800 lbs.
Min. Bend Radius (Install)/Minor Axis:	2.500 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMG-LS
CEC/C(UL) Specification:	CMG-LS
IEEE Specification:	Std. 45 clause 23
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	08/07/2006
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Other Specification:	UL444, ABWS Type Approval Certificate 06-HS184641C

Flame Test

UL Flame Test:	UL1685 FT4 Loading, Limited Smoke
C(UL) Flame Test:	FT4, Limited Smoke
IEC Flame Test:	60332-1, 60332-3-22 (Category A)
IEEE Flame Test:	1202

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Sunlight Resistance:	Yes
Non-halogenated:	Yes

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Description	Impedance (Ohm)
22 AWG Pair	100

Nom. Inductance:

Description	Inductance (µH/ft)
-------------	--------------------

1502SB Multi-Conductor - Multimedia Control Cable

22 AWG	.232
18 AWG	.168

Nom. Capacitance Conductor to Conductor:

Description	Capacitance (pF/ft)
22 AWG Pair	14
18 AWG Pair	

Nom. Capacitance Cond. to Other Conductor & Shield:

Description	Freq. (MHz)	Start Freq. (MHz)	Stop Freq. (MHz)	Capacitance (pF/ft)
22 AWG Pair				38

Nom. Conductor DC Resistance:

Description	DCR @ 20°C (Ohm/1000 ft)
22 AWG	16.3
18 AWG	6.9

Max. Operating Voltage - UL:

Voltage
300 V RMS

Max. Recommended Current:

Current
3.8 Amps per conductor @ 25°C (22 AWG); 7.2 Amps per conductor @ 25°C (18 AWG)

Notes (Overall)

Notes: Sequential footage marking every two feet.

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1502SB 0101000	1,000 FT	43.000 LB	BLACK	C	2#18 PP + 2FS #22 FHDPE FRNHPO

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 3 Revision Date: 02-20-2009

© 2012 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.