

## 1502P Multi-Conductor - Multimedia Control Cable



For more Information  
please call

1-800-Belden1



### Description:

22 AWG stranded (7x30) TC conductors, plenum, foam FEP insulation (data), STP w/Beldfoil®, 18 AWG (16x30) TC conductors unshielded, polypropylene binder tape, Flammarrest® insulation (power), Flammarrest® jacket.

### Physical Characteristics (Overall)

#### Conductor

AWG:

# Conductors	# Pairs	AWG	Stranding	Conductor Material
2	1	22	7x30	TC - Tinned Copper
	1	18	16x30	TC - Tinned Copper

#### Insulation

Insulation Material:

Insulation Trade Name	Insulation Material	Wall Thickness (in.)	AWG
	FFEP - Foam Fluorinated Ethylene Propylene	0.025	22
Flammarrest®	LS PVC - Low Smoke Polyvinyl Chloride	0.011	18

#### Inner Shield

Inner Shield Material:

Layer #	Inner Shield Trade Name	Type	Inner Shield Material	Coverage (%)	Stranding	Dia. (in.)	Conductor Material
22 AWG Pair	Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100			

Inner Shield Drain Wire AWG:

AWG
24

Inner Shield Drain Wire Stranding: 7x32

Inner Shield Drain Wire Conductor Material: TC - Tinned Copper

#### Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

#### Outer Jacket

Outer Jacket Material:

Outer Jacket Trade Name	Outer Jacket Material	Nom. Wall Thickness (in.)
Flammarrest®	LS PVC - Low Smoke Polyvinyl Chloride	.015

Outer Jacket Ripcord: Yes

#### Overall Cable

Overall Nominal Diameter: 0.205 in.

#### Pair

Pair Color Code Chart:

Number	Color
1	Blue & White
2	Red & Black

Pair Lay Length & Direction:

Lay Length (in.)	Twists/ft. (twist/ft)

2.000	6.000
-------	-------

## Mechanical Characteristics (Overall)

Operating Temperature Range:	-20°C To +60°C
Non-UL Temperature Rating:	75°C
Bulk Cable Weight:	25 lbs/1000 ft.
Max. Recommended Pulling Tension:	59.800 lbs.
Min. Bend Radius (Install)/Minor Axis:	2.500 in.

## Applicable Specifications and Agency Compliance (Overall)

### Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMP
CEC/C(UL) Specification:	CMP
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

### Flame Test

UL Flame Test:	NFPA 262
C(UL) Flame Test:	FT6

### Plenum/Non-Plenum

Plenum (Y/N):	Yes
Non-Plenum Number:	1502R

## Electrical Characteristics (Overall)

### Nom. Characteristic Impedance:

Description	Impedance (Ohm)
22 AWG Pair	100

### Nom. Inductance:

Description	Inductance (µH/ft)
22 AWG	.232
18 AWG	.168

### Nom. Capacitance Conductor to Conductor:

Description	Capacitance (pF/ft)
22 AWG Pair	14
18 AWG Pair	29

### Nom. Capacitance Cond. to Other Conductor & Shield:

Description	Freq. (MHz)	Start Freq. (MHz)	Stop Freq. (MHz)	Capacitance (pF/ft)
22 AWG Pair				38

### Nom. Conductor DC Resistance:

Description	DCR @ 20°C (Ohm/1000 ft)
22 AWG	16.3
18 AWG	6.9

### Max. Operating Voltage - UL:

Voltage

## 1502P Multi-Conductor - Multimedia Control Cable

300 V RMS

**Max. Recommended Current:**

**Current**

3.8 Amps per conductor @ 25°C (22 AWG); 7.2 Amps per conductor @ 25°C (18 AWG)

### Notes (Overall)

**Notes:** Sequential footage marking every two feet.

### Related Documents:

No related documents are available for this product

### Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1502P 0101000	1,000 FT	33.000 LB	BLACK	C	COMPOSITE CABLE PVC
1502P 8771000	1,000 FT	33.000 LB	NATURAL	C	COMPOSITE CABLE PVC

**Notes:**

C = CRATE REEL PUT-UP.

Revision Number: 3    Revision Date: 01-07-2010

© 2012 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.