


For more Information
please call

1-800-Belden1



Description:

24 AWG stranded (7x32) TC conductor, polyolefin insulation, individually shielded Beldfoil® (100% coverage) numbered/color-coded PVC jackets, jackets and shields bonded to strip simultaneously, overall Beldfoil shield and 24 AWG TC drain wire.

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material	Dia. (in.)
2	24	7x32	TC - Tinned Copper	.024

Insulation

Insulation Material:

Insulation Material	Wall Thickness (in.)	Dia. (in.)
PO - Polyolefin	.008	.040

Inner Shield

Inner Shield Material:

Inner Shield Trade Name	Type	Inner Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100

Inner Shield Drain Wire AWG:

AWG
24

Inner Shield Drain Wire Stranding: 7x32

Inner Shield Drain Wire Conductor Material: TC - Tinned Copper

Inner Jacket

Inner Jacket Material:

Inner Jacket Material	Nom Wall (in.)	Nom. Dia. (in.)
PVC - Polyvinyl Chloride	.014	.111

Inner Jacket Color Code Chart:

Number	Color
1	Brown
2	Red

Outer Shield

Outer Shield Material:

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
24	7x32	TC - Tinned Copper

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (in.)
PVC - Polyvinyl Chloride	.034

Outer Jacket Ripcord: Yes

Overall Cable

Overall Nominal Diameter: 0.301 in.

Pair

Pair Color Code Chart:

Color
Red & Black

Pair Lay Length & Direction:

Lay Length (in.)	Twists/ft. (twist/ft)
1.750	6.850

Mechanical Characteristics (Overall)

Operating Temperature Range:	-35°C To +75°C
Bulk Cable Weight:	42 lbs/1000 ft.
Max. Recommended Pulling Tension:	55.400 lbs.
Min. Bend Radius (Install)/Minor Axis:	2.900 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CM
CEC/C(UL) Specification:	CM
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Plenum/Non-Plenum

Plenum (Y/N): No

Electrical Characteristics (Overall)

Nom. Inductance:

Inductance (µH/ft)
.18

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)
31

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/ft)
58

Nominal Velocity of Propagation:

VP (%)
66

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
23.3

Ind. Pair Nominal Shield DC Resistance @ 20 Deg. C: 15.900 Ohm/1000 ft

1509C Multi-Conductor - Flexible, CM Rated Cable

Max. Operating Voltage - UL:

Voltage
300 V RMS

Max. Recommended Current:

Current
1.05 Amps per conductor @ 25°C

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1509C B591000	1,000 FT	46.000 LB	BLACK, MATTE	C	2 PR #24 PO FS PVC FS PVC
1509C B59500	500 FT	24.000 LB	BLACK, MATTE	C	2 PR #24 PO FS PVC FS PVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 04-18-2008

© 2012 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.