

1521A Coax - Bundled RGB Coaxial Cables Miniature Type

For more Information
please call

1-800-Belden1



Description:

30 AWG stranded (7x38) .012" TC conductors, foam HDPE insulation, Coaxes w/Duofoil® + TC braid (90% coverage), overall Beldfoil® shield, overall PVC jkt.

Physical Characteristics (Overall)

Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (in.)
4	30	7x38	TC - Tinned Copper	.013

Insulation

Insulation Material:

Insulation Material	Dia. (in.)
FHDPE - Foam High Density Polyethylene	.056

Inner Shield

Inner Shield Material:

Layer #	Inner Shield Trade Name	Type	Inner Shield Material	Coverage (%)
1	Duofoil®	Tape	Aluminum Foil-Polyester Tape-Aluminum Foil	100
2		Braid	TC - Tinned Copper	90

Inner Jacket

Inner Jacket Material:

Inner Jacket Material	Nom. Dia. (in.)
PVC - Polyvinyl Chloride	.102

Inner Jacket Color Code Chart:

Number	Color
1	Red
2	Green
3	Blue
4	White

Outer Shield

Outer Shield Material:

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cable

Overall Nominal Diameter: 0.310 in.

Mechanical Characteristics (Overall)

Operating Temperature Range: -40°C To +60°C

UL Temperature Rating: 60°C (UL AWM Style 1354)

Non-UL Temperature Rating: 60°C

1521A Coax - Bundled RGB Coaxial Cables Miniature Type

Bulk Cable Weight: 55 lbs/1000 ft.

Max. Recommended Pulling Tension: 56 lbs.

Min. Bend Radius (Install)/Minor Axis: 3 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: CL2

AWM Specification: UL Style 1354 (each coax); UL Style 2688 (overall)

EU CE Mark: No

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 01/01/2004

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

RG Type: Mini

Suitability

Plenum/Non-Plenum

Plenum (Y/N): No

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)

75

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/ft)

17.3

Nominal Velocity of Propagation:

VP (%)

78

Nominal Delay:

Delay (ns/ft)

1.30

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

100.0

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

9.5

Nom. Attenuation:

Freq. (MHz) Attenuation (dB/100 ft.)

1	0.8
5	1.5
10	2.2
30	4.0
50	5.4
100	8.2
200	12.5
400	18.9
700	26.5

1521A Coax - Bundled RGB Coaxial Cables Miniature Type

900	30.8
1000	32.8

Max. Operating Voltage - UL:

Voltage
30 V RMS (UL AWM Style 1354)
300 V RMS (CL2)

Minimum Return Loss:

Description	Freq. (MHz)	Start Freq. (MHz)	Stop Freq. (MHz)	Min. RL (dB)
		10	40	25

Sweep Test

Sweep Testing: 100% sweep tested. 10MHz to 40MHz.

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1521A 0101000	1,000 FT	59.000 LB	BLACK	C	4 #30 FHDPE BRD PVC FS PVC
1521A 010500	500 FT	31.000 LB	BLACK	C	4 #30 FHDPE BRD PVC FS PVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 4 Revision Date: 04-11-2008

© 2012 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.