

For more Information
please call

1-800-Belden1



Description:

28 AWG stranded (7x36) bare copper conductors, non-plenum, patented step polyolefin insulation, twisted pairs, overall Beldfoil® shielded + TC braid shield (65% coverage), TC drain wire, PVC jacket (see RISC color code chart below).

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
7	28	7x36	BC - Bare Copper

Insulation

Insulation Material:

Layer #	Insulation Material
1	Solid PP - Solid Polypropylene
2	Solid PE - Solid Polyethylene

Outer Shield

Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100
2		Braid	TC - Tinned Copper	65

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
28	7x36	TC - Tinned Copper

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cable

Overall Cabling Color Code Chart:

Number	Color
1	White over Blue
2	White over Orange
3	White over Green
4	White over Brown
5	White over Gray
6	White over Red
7	White over Yellow

Overall Nominal Diameter: 0.190 in.

Mechanical Characteristics (Overall)

Non-UL Temperature Rating: -30°C To +75°C

Bulk Cable Weight: 23 lbs/1000 ft.

Min. Bend Radius (Install)/Minor Axis: 2 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CL2
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Other Specification:	RJ-45 compatible
Customer Part Number Reference Specification:	IBM P/N: XX, YY Cable

Flame Test

UL Flame Test:	UL1685 UL Loading
----------------	-------------------

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)
12.5

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/ft)
23

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
63

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
7.2

Max. Operating Voltage - UL:

Voltage
150 V RMS

Max. Recommended Current:

Current
0.9 Amps per conductor @ 25°C

Notes (Overall)

Notes: Patent # 5, 220, 130. Single conductors are dual insulated. Outer layer of insulation must be stripped off before attaching modular connectors.

Notes (Cont'd.): Use a stripping tool such as Cooper Tools Xcelite Model 103-S or equivalent with a mechanical stop to avoid nicking the inner insulation.

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
--------	-------	-------------	-------	-------	-----------

1540A Multi-Conductor - IBM RISC System/6000

1540A 0081000	1,000 FT	21.000 LB	GRAY	C	7 #28 FEP/PE SH PVC
---------------	----------	-----------	------	---	---------------------

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 05-14-2007

© 2012 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.