### **ENGLISH MEASUREMENT VERSION**



# 1585LC Multi-Conductor - Category 5e Nonbonded-Pair Cable

For more Information please call

1-800-Belden1



## **Description:**

24 AWG Solid Bare Copper Conductors, Plenum, FEP Teflon® Insulation, Twisted Pairs, FEP Jacket

# **Usage (Overall)**

Suitable Applications:

Premise Horizontal Cable, Gigabit Ethernet, 100BaseTX, 100BaseVG ANYLAN, 155ATM, 622ATM, NTSC/PAL Component or Composite Video, AES/EBU, Digital Video, RS-422

## **Physical Characteristics (Overall)**

### Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material
4	24	Solid	BC - Bare Copper

#### Insulation

**Insulation Material:** 

Insulation Trade Name	Insulation Material
Teflon®	FEP - Fluorinated Ethylene Propylene

### **Outer Shield**

**Outer Shield Material:** 

Outer Shield	Material
Unshielded	

### **Outer Jacket**

**Outer Jacket Material:** 

Outer Jacket Material
FEP - Fluorinated Ethylene Propylene

### **Outer Jacket Diameter:**

**Nom. Dia. (in.)** 0.184

Outer Jacket Ripcord: No

## **Overall Cable**

Overall Nominal Diameter: 0.184 in.

### **Pair**

# Pair Color Code Chart:

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

# **Mechanical Characteristics (Overall)**

Operating Temperature Range:	-40°C To +150°C		
Bulk Cable Weight:	25 lbs/1000 ft.		
Max. Recommended Pulling Tension:	35 lbs.		

Page 1 of 4 01-06-2012





# 1585LC Multi-Conductor - Category 5e Nonbonded-Pair Cable

Min. Bend Radius (Install)/Minor Axis: 0.500 in

	Min. Bend Radius (Install)/Minor Axis:	0.500 in.						
Ap	Applicable Specifications and Agency Compliance (Overall)							
Ap	Applicable Standards & Environmental Programs							
	NEC/(UL) Specification:	CMP, FHC 25/50						
	NEC Articles:	NFPA 259, NFPA 255						
CEC/C(UL) Specification:		CMP, FHC 25/50						
Other Standards:		ISO/IEC 11801 ed 2.1 (2008) Class D						
EU CE Mark:		Yes						
	EU Directive 2000/53/EC (ELV):	Yes						
	EU Directive 2002/95/EC (RoHS):	Yes						
	EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004						
	EU Directive 2002/96/EC (WEEE):	Yes						
	EU Directive 2003/11/EC (BFR):	Yes						
	CA Prop 65 (CJ for Wire & Cable):	Yes						
	MII Order #39 (China RoHS):	Yes						
	Telecommunications Standards:	Category 5e - TIA 568.C.2						
	Other Specification:	NEMA WC-63.1 Category 5e, UL Verified to Category 5e						
Fla	ame Test							
	UL Flame Test:	NFPA 262 Plenum Flame Test (UL910)(FT6), UL723 (NFPA 255)						
	C(UL) Flame Test:	Limited Smoke						
	CSA Flame Test:	FT6, Limited Smoke						
Su	itability							
	Suitability - Indoor:	Yes						
	Suitability - Outdoor:	Yes						
	Suitability - Aerial:	Yes - UL						
	Suitability - Burial:	No						
Plenum/Non-Plenum								
	Plenum (Y/N):	Yes						

1585A

1583A

### **Electrical Characteristics (Overall)**

Nom. Mutual Capacitance:

**Plenum Number:** 

Non-Plenum Number:

Capacitance (pF/ft)
15

Maximum Capacitance Unbalance (pF/100 m): 330

Nominal Velocity of Propagation:

**VP (%)**72

Maximum Delay:

**Delay (ns/100 m)** 510 @ 100MHz

Max. Delay Skew:

Delay Skew (ns/100 m) 45

**Maximum Conductor DC Resistance:** 

Page 2 of 4 01-06-2012

**ENGLISH MEASUREMENT VERSION** 



# 1585LC Multi-Conductor - Category 5e Nonbonded-Pair Cable

DCR @ 20°C (Ohm/100 m) 9.38

Max. Operating Voltage - UL:

Voltage 300 V RMS

Maximum DCR Unbalanced:

DCR Unbalance @ 20°C (%) 3

## **Electrical Characteristics-Premise (Overall)**

### **Premise Cable Electrical Table 1:**

Freq. (MHz)	Max. Attenuation (dB/100 m)	Min. NEXT (dB)	Min. PSNEXT (dB)	Min. ACR (dB)	Min. PSACR (dB)	Min RL (dB)	Min. SRL (dB)
1	2.0	65.3	62.3	63.0	60.3	20.0	23.0
4	4.1	56.3	53.3	51.0	49.2	23.0	23.0
8	5.8	51.8	48.8	46.0	43.0	24.5	24.5
10	6.5	50.3	47.3	43.0	40.8	25.0	25.0
16	8.2	47.3	44.3	39.0	36.0	25.0	25.0
20	9.3	45.8	42.8	36.5	33.5	25.0	25.0
25	10.4	44.3	41.3	33.9	30.9	24.3	24.3
31.25	11.7	42.9	39.9	31.0	28.2	23.6	23.6
62.5	17.0	38.4	35.4	22.0	19.0	21.5	21.5
100	22.0	35.3	32.3	14.0	10.3	20.1	20.1
155	28.1	32.5	29.5	4.4	1.4	15.8	
200	32.0	30.8	27.8	4.0	1.0	15.0	

### **Premise Cable Electrical Table 2:**

Freq. (MHz)	Input (Unfitted) Imp. (Ohms)	Fitted Impedance	Min. ELFEXT (dB)	Min. PSELFEXT (dB)
1	100 ± 15	100 ± 15	63.8	60.8
4	100 ± 15	100 ± 15	51.7	48.7
8	100 ± 15	100 ± 15	45.7	42.7
10	100 ± 15	100 ± 15	43.8	40.8
16	100 ± 15	100 ± 15	39.7	36.7
20	100 ± 15	100 ± 15	37.7	34.7
25	100 ± 15	100 ± 15	35.8	32.8
31.25	100 ± 15	100 ± 15	33.9	30.9
62.5	100 ± 15	100 ± 15	27.8	24.9
100	100 ± 15	100 ± 15	23.8	20.8
155	100 ± 25	100 ± 15	19.9	16.9
200	100 ± 25	100 ± 15	17.7	14.7

## **Notes (Overall)**

Notes: Jacket sequentially marked at 2 ft. intervals. Thrid party verified to ANSI/TIA-568-C.2, Category 5e.

### **Related Documents:**

No related documents are available for this product

# **Put Ups and Colors:**

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1585LC 006U1000	1,000 FT	23.000 LB	BLUE, LIGHT		CAT5E 4PR U/UTP LC BOX
1585LC 0061000	1,000 FT	24.000 LB	BLUE, LIGHT	С	CAT5E 4PR U/UTP LC REEL
1585LC 009U1000	1,000 FT	23.000 LB	WHITE		CAT5E 4PR U/UTP LC BOX
1585LC 0091000	1,000 FT	24.000 LB	WHITE	С	CAT5E 4PR U/UTP LC REEL

Notes:

C = CRATE REEL PUT-UP.

Page 3 of 4 01-06-2012

### **ENGLISH MEASUREMENT VERSION**



# 1585LC Multi-Conductor - Category 5e Nonbonded-Pair Cable

Revision Number: 3 Revision Date: 05-03-2011

© 2012 Belden, Inc All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.

Page 4 of 4