#### **ENGLISH MEASUREMENT VERSION**



# 1624R Multi-Conductor - Category 5 Nonbonded-Pair ScTP Cable



For more Information please call

1-800-Belden1



## **Description:**

24 AWG solid bare copper conductors, non-plenum, Polyolefin insulation, twisted pairs, Beldfoil® shield, 24 (7x32) TC drain wire, RJ-45 compatible, see color code chart (below), PVC jacket (red, orange, yellow, green blue, purple or light gray).

# **Usage (Overall)**

**Suitable Applications:** 

Premise Horizontal Cable, Gigabit Ethernet, 100BaseTX, 100BaseVG ANYLAN, 155ATM, 622ATM, NTSC/PAL Component or Composite Video, AES/EBU Digital Audio, AES51, RS-422, 100MHz Category 5

## **Physical Characteristics (Overall)**

#### Conductor

AWG:

# Pairs	AWG	Stranding	<b>Conductor Material</b>
4	24	Solid	BC - Bare Copper

#### Insulation

**Insulation Material:** 



#### **Outer Shield**

**Outer Shield Material:** 

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100

#### **Outer Shield Drain Wire AWG:**

AWG	Stranding	<b>Drain Wire Conductor Material</b>
24	7x32	TC - Tinned Copper

#### **Outer Jacket**

**Outer Jacket Material:** 

Outer Jacket Material
PVC - Polyvinyl Chloride

#### **Overall Cable**

Overall Nominal Diameter: 0.260 in.

#### Pair

#### **Pair Color Code Chart:**

Number	Color
1	White/Blue Stripe & Blue
2	White /Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

## **Mechanical Characteristics (Overall)**

Operating Temperature Range:	-20°C To +75°C
Bulk Cable Weight:	30 lbs/1000 ft.
Max. Recommended Pulling Tension:	25 lbs.

Page 1 of 4 01-06-2012





# 1624R Multi-Conductor - Category 5 Nonbonded-Pair ScTP Cable

Applicable Specifications and Agency Compliance (Overall)					
Applicable Standards & Environmental Programs					
NEC/(UL) Specification:	CMR, UL444				
CEC/C(UL) Specification:	CMR				
Other Standards:	11801 Category 5				
EU CE Mark:	Yes				
EU Directive 2000/53/EC (ELV):	Yes				
EU Directive 2002/95/EC (RoHS):	Yes				
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004				
EU Directive 2002/96/EC (WEEE):	Yes				
EU Directive 2003/11/EC (BFR):	Yes				
CA Prop 65 (CJ for Wire & Cable):	Yes				
MII Order #39 (China RoHS):	Yes				
Telecommunications Standards:	568-B.2 Category 5				
Other Specification:	NEMA WC-63.1 Category 5, UL Verified to Category 5				
Flame Test					
UL Flame Test:	UL1666 Riser				
CSA Flame Test:	FT4				
Plenum/Non-Plenum					
Plenum (Y/N):	No				
Plenum Number:	1624P				

# E

Capacitance (pF/ft)

Maximum Capacitance Unbalance (pF/100 m): 300

Nominal Velocity of Propagation:

VP (%) 67

Maximum Delay:

Delay (ns/100 m) 538 @ 100MHz

Max. Delay Skew:

Delay Skew (ns/100 m)

**Maximum Conductor DC Resistance:** 

DCR @ 20°C (Ohm/100 m)

Max. Operating Voltage - UL:

Voltage 300 V RMS

Maximum DCR Unbalanced:

DCR Unbalance @ 20°C (%)

Page 2 of 4

**ENGLISH MEASUREMENT VERSION** 



# 1624R Multi-Conductor - Category 5 Nonbonded-Pair ScTP Cable

# **Electrical Characteristics-Premise (Overall)**

#### **Premise Cable Elelctricals:**

Freq. (MHz)	Max. Attenuation (dB/100 m)	Min. NEXT (dB)	Min. PSNEXT (dB)	Min. SRL (dB)	Fitted Imp. (Ohms)
1	2.0	62.2	62.3	23.0	100 ± 15%
4	4.1	53.3	53.3	23.0	100 ± 15%
8	5.8	48.8	48.8	23.0	100 ± 15%
10	6.5	47.3	47.3	23.0	100 ± 15%
16	8.2	44.3	44.3	23.0	100 ± 15%
20	9.3	42.8	42.8	23.0	100 ± 15%
25	10.4	41.3	41.3	22.0	100 ± 15%
31.25	11.7	39.9	39.9	21.1	100 ± 15%
62.5	17.0	35.4	35.4	18.0	100 ± 15%
100	22.0	32.2	32.3	16.0	100 ± 15%

## **Notes (Overall)**

Notes: Shield is bonded to jacket inner wall for electrical stability. RJ-45 Compatible. Jacket sequentially marked at 2 ft. intervals. Third party verified to TIA/EIA-568-B.2, Category 5.

#### **Related Documents:**

No related documents are available for this product

#### **Put Ups and Colors:**

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1624R B02A1000	1,000 FT	36.000 LB	PURPLE		CAT5 4PR F/UTP CMR RIB
1624R B021000	1,000 FT	33.000 LB	PURPLE		CAT5 4PR F/UTP CMR REEL
1624R F2VA1000	1,000 FT	36.000 LB	GRAY, DEC		CAT5 4PR F/UTP CMR RIB
1624R F2V1000	1,000 FT	33.000 LB	GRAY, DEC	С	CAT5 4PR F/UTP CMR REEL
1624R F2V1640	1,640 FT	54.120 LB	GRAY, DEC		CAT5 4PR F/UTP CMR REEL
1624R 002A1000	1,000 FT	36.000 LB	RED		CAT5 4PR F/UTP CMR RIB
1624R 0021000	1,000 FT	33.000 LB	RED	С	CAT5 4PR F/UTP CMR REEL
1624R 003A1000	1,000 FT	36.000 LB	ORANGE		CAT5 4PR F/UTP CMR RIB
1624R 0031000	1,000 FT	33.000 LB	ORANGE	С	CAT5 4PR F/UTP CMR REEL
1624R 004A1000	1,000 FT	36.000 LB	YELLOW		CAT5 4PR F/UTP CMR RIB
1624R 0041000	1,000 FT	33.000 LB	YELLOW	С	CAT5 4PR F/UTP CMR REEL
1624R 005A1000	1,000 FT	36.000 LB	GREEN, DARK		CAT5 4PR F/UTP CMR RIB
1624R 0051000	1,000 FT	33.000 LB	GREEN, DARK	С	CAT5 4PR F/UTP CMR REEL
1624R 006A1000	1,000 FT	36.000 LB	BLUE, LIGHT		CAT5 4PR F/UTP CMR RIB
1624R 0061000	1,000 FT	33.000 LB	BLUE, LIGHT	С	CAT5 4PR F/UTP CMR REEL

## Notes:

C = CRATE REEL PUT-UP.

Revision Number: 2 Revision Date: 03-24-2011

© 2012 Belden, Inc. All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.

Page 3 of 4

**ENGLISH MEASUREMENT VERSION** 



1624R Multi-Conductor - Category 5 Nonbonded-Pair ScTP Cable

Page 4 of 4 01-06-2012