
ENGLISH MEASUREMENT VERSION



1803F Multi-Conductor - Multi-Pair Snake Cable



For more Information please call

1-800-Belden1



Description:

24 AWG stranded (7x32) TC conductor, Datalene® insulation, pairs individually shielded with bonded Beldfoil® with a drain wire and have numbered and color-coded PVC jackets, overall Beldfoil® shield/drain wire + overall PVC jacket w/nylon rip cord.

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material	Dia. (in.)
4	24	7x32	TC - Tinned Copper	.024

Insulation

Insulation Material:

Insulation Trade Name	Insulation Material	Dia. (in.)
Datalene®	FHDPE - Foam High Density Polyethylene	.068

Inner Shield

Inner Shield Material:

Inner Shield Trade Name	Type	Inner Shield Material	Coverage (%)
Beldfoil®	Tape	Bonded Aluminum Foil-Polyester Tape	100

Inner Shield Drain Wire AWG:



Inner Shield Drain Wire Stranding: Stranded

Inner Shield Drain Wire Conductor Material: TC - Tinned Copper

Inner Jacket

Inner Jacket Material:

Inner Jacket Material	Nom. Dia. (in.)
PVC - Polyvinyl Chloride	.167

Inner Jacket Color Code Chart:

Number	Color
1	Brown and Numbered 1
2	Red and Numbered 2
3	Orange and Numbered 3
4	Yellow and Numbered 4

Outer Shield

Outer Shield Material:

1	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
	Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
16	Stranded	TC - Tinned Copper

Outer Jacket

Outer Jacket Material:

Outer Jacket Material

Page 1 of 4 01-06-2012





1803F Multi-Conductor - Multi-Pair Snake Cable

PVC - Polyvinyl Chloride

Outer Jacket Ripcord: Yes

Overall Cable

Overall Nominal Diameter: 0.488 in.

Pair

Pair Color Code Chart:

Number	Color
1	Red & Black
2	Red & Black
3	Red & Black
4	Red & Black

Mechanical	Characteristics	(Overall)

Operating Temperature Range:	-30°C To +60°C
UL Temperature Rating:	60°C
Bulk Cable Weight:	100 lbs/1000 ft.
Max. Recommended Pulling Tension:	82.500 lbs.
Min. Bend Radius (Install)/Minor Axis:	5 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMG
CEC/C(UL) Specification:	CMG
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Other Specification:	AES/EBU
ame Test	

Fla

UL Flame Test:	UL1685 FT4 Loading		
C(UL) Flame Test:	FT4		

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm) 110

Nom. Inductance:

Inductance (µH/ft)

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft) 12

Page 2 of 4

ENGLISH MEASUREMENT VERSION



1803F Multi-Conductor - Multi-Pair Snake Cable

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/ft))
26	1

Nominal Velocity of Propagation:



Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
23.7

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100 ft.)		
.384	.69		
.7056	.93		
.768	.96		
1.024	1.07		
1.4112	1.19		
1.536	1.21		
2.048	1.31		
2.8224	1.41		
3.0720	1.45		
4.096	1.57		
5.6448	1.76		
6.144	1.83		
8.192	2.01		
11.2896	2.24		
12.288	2.30		
24.576	3.08		

Max. Operating Voltage - UL:

Voltage 300 V RMS

Max. Recommended Current:

Current
2.75 Amps per conductor @ 25°C

Notes (Overall)

Notes: Pair jackets and shields are bonded so both strip simultaneously with automatic stripping equipment. Datalene® insulation features include low dielectric constant and a dissipation factor for high-speed, low-distortion data handling. Physical properties include good crush resistance and light weight.

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1803F Z4B1000	1,000 FT	107.000 LB	VIO Z4B	С	4 #24 FHDPE FS PR PVC FS PVC
1803F Z4B500	500 FT	57.500 LB	VIO Z4B	С	4 #24 FHDPE FS PR PVC FS PVC

Notes

C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 05-14-2007

© 2012 Belden, Inc All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express,

Page 3 of 4 01-06-2012

ENGLISH MEASUREMENT VERSION



1803F Multi-Conductor - Multi-Pair Snake Cable

statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.

Page 4 of 4 01-06-2012