

For more Information
please call

1-800-Belden1



Description:

Series 6, 18 AWG solid .040" bare copper or bare copper-covered steel conductor (see below), gas-injected foam polyethylene insulation, Duobond® II + aluminum braid shield (60% coverage), black polyethylene jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (in.)
1	18	Solid	BCAC - Bare Copper w/Anti-Corrosion Treatment	.0403

Corrosion Resistance: Yes

Insulation

Insulation Material:

Insulation Material	Dia. (in.)
Gas-injected FPE - Foam Polyethylene	.180

Outer Shield

Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Bonded Duofoil®	Tape	Bonded Aluminum Foil-Polyester Tape-Aluminum Foil	100
2		Braid	AL - Aluminum	60

Outer Shield Flooding Grease: CoreGuard®

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PE - Polyethylene

Overall Cable

Overall Nominal Diameter: 0.270 in.

Mechanical Characteristics (Overall)

Operating Temperature Range: -55°C To +80°C

Non-UL Temperature Rating: 80°C

Bulk Cable Weight: 24 lbs/1000 ft.

Max. Recommended Pulling Tension: 80 lbs.

Min. Bend Radius (Install)/Minor Axis: 2.750 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

EU CE Mark: No

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 01/01/2004

EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MIL Order #39 (China RoHS):	Yes
Series Type:	Series 6

Suitability

Suitability - Burial:	Yes
-----------------------	-----

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)	Tolerance (Ohms)
75	± 3

Nom. Inductance:

Inductance (µH/ft)
.097

Nom. Capacitance Conductor to Shield:

Capacitance (pF/ft)
16.2

Nominal Velocity of Propagation:

VP (%)
83

Nominal Delay:

Delay (ns/ft)
1.2

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
6.4

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
9

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100 ft.)
5	.5
55	1.4
211	2.6
500	4.1
750	5.1
862	5.5
1000	6.0
1450	7.8
1800	8.6
2250	9.8
3000	11.3

Max. Attenuation:

Freq. (MHz)	Attenuation (dB/100 ft.)
5	0.67
55	1.60
211	2.87
500	4.48
750	5.59
862	5.98

1000	6.54
1450	8.00
1800	8.80
2250	10.0
3000	11.9

Max. Operating Voltage - Non-UL:

Voltage
300 V RMS

Minimum Structural Return Loss:

Start Freq. (MHz)	Stop Freq. (MHz)	Min. SRL (dB)
950	2250	15
2250	3000	10

Sweep Test

Sweep Testing: 950 MHz - 3 GHz

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1829BC 0101000	1,000 FT	27.000 LB	BLACK	C	#18 LDPE/GIFHDLPE SH PE

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 4 Revision Date: 04-25-2008

© 2012 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.