

For more Information
please call

1-800-Belden1



Description:

RG-401/U type, 14 AWG solid .065" silver-plated copper conductor, TFE Teflon® insulation, copper-tin composite shield (100% coverage), unjacketed.

Physical Characteristics (Overall)

Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (in.)
1	14	Solid	SPC - Silver Plated Copper	.065

Insulation

Insulation Material:

Insulation Trade Name	Insulation Material	Dia. (in.)
Teflon®	TFE - Tetrafluoroethylene	.210

Outer Shield

Outer Shield Material:

Layer #	Type	Outer Shield Material	Coverage (%)
1	Tape	Copper Foil	100
2	Braid	Tin-Filled Composite	100

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
Unjacketed

Overall Cable

Overall Nominal Diameter: 0.246 in.

Mechanical Characteristics (Overall)

Operating Temperature Range: -70°C To +200°C

UL Temperature Rating: 105°C

Non-UL Temperature Rating: 200°C

Bulk Cable Weight: 81 lbs/1000 ft.

Max. Recommended Pulling Tension: 122 lbs.

Min. Bend Radius (Install)/Minor Axis: 0.370 in.

Min. Bend Radius (Continuous Flexing): 1.120 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

AWM Specification: UL Style 10245

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 01/01/2005

EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MIL Order #39 (China RoHS):	Yes
RG Type:	401/U

Flame Test

Other Flame Test:	Horizontal Wire
-------------------	-----------------

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)

50

Nom. Inductance:

Inductance (µH/ft)

0.070

Nom. Capacitance Conductor to Shield:

Capacitance (pF/ft)

29.6

Nominal Velocity of Propagation:

VP (%)

69.5

Nominal Delay:

Delay (ns/ft)

1.46

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

2.5

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

8

Maximum VSWR:

Description	Freq. (MHz)	Max. VSWR
Ramp Function, End Points	400	1.1
	1800	1.38

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100 ft.)
400	3.8
500	4.4
1000	6.8
2000	10.4
3000	13.4
5000	18.5
7000	22.8
10000	28.4
15000	36.6
18000	41.0

Max. Attenuation:

Freq. (MHz)	Attenuation (dB/100 ft.)
400	5.0
500	5.7
1000	8.8
3000	17.3
5000	23.8
10000	36.6
18000	52.8

Nom. Power Rating:

Freq. (MHz)	Rating (W)
400	1900
500	1665
1000	1105
2000	733
3000	577
5000	427
7000	350
10000	283
15000	223
18000	200

Max. Operating Voltage - UL:

Voltage
30 V RMS

Max. Operating Voltage - Non-UL:

Voltage
2900 V RMS

Notes (Overall)

Notes: US Patents 4, 694, 122 & 5, 293, 001. Patent held in the U.S., Singapore, Australia, Germany, France, and England. Patent pending in Japan. Teflon® is a registered trademark of E. I. duPont de Nemours and Co. used under license by Belden, Inc.

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1675A TIN100	100 FT	8.100 LB	TIN - COLOR	E	#14 TFE CU FS BRD TINNED COAX
1675A TIN500	500 FT	40.500 LB	TIN - COLOR	C E	#14 TFE CU FS BRD TINNED COAX

Notes:

C = CRATE REEL PUT-UP.

E = MAY CONTAIN MORE THAN 1 PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 25'

Revision Number: 2 Revision Date: 05-14-2007

© 2012 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

1675A Coax - 50 Ohm Microwave Cable

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.