Detailed Specifications & Technical Data



ENGLISH MEASUREMENT VERSION

1908A Multi-Conductor - FleXnake® Super-Flexible, High-Performance Cable



For more Information please call

1-800-Belden1



Description:

24 AWG stranded (41x40) bare copper conductor, polyolefin insulation, individually shielded with double serve "French Braid" (93% coverage), TC drain wire, numbered/color-coded PVC jackets, overall Black PVC jacket.

Physical Characteristics (Overall)	
Conductor AWG:	
# Conductors # Pairs AWG Stranding Conductor M	Material Dia. (in.)
16 8 24 41x40 BC - Bare Co	opper .023
Insulation Insulation Material:	
Insulation Material Wall Thickness (in.) Dia. (in.)	
PO - Polyolefin .008 .040	
Inner Shield Inner Shield Material:	
TypeInner Shield MaterialCoverage (%)French BraidBC - Bare Copper95	
Inner Shield Drain Wire AWG: AWG 24	
Inner Shield Drain Wire Stranding:	19x26
Inner Shield Drain Wire Conductor Material:	TC - Tinned Copper
Inner Jacket Inner Jacket Material:	
Inner Jacket Material Nom Wall (in.) Nom. Dia. (in.) PVC - Polyvinyl Chloride .014 .119	n.)
Outer Shield Material: Outer Shield Material Unshielded	
Outer Jacket Outer Jacket Material:	
Outer Jacket Material Nom. Wall Thickness (in.) PVC - Polyvinyl Chloride .050	
Overall Cable Overall Cabling Color Code Chart:	
Color 7	
Overall Nominal Diameter:	0.482 in.
Pair Pair Color Code Chart:	
Color	

Detailed Specifications & Technical Data



ENGLISH MEASUREMENT VERSION

1908A Multi-Conductor - FleXnake® Super-Flexible, High-Performance Cable

Red and Black

Pair Lay Length & Direction:

Lay Length (in.) Twists/ft. (twist/ft)

1.000 12.000

Mechanical Characteristics (Overall)

Operating Temperature Range:	-20°C To +60°C	
Bulk Cable Weight:	130 lbs/1000 ft.	
Max. Recommended Pulling Tension:	230 lbs.	
Min. Bend Radius (Install)/Minor Axis:	3.750 in.	

Applicable Specifications and Agency Compliance (Overall)

Applicable	Standards &	& Environmental	Programs
------------	-------------	-----------------	----------

No
Yes
Yes
01/01/2004
Yes
Yes
Yes
Yes
No

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)

60

Nom. Inductance:

Inductance (µH/ft) .18

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft) 26.1

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/ft)

47.5

Nominal Velocity of Propagation:

VP (%) 66

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft) 25.5

Ind. Pair Nominal Shield DC Resistance @ 20 7.200 Ohm/1000 ft Deg. C:

Max. Operating Voltage - UL:

Voltage 300 V RMS

Max. Recommended Current:

Current

Detailed Specifications & Technical Data



ENGLISH MEASUREMENT VERSION

1908A Multi-Conductor - FleXnake® Super-Flexible, High-Performance Cable

1.05 Amps per conductor @ 25°C

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1908A B591000	1,000 FT	138.000 LB	BLACK, MATTE	С	8 #24 JKTD PR PVC
1908A B59250	250 FT	36.000 LB	BLACK, MATTE		8 #24 JKTD PR PVC
1908A B59500	500 FT	72.500 LB	BLACK, MATTE		8 #24 JKTD PR PVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 04-18-2008

© 2012 Belden, Inc All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this products are subject to belden's standard terms and conductors or safe. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.