

501PTZ Composite - For PTZ Cameras: CCTV + Control + Power



For more Information
please call

1-800-Belden1



Description:

(1) Coax - 20 AWG solid BC cond., gas-injected foam HDPE insul., 95% BC braid shield, PVC jkt, cabled with (1) pair - 22 AWG stranded (7x30) BC cond., PO insul., Beldfoil® shield, PVC jkt, cabled with (2) cond., 18 AWG (7x26) BC cond., PP insul., PVC Jkt

Coax

Physical Characteristics

Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (in.)
1	20	Solid	BC - Bare Copper	0.032

Insulation

Insulation Material:

Insulation Material	Dia. (in.)
Gas-injected FHDPE - Foam High Density Polyethylene	0.145

Inner Shield

Inner Shield Material:

Type	Inner Shield Material	% Coverage (%)
Braid	BC - Bare Copper	95

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Outer Jacket Diameter:

Nom. Dia. (in.)
0.227

Outer Jacket Color Code Chart:

Number	Color
Video	Black

Applicable Specifications and Agency Compliance

Applicable Standards & Environmental Programs

NEC/(UL) Specification: CMR

CEC/C(UL) Specification: CMG

EU CE Mark: Yes

RG Type: 59/U

Flame Test

UL Flame Test: UL1666 Vertical Shaft

Suitability

Suitability - Indoor: Yes

Electrical Characteristics

Nom. Characteristic Impedance:

Impedance (Ohm)

501PTZ Composite - For PTZ Cameras: CCTV + Control + Power

75

Nom. Inductance:

Inductance (µH/ft)
0.097

Nom. Capacitance Conductor to Shield:

Capacitance (pF/ft)
16.300

Nominal Velocity of Propagation:

VP (%)
83.000

Nominal Delay:

Delay (ns/ft)
1.220

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
10.000

Nom. Inner Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
3.500

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100 ft.)
1.000	0.300
5.000	0.650
10.000	0.900
50.000	1.900
100.000	2.600
200.000	3.600
400.000	5.000
700.000	7.000
900.000	8.000
1000.000	8.500

Max. Operating Voltage - UL: 300 V RMS

Twisted Pair

Physical Characteristics

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material	Dia. (in.)
1	22	7x30	BC - Bare Copper	0.030

Insulation

Insulation Material:

Insulation Material Dia. (in.)
PO - Polyolefin 0.062

Twisted Pair Color Code Chart:

Number	Color
1	Blue and White/Blue

Individual Shield

Outer Shield

Outer Shield Material:

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100.000

Outer Shield Drain Wire AWG:

AWG Stranding	Drain Wire Conductor Material

501PTZ Composite - For PTZ Cameras: CCTV + Control + Power

22	7x30	TC - Tinned Copper
----	------	--------------------

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Outer Jacket Diameter:

Nom. Dia. (in.)
0.177

Outer Jacket Color Code Chart:

Number	Color
1	Blue

Applicable Specifications and Agency Compliance Applicable Standards & Environmental Programs

NEC/(UL) Specification: CMR

CEC/(UL) Specification: CMG

Flame Test

UL Flame Test: UL1666 Vertical Shaft

Suitability

Suitability - Indoor: Yes

Electrical Characteristics

Nom. Capacitance Conductor to Shield:

Capacitance (pF/ft)
47.000

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)
24.000

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
16.000

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
12.000

Max. Operating Voltage - Other:

Voltage
300 V RMS

Max. Recommended Current:

Current
2.9 Amps per conductor @ 25°C

Multi Conductor

Physical Characteristics

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material	Dia. (in.)
2	18	7x26	BC - Bare Copper	0.047

Insulation

Insulation Material:

Insulation Material
PP - Polypropylene

Insulation Color Code Chart:

Number	Color
--------	-------

501PTZ Composite - For PTZ Cameras: CCTV + Control + Power

1	Red
2	Black

Individual Shield

Outer Jacket

Outer Jacket Diameter:

Nom. Dia. (in.)
0.158

Outer Jacket Color Code Chart:

Number	Color
1	White

Applicable Specifications and Agency Compliance

Applicable Standards & Environmental Programs

NEC/(UL) Specification: CMR

CEC/C(UL) Specification: CMG

Flame Test

UL Flame Test: UL1666 Vertical Shaft

Suitability

Suitability - Indoor: Yes

Electrical Characteristics

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)
21.500

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
6.500

Max. Operating Voltage - Other:

Voltage
300 V RMS

Max. Recommended Current:

Current
5 Amps per conductor @ 25°C

Physical Characteristics (Overall)

Conductor

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
Unjacketed

Overall Cable

Overall Nominal Diameter: 0.419 in.

Mechanical Characteristics (Overall)

Operating Temperature Range: -10°C To +75°C

Separation Temperature Range: 0°C To +75°C

Bulk Cable Weight: 60.000 lbs/1000 ft.

Max. Recommended Pulling Tension: 120.000 lbs.

Min. Bend Radius (Install)/Minor Axis: 4.200 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

EU Directive 2000/53/EC (ELV): Yes

501PTZ Composite - For PTZ Cameras: CCTV + Control + Power

EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	601PTZ

Notes (Overall)

Notes: RG59 CCTV + 1 STP22 AWG Control Grade + 2C 18 AWG CMR. Individually jacketed and color coded components, cabled around and each fused to a central binding spline. Cold environment installation: When installing cables that have been stored at ambient temperatures of 32 degrees Fahrenheit (0 degrees Centigrade) or lower, Belden recommends conditioning of the cable for 12 hours at room temperature prior to individual cable leg separation. Banana Peel® US PATENT 7049523.

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
501PTZ 0001000	1,000 FT	71.000 LB	NONE	C	1 RG59 + 1 STP 22 + 2C18

Notes:
C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 07-15-2008

© 2012 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.