

5020FZ Multi-Conductor - Circuit Integrity in a Conduit

For more Information
please call

1-800-Belden1

**Description:**

16 AWG solid bare copper conductors, ceramifiable silicone insulation, FRPE (low smoke non-halogen) jacket, sequential footage marking every two feet.

Usage (Overall)**Suitable Applications:**

Survivability, Survivability from Attach by Fire, Fire Alarm Circuit Integrity, CI, Survivability by NFPA72, Sim to MI, Similar to Mineral Insulated, FPLR-CI, Emergency Circuits, Notification Devices, Fire Pumps, 2 hour fire rating

Physical Characteristics (Overall)**Conductor****AWG:**

# Conductors	AWG	Stranding	Conductor Material
2	12	Solid	BC - Bare Copper

Insulation**Insulation Material:**

Insulation Material	Wall Thickness (in.)
Silicone Rubber	.035

Outer Shield**Outer Shield Material:**

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
14	7x22	TC - Tinned Copper

Outer Jacket**Outer Jacket Material:**

Outer Jacket Material	Nom. Wall Thickness (in.)
FRPE - Flame Retardant Polyethylene	.056

Overall Cable**Overall Cabling Color Code Chart:**

Number	Color
1	Black
2	Red

Overall Nominal Diameter: 0.420 in.

Mechanical Characteristics (Overall)

Operating Temperature Range: -20°C To +105°C

UL Temperature Rating: 105°C

Bulk Cable Weight: 108 lbs/1000 ft.

Max. Recommended Pulling Tension: 208 lbs.

Min. Bend Radius (Install)/Minor Axis: 4.200 in.

5020FZ Multi-Conductor - Circuit Integrity in a Conduit

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	FPLR, Electrical Circuit Protective Systems (FHIT #30)
NEC Articles:	760
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	11/14/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	UL1666 Riser, UL2196 Two Hour Circuit Integrity (in conduit only)
----------------	---

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)

27

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

1.6

Max. Operating Voltage - UL:

Voltage

300 V RMS

Notes (Overall)

Notes: UL 2196 (2 Hour Flame Rated) - Only when installed in conduit per FHIT #30 of the UL fire resistance directory.

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
5020FZ 0021000	1,000 FT	117.000 LB	RED		1 FS PR #12 SIL FRNHPO

Revision Number: 1 Revision Date: 06-04-2009

© 2012 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge,

5020FZ Multi-Conductor - Circuit Integrity in a Conduit

information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.