


1874A Multi-Conductor - Enhanced Category 6 Bonded-Pair Cable



For more Information
please call

1-800-Belden1

**Description:**

23 AWG Bonded-Pairs, Solid Bare Copper Conductor, Plenum, FEP Teflon Insulation, Rip Cord, Flamarrest(R) PVC Jacket.

Usage (Overall)**Suitable Applications:**

Premise Horizontal Cable, Gigabit Ethernet, 100BaseTX, 100BaseVG ANYLAN, 155ATM, 622ATM, NTSC/PAL Component or Composite Video, AES/EBU, Digital Video, RS-422, Noisy Environments

Physical Characteristics (Overall)**Conductor****AWG:**

# Pairs	AWG	Stranding	Conductor Material
4	23	Solid	BC - Bare Copper

Insulation**Insulation Material:**

Insulation Material
FEP - Fluorinated Ethylene Propylene

Outer Shield**Outer Shield Material:**

Outer Shield Material
Unshielded

Outer Jacket**Outer Jacket Material:**

Outer Jacket Trade Name	Outer Jacket Material
Flamarrest®	LS PVC - Low Smoke Polyvinyl Chloride

Outer Jacket Diameter:

Nom. Dia. (in.)
0.365
0.165

Outer Jacket Ripcord:

Yes

Overall Cable**Overall Nominal Diameter:**

0.365 x 0.165 in.

Pair**Pair Color Code Chart:**

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

Mechanical Characteristics (Overall)**Operating Temperature Range:**

-20°C To +80°C

Bulk Cable Weight:

31 lbs/1000 ft.

1874A Multi-Conductor - Enhanced Category 6 Bonded-Pair Cable

Max. Recommended Pulling Tension:	45 lbs.
--	---------

Min. Bend Radius (Install)/Minor Axis:	1 in.
---	-------

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

NEC/(UL) Specification:	CMP
--------------------------------	-----

CEC/C(UL) Specification:	CMP
---------------------------------	-----

Other Standards:	ISO/IEC 11801 ed 2.1 (2008) Class E
-------------------------	-------------------------------------

EU Directive 2000/53/EC (ELV):	Yes
---------------------------------------	-----

EU Directive 2002/95/EC (RoHS):	Yes
--	-----

EU RoHS Compliance Date (mm/dd/yyyy):	07/01/2006
--	------------

EU Directive 2002/96/EC (WEEE):	Yes
--	-----

EU Directive 2003/11/EC (BFR):	Yes
---------------------------------------	-----

CA Prop 65 (CJ for Wire & Cable):	Yes
--	-----

MII Order #39 (China RoHS):	Yes
------------------------------------	-----

Telecommunications Standards:	Category 6 - TIA 568.C.2
--------------------------------------	--------------------------

Other Specification:	UL Verified to Category 6
-----------------------------	---------------------------

Applicable Patents:

Country	Patent
US	5606151
US	5734126
US	5821467

Flame Test

UL Flame Test:	NFPA 262 Plenum Flame Test (UL910)(FT6)
-----------------------	---

CSA Flame Test:	FT6
------------------------	-----

Plenum/Non-Plenum

Plenum (Y/N):	Yes
----------------------	-----

Non-Plenum Number:	1872A
---------------------------	-------

Electrical Characteristics (Overall)**Nom. Mutual Capacitance:**

Capacitance (pF/ft)
15.0

Maximum Capacitance Unbalance (pF/100 m):	49
--	----

Nominal Velocity of Propagation:

VP (%)
72

Maximum Delay:

Delay (ns/100 m)
510 @ 100MHz

Max. Delay Skew:

Delay Skew (ns/100 m)
25

Maximum Conductor DC Resistance:

DCR @ 20°C (Ohm/100 m)
7.500

Max. Operating Voltage - UL:

Voltage
300 V RMS

1874A Multi-Conductor - Enhanced Category 6 Bonded-Pair Cable

Maximum DCR Unbalanced:

DCR Unbalance @ 20°C (%)

3

Electrical Characteristics-Premise (Overall)

Premise Cable Electrical Table 1:

Freq. (MHz)	Max. Attenuation (dB/100 m)	Min. NEXT (dB)	Min. PSNEXT (dB)	Min. ACR (dB)	Min. PSACR (dB)	Min RL (dB)
1	1.900	74.3	72.3	70	70	20.000
4	3.700	65.3	63.3	59	59	23.000
8	5.300	60.3	58.8	53	53	24.500
10	5.900	59.3	57.3	51	51	25.000
16	7.500	56.3	54.3	46	46	25.000
20	8.400	54.8	52.8	44	44	25.000
25	9.500	53.4	51.4	42	42	24.300
31.25	10.600	51.9	49.9	39	39	23.600
62.5	15.400	47.4	45.4	30	30	21.500
100	19.800	44.4	42.3	25	25	21.000
155	25.100	41.5	39.4	14	14	21.000
200	29.000	39.8	37.8	10	10	21.000
250	32.800	38.3	36.3	3	3	18.000
300	35.200	37.2	35.1	0	0	18.000
310	37.100	36.9	34.9			18.000
350	39.800	36.1	34.1			17.000
400**	43.000	35.3	33.3			14.000
500**	49.000	33.8	31.8			14.000

Premise Cable Electrical Table 2:

Freq. (MHz)	Input (Unfitted) Imp. (Ohms)	Fitted Impedance	Min. ELFEXT (dB)	Min. PSELFEXT (dB)
1	100 ± 12	100 ± 15	67.8	64.8
4	100 ± 12	100 ± 15	55.7	52.8
8	100 ± 12	100 ± 15	49.7	46.7
10	100 ± 12	100 ± 15	47.8	44.8
16	100 ± 12	100 ± 8	43.7	40.7
20	100 ± 12	100 ± 8	41.7	38.7
25	100 ± 15	100 ± 8	39.8	36.8
31.25	100 ± 15	100 ± 8	37.9	34.9
62.5	100 ± 15	100 ± 8	31.8	28.9
100	100 ± 15	100 ± 8	27.8	24.8
155	100 ± 15	100 ± 8	23.9	20.9
200	100 ± 15	100 ± 8	21.7	18.8
250	100 ± 20	100 ± 8	19.8	16.8
300	100 ± 20	100 ± 8	18.2	15.2
310	100 ± 20	100 ± 8	17.9	14.9
350	100 ± 22	100 ± 8	16.9	13.9
400**	100 ± 32	100 ± 8	15.7	12.7
500**	100 ± 32	100 ± 8	13.8	10.8

Notes (Overall)

Notes: Belden IBDN. Jacket sequentially marked at 2 ft. intervals. Values above 350 MHz are information only. Third party verified to ANSI/TIA-568-C.2 Category 6.

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1874A D15A1000	1,000 FT	39.000 LB	BLUE		CAT6+ 4PRB U/UTP CMP RIB
1874A F6HA1000	1,000 FT	39.000 LB	GRAY, DARK PEARL		CAT6+ 4PRB U/UTP CMP RIB
1874A F6H1000	1,000 FT	37.000 LB	GRAY, DARK PEARL	C	CAT6+ 4PRB U/UTP CMP REEL

1874A Multi-Conductor - Enhanced Category 6 Bonded-Pair Cable

1874A 002A1000	1,000 FT	39.000 LB	RED		CAT6+ 4PRB U/UTP CMP RIB
1874A 003A1000	1,000 FT	39.000 LB	ORANGE		CAT6+ 4PRB U/UTP CMP RIB
1874A 004A1000	1,000 FT	39.000 LB	YELLOW		CAT6+ 4PRB U/UTP CMP RIB
1874A 005A1000	1,000 FT	39.000 LB	GREEN, DARK		CAT6+ 4PRB U/UTP CMP RIB
1874A 007A1000	1,000 FT	39.000 LB	VIOLET		CAT6+ 4PRB U/UTP CMP RIB
1874A 0071000	1,000 FT	37.000 LB	VIOLET	C	CAT6+ 4PRB U/UTP CMP REEL
1874A 009A1000	1,000 FT	39.000 LB	WHITE		CAT6+ 4PRB U/UTP CMP RIB
1874A 0091000	1,000 FT	37.000 LB	WHITE	C	CAT6+ 4PRB U/UTP CMP REEL
1874A 0101000	1,000 FT	37.000 LB	BLACK	C	CAT6+ 4PRB U/UTP CMP REEL
1874A 877A1000	1,000 FT	39.000 LB	NATURAL		CAT6+ 4PRB U/UTP CMP RIB
1874A 8771000	1,000 FT	37.000 LB	NATURAL	C	CAT6+ 4PRB U/UTP CMP REEL

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 3 Revision Date: 05-03-2011

© 2012 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.