


For more Information  
please call

1-800-Belden1



### Description:

14 AWG bare copper conductors, PVC insulation, conductors cabled together, Beldfoil® shield and drain wire, PVC jacket with ripcord, sequential footage marking every two feet.

### Usage (Overall)

**Suitable Applications:** Fire Protection, Alarm, Signal, Monitor/Detection, Audio Circuits, Control Circuits, Initiating Circuits, Notification Circuits

### Physical Characteristics (Overall)

#### Conductor

**AWG:**

# Conductors	AWG	Stranding	Conductor Material
4	14	Solid	BC - Bare Copper

#### Insulation

**Insulation Material:**

Insulation Material	Wall Thickness (in.)
PVC - Polyvinyl Chloride	.013

#### Outer Shield

**Outer Shield Material:**

Outer Shield Trade Name	Outer Shield Material	Coverage (%)
Beldfoil®	Aluminum Foil-Polyester Tape	100

**Outer Shield Drain Wire AWG:**

AWG	Stranding	Drain Wire Conductor Material
20	7	TC - Tinned Copper

#### Outer Jacket

**Outer Jacket Material:**

Outer Jacket Material	Nom. Wall Thickness (in.)
PVC - Polyvinyl Chloride	.015

**Outer Jacket Ripcord:** Yes

#### Overall Cable

**Overall Cabling Lay Length & Direction:**

Length (in.)	Twists (ft.)
3.75	3.2

**Overall Cabling Color Code Chart:**

Number	Color
1	Black
2	Red
3	Brown
4	Blue

**Overall Nominal Diameter:** 0.255 in.

### Mechanical Characteristics (Overall)

**Operating Temperature Range:** -20°C To +75°C

**UL Temperature Rating:** 75°C

## 5122FL Multi-Conductor - Commercial Applications

<b>Bulk Cable Weight:</b>	71.500 lbs/1000 ft.
<b>Max. Recommended Pulling Tension:</b>	212.800 lbs.
<b>Min. Bend Radius (Install)/Minor Axis:</b>	2.500 in.

### Applicable Specifications and Agency Compliance (Overall)

#### Applicable Standards & Environmental Programs

<b>NEC/(UL) Specification:</b>	FPLR
<b>NEC Articles:</b>	760
<b>EU CE Mark:</b>	Yes
<b>EU Directive 2000/53/EC (ELV):</b>	Yes
<b>EU Directive 2002/95/EC (RoHS):</b>	Yes
<b>EU RoHS Compliance Date (mm/dd/yyyy):</b>	04/01/2005
<b>EU Directive 2002/96/EC (WEEE):</b>	Yes
<b>EU Directive 2003/11/EC (BFR):</b>	Yes
<b>CA Prop 65 (CJ for Wire &amp; Cable):</b>	Yes
<b>MII Order #39 (China RoHS):</b>	Yes
<b>Other Specification:</b>	California State Fire Marshall

#### Flame Test

<b>UL Flame Test:</b>	UL1666 Vertical Shaft
<b>CSA Flame Test:</b>	FT4

#### Plenum/Non-Plenum

<b>Plenum (Y/N):</b>	No
<b>Plenum Number:</b>	6122FL

### Electrical Characteristics (Overall)

#### Nom. Capacitance Conductor to Conductor:

<b>Capacitance (pF/ft)</b>
43

#### Nom. Capacitance Cond. to Other Conductor & Shield:

<b>Capacitance (pF/ft)</b>
77.4

#### Nom. Conductor DC Resistance:

<b>DCR @ 20°C (Ohm/1000 ft)</b>
2.43

#### Maximum Conductor DC Resistance:

<b>DCR @ 20°C (Ohm/100 m)</b>
6.9

#### Max. Operating Voltage - UL:

<b>Voltage</b>
300 V RMS

#### Max. Recommended Current:

<b>Current</b>
6.4 Amps per conductor @ 25°C

### Related Documents:

No related documents are available for this product

### Put Ups and Colors:

## 5122FL Multi-Conductor - Commercial Applications

Item #	Putup	Ship Weight	Color	Notes	Item Desc
5122FL 0021000	1,000 FT	66.000 LB	RED	C	4 #14 PP FS FRPVC

**Notes:**

C = CRATE REEL PUT-UP.

Revision Number: 2    Revision Date: 07-24-2009

© 2012 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.