
Detailed Specifications & Technical Data



ENGLISH MEASUREMENT VERSION

5200FE Multi-Conductor - Commercial Audio Systems - 2 Conductors Cabled



For more Information please call

1-800-Belden1



Description: 16 AWG bare copper conductors, PP insulation, conductors cabled, Beldfoil® shield tape (foil side out) with drain wire, PVC jacket with ripcord, sequential footage marking every two feet **Usage (Overall)** Suitable Applications: Intercom/PA Systems, Sound/Audio Systems **Physical Characteristics (Overall)** Conductor AWG: # Conductors AWG Stranding Conductor Material 2 16 19x29 BC - Bare Copper Insulation **Insulation Material:** Insulation Material Wall Thickness (in.) PP - Polypropylene 0.007 **Outer Shield Outer Shield Material:** Outer Shield Trade Name Type Outer Shield Material Coverage (%) Beldfoil® Tape Aluminum Foil-Polyester Tape w/Shorting Fold 100 **Outer Shield Drain Wire AWG:** AWG Stranding Drain Wire Conductor Material 24 7x32 TC - Tinned Copper **Outer Jacket Outer Jacket Material:** Nom. Wall Thickness (in.) Outer Jacket Material PVC - Polyvinyl Chloride 0.017 **Outer Jacket Ripcord:** Yes **Overall Cable Overall Cabling Lay Length & Direction:** Length (in.) Twists (ft.) 3 4 **Overall Cabling Color Code Chart:** Number Color Black 1 2 Red **Overall Nominal Diameter:** 0.180 in. **Mechanical Characteristics (Overall) Operating Temperature Range:** -20°C To +75°C 75°C **UL Temperature Rating: Bulk Cable Weight:** 30.100 lbs/1000 ft. Max. Recommended Pulling Tension: 85.500 lbs.

Detailed Specifications & Technical Data



ENGLISH MEASUREMENT VERSION

5200FE Multi-Conductor - Commercial Audio Systems - 2 Conductors Cabled

Min. Bend Radius (Install)/Minor Axis:	1.800 in.			
Applicable Specifications and Agency C	ompliance (Overall)			
Applicable Standards & Environmental Prog	-			
NEC/(UL) Specification:	CMR			
NEC Articles:	800			
CEC/C(UL) Specification:	CMG			
EU CE Mark:	Yes			
EU Directive 2000/53/EC (ELV):	Yes			
EU Directive 2002/95/EC (RoHS):	Yes			
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005			
EU Directive 2002/96/EC (WEEE):	Yes			
EU Directive 2003/11/EC (BFR):	Yes			
CA Prop 65 (CJ for Wire & Cable):	Yes			
MII Order #39 (China RoHS):	Yes			
Flame Test				
UL Flame Test:	UL1666 Vertical Shaft			
C(UL) Flame Test:	FT4			
Plenum/Non-Plenum				
Plenum Number:	6200FE			
Surface Printing (Overall)				
Electrical Characteristics (Overall)				
Nom. Inductance:				
Inductance (μH/ft) 0.140				
Nom. Capacitance Conductor to Conductor: Capacitance (pF/ft) 63.250				
Nom. Capacitance Cond. to Other Conductor & SI Capacitance (pF/ft) 114.000	nield:			
Nom. Conductor DC Resistance: DCR @ 20°C (Ohm/1000 ft) 4.0				
Nominal Outer Shield DC Resistance: DCR @ 20°C (Ohm/1000 ft) 14.400				
Max. Operating Voltage - UL: Voltage 300 V RMS				
Max. Recommended Current: Current 6.25 Amps per conductor @ 25°C				
Related Documents:				
No related documents are available for this product				

Put Ups and Colors:

Detailed Specifications & Technical Data



ENGLISH MEASUREMENT VERSION

5200FE Multi-Conductor - Commercial Audio Systems - 2 Conductors Cabled

Item #	Putup	Ship Weight	Color	Notes	Item Desc
5200FE 008U1000	1,000 FT	31.000 LB	GRAY		2 #16 PP FS FRPVC
5200FE 008U500	500 FT	13.500 LB	GRAY		2 #16 PP FS FRPVC
5200FE 0081000	1,000 FT	26.000 LB	GRAY	С	2 #16 PP FS FRPVC
5200FE 008500	500 FT	13.500 LB	GRAY	С	2 #16 PP FS FRPVC
5200FE 009U1000	1,000 FT	31.000 LB	WHITE		2 #16 PP FS FRPVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 2 Revision Date: 06-02-2008

© 2012 Belden, Inc All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.