Detailed Specifications & Technical Data

ENGLISH MEASUREMENT VERSION



5240F1 Multi-Conductor - Water Resistant

For more Information please call

1-800-Belden1



Description:

16 AWG stranded (7x24) tinned copper conductors, PVC insulation, Beldfoil® shield (100% coverage), drain wire, water-blocking tape, PVC jacket.

Usage (Overall)

Suitable Applications: Low Voltage, Direct Burial, PLTC, FPL, Intercom, Sound, Audio

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material
1	16	7x24	TC - Tinned Copper

Insulation

Insulation Material:

Insulation Material	Wall Thickness (in.)
PVC - Polyvinyl Chloride	.010

Outer Shield

Outer Shield Material:

Outer Shield Trade Name		Type	Outer Shield Material	Coverage (%)
	Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100

Outer Shield Drain Wire AWG:

AWG Stranding		Drain Wire Conductor Material		
18	7x26	TC - Tinned Copper		

Outer Shield Waterblocking Tape: Yes

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (in.)
PVC - Polyvinyl Chloride	.037

Overall Cable

Overall Nominal Diameter: 0.254 in.

Pair

Pair Color Code Chart:

Number	Color
1	Black & Red

Mechanical Characteristics (Overall)

Operating Temperature Range:	-30°C To +105°C		
UL Temperature Rating:	105°C		
Bulk Cable Weight:	38 lbs/1000 ft.		
Max. Recommended Pulling Tension:	93 lbs.		
Min. Bend Radius (Install)/Minor Axis:	2.750 in.		

Page 1 of 3 01-06-2012

Detailed Specifications & Technical Data

ENGLISH MEASUREMENT VERSION



5240F1 Multi-Conductor - Water Resistant

Applicable Specifications and Agency Compliance (Overall)					
Applicable Standards & Environmental Programs					
NEC/(UL) Specification:	CMG, FPL, PLTC				
CEC/C(UL) Specification:	CMG				
EU CE Mark:	Yes				
EU Directive 2000/53/EC (ELV):	Yes				
EU Directive 2002/95/EC (RoHS):	Yes				
EU RoHS Compliance Date (mm/dd/yyyy):	11/08/2006				
EU Directive 2002/96/EC (WEEE):	Yes				
EU Directive 2003/11/EC (BFR):	Yes				
CA Prop 65 (CJ for Wire & Cable):	Yes				
MII Order #39 (China RoHS):	Yes				
Other Specification:	PLTC-ER				
Flame Test					
UL Flame Test:	UL1685 FT4/IEEE 1202 Vertical Tray Flame Test				
C(UL) Flame Test:	FT4				
Other Flame Test:	IEEE 1202				
Suitability					
Suitability - Indoor:	Yes				
Suitability - Outdoor:	Yes				
Sunlight Resistance:	Yes				
Plenum/Non-Plenum					
Plenum (Y/N):	No				

Electrical Characteristics (Overall)

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft) 76.000

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft) 4.4

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft) 5.4

Max. Operating Voltage - UL:

Voltage 300 V RMS

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
5240F1 0021000	1,000 FT	42.000 LB	RED	С	1 FS PR #16 PVC PVC
5240F1 0101000	1,000 FT	42.000 LB	BLACK	С	1 FS PR #16 PVC PVC

Notes:

C = CRATE REEL PUT-UP.

Page 2 of 3 01-06-2012

Detailed Specifications & Technical Data

ENGLISH MEASUREMENT VERSION



5240F1 Multi-Conductor - Water Resistant

Revision Number: 1 Revision Date: 01-07-2011

© 2012 Belden, Inc All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.