

5302F1 Multi-Conductor - Water-Blocked for Use in Underground Ducts



For more Information
please call

1-800-Belden1

**Description:**

18 AWG stranded (7x26) tinned copper conductors, PVC insulation, water-blocking tape, overall aluminum foil-polyester tape shield (100% coverage), drain wire, overall PVC jacket.

Usage (Overall)

Suitable Applications: Low Voltage, Direct Burial, PLTC-ER, FPL, Intercom, Sound, Audio

Physical Characteristics (Overall)**Conductor****AWG:**

# Conductors	AWG	Stranding	Conductor Material
4	18	7x26	TC - Tinned Copper

Insulation**Insulation Material:**

Insulation Material
PVC - Polyvinyl Chloride

Outer Shield**Outer Shield Material:**

Outer Shield Material	Coverage (%)
Aluminum Foil-Polyester Tape	100

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
20	Stranded	TC - Tinned Copper

Outer Jacket**Outer Jacket Material:**

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cable**Overall Cabling Color Code Chart:**

Number	Color
1	Black
2	White
3	Red
4	Green

Overall Cabling Separator Material: Waterblocking Tape

Overall Nominal Diameter: 0.259 in.

Mechanical Characteristics (Overall)

Operating Temperature Range: -30°C To +105°C

UL Temperature Rating: 105°C

Bulk Cable Weight: 44 lbs/1000 ft.

Max. Recommended Pulling Tension: 102 lbs.

Min. Bend Radius (Install)/Minor Axis: 2.750 in.

5302F1 Multi-Conductor - Water-Blocked for Use in Underground Ducts

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMG, FPL, PLTC, PLTC-ER
-------------------------	-------------------------

CEC/C(UL) Specification:	CMG
--------------------------	-----

EU CE Mark:	Yes
-------------	-----

EU Directive 2000/53/EC (ELV):	Yes
--------------------------------	-----

EU Directive 2002/95/EC (RoHS):	Yes
---------------------------------	-----

EU RoHS Compliance Date (mm/dd/yyyy):	11/06/2006
---------------------------------------	------------

EU Directive 2002/96/EC (WEEE):	Yes
---------------------------------	-----

EU Directive 2003/11/EC (BFR):	Yes
--------------------------------	-----

CA Prop 65 (CJ for Wire & Cable):	Yes
-----------------------------------	-----

MII Order #39 (China RoHS):	Yes
-----------------------------	-----

Flame Test

UL Flame Test:	UL1685 FT4/IEEE 1202 Vertical Tray Flame Test
----------------	---

CSA Flame Test:	FT4
-----------------	-----

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Suitability - Outdoor:	Yes
------------------------	-----

Suitability - Burial:	Yes
-----------------------	-----

Sunlight Resistance:	Yes
----------------------	-----

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)

40

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

6.6

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

7.7

Max. Operating Voltage - UL:

Voltage

300 V RMS

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
5302F1 0021000	1,000 FT	48.000 LB	RED	C	4 #18 PVC FS PVC
5302F1 0101000	1,000 FT	48.000 LB	BLACK	C	4 #18 PVC FS PVC

Notes:

C = CRATE REEL PUT-UP.

5302F1 Multi-Conductor - Water-Blocked for Use in Underground Ducts

Revision Number: 2 Revision Date: 01-07-2011

© 2012 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.