


5399X5 Composite - Surveillance and CCTV Applications

For more Information
please call

1-800-Belden1



Description:

Coax: 18 AWG solid bare copper conductor, foam polyolefin insulation, bare copper braid shield (95% coverage), water resistant tape; Pair: 16 AWG stranded bare copper conductors, PVC insulation, water resistant tape; overall PVC jacket

Coax

Physical Characteristics

Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (in.)
1	18	Solid	BC - Bare Copper	0.040

Insulation

Insulation Material:

Insulation Material	Dia. (in.)
FPE - Foam Polyethylene	0.180

Separator

Outer Jacket Separator Material: Water resistant tape (over braid, under jacket)

Inner Shield

Inner Shield Material:

Type	Inner Shield Material	% Coverage (%)
Braid	BC - Bare Copper	95

Overall Diameter

Overall Nominal Diameter: 0.279 in.

Applicable Specifications and Agency Compliance Applicable Standards & Environmental Programs

EU CE Mark: Yes

RG Type: 6/U

Electrical Characteristics

Nom. Characteristic Impedance:

Impedance (Ohm)
75

Nom. Inductance:

Inductance (µH/ft)
0.097

Nom. Capacitance Conductor to Shield:

Capacitance (pF/ft)
16.300

Nominal Velocity of Propagation:

VP (%)
83.000

Nominal Delay:

Delay (ns/ft)
1.220

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
6.400

Nom. Inner Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
3.100

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100 ft.)
1.000	0.200
5.000	0.450
10.000	0.640
50.000	1.460
100.000	2.100
200.000	3.000
400.000	4.300
700.000	5.800
900.000	6.700
1000.000	7.100

Max. Operating Voltage - UL: 350 V RMS

Twisted Pair

Physical Characteristics

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material	Dia. (in.)
1	16	19	BC - Bare Copper	0.057

Insulation

Insulation Material:

Insulation Material	Dia. (in.)
PVC - Polyvinyl Chloride	0.077

Twisted Pair Color Code Chart:

Number	Color
1	Black and Red

Separator

Separator Material: Water resistant tape (over pair, under jacket)

Overall Diameter

Overall Nominal Diameter: 0.235 in.

Electrical Characteristics

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)
24.000

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
4.000

Physical Characteristics (Overall)

Conductor

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Material

PVC - Polyvinyl Chloride

Overall Cable

Overall Nominal Diameter: 0.279 in.

Mechanical Characteristics (Overall)

Operating Temperature Range: -30°C To +80°C

Non-UL Temperature Rating: 75°C

Bulk Cable Weight: 68.000 lbs/1000 ft.

Max. Recommended Pulling Tension: 114.000 lbs.

Min. Bend Radius (Install)/Minor Axis: 2.750 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: CM

NEC Articles: 800

CEC/C(UL) Specification: CM

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 04/24/2006

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

Other Specification: NEC Article 800

Flame Test

UL Flame Test: UL1685 UL Loading

C(UL) Flame Test: FT1

Suitability

Suitability - Indoor: Yes

Suitability - Outdoor: Yes

Sunlight Resistance: Yes

Plenum/Non-Plenum

Plenum (Y/N): No

Electrical Characteristics (Overall)

Max. Operating Voltage - UL:

Voltage

300 V RMS

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
5399X5 0101000	1,000 FT	69.000 LB	BLACK		1 #16 PR, 1 RG-6/U COAX

5399X5 Composite - Surveillance and CCTV Applications

Revision Number: 2 Revision Date: 01-07-2011

© 2012 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.