

5400F1 Multi-Conductor - Water-Blocked for Use in Underground Ducts - 2 Cond Cabled



For more Information
please call

1-800-Belden1



Description:

20 AWG tinned copper conductors, PVC insulation, cabled with overall water-blocking tape, PVC jacket with ripcord. Sequential footage marking every two feet.

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
2	20	7x28	TC - Tinned Copper

Insulation

Insulation Material:

Insulation Material	Wall Thickness (in.)
PVC - Polyvinyl Chloride	.010

Outer Shield

Outer Shield Material:

Outer Shield Trade Name	Outer Shield Material
Beldfoil®	Aluminum Foil-Polyester Tape

Outer Shield Drain Wire AWG:

Drain Wire Conductor Material
TC - Tinned Copper

Outer Shield Waterblocking Tape: Non-woven waterblocking tape

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (in.)
PVC - Polyvinyl Chloride	.025

Outer Jacket Ripcord: Yes

Overall Cable

Overall Cabling Lay Length & Direction:

Length (in.)
2

Overall Nominal Diameter: 0.206 in.

Mechanical Characteristics (Overall)

Operating Temperature Range: -20°C To +105°C

Bulk Cable Weight: 20.200 lbs/1000 ft.

Max. Recommended Pulling Tension: 37.100 lbs.

Min. Bend Radius (Install)/Minor Axis: 2 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: CM

CEC/C(UL) Specification: CM

5400F1 Multi-Conductor - Water-Blocked for Use in Underground Ducts - 2 Cond Cabled

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 10/01/2005

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

Flame Test

UL Flame Test: UL1685 UL Loading

CSA Flame Test: FT1

Plenum/Non-Plenum

Plenum (Y/N): No

Electrical Characteristics (Overall)

Nom. Inductance:

Inductance (µH/ft)

.17

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)

56

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/ft)

101

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

10.3

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

11.7

Max. Operating Voltage - UL:

Voltage

300 V RMS

Max. Recommended Current:

Current

3.75 Amps per conductor @ 25°C (10°C rise in temp)

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
5400F1 0081000	1,000 FT	22.000 LB	GRAY	C	2 #20 S-R PVC FS PVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 01-07-2011

© 2012 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications

5400F1 Multi-Conductor - Water-Blocked for Use in Underground Ducts - 2 Cond Cabled

described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.