Detailed Specifications & Technical Data

ENGLISH MEASUREMENT VERSION



5543FE Multi-Conductor - Commercial Applications



For more Information please call

1-800-Belden1



Description:

22 AWG bare copper conductors, PVC insulation, conductors twisted into pairs, multiple pairs cabled together, overall Beldfoil® shield (foil side out) and drain wire, overall PVC jacket with rip cord. Sequential footage marking every two feet.

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material
4	22	7x30	BC - Bare Copper

Insulation

Insulation Material:

Insulation Material	Wall Thickness (in.)
PVC - Polyvinyl Chloride	.010

Outer Shield

Outer Shield Material:

Outer Shield Trade Name	Outer Shield Material		
Beldfoil®	Aluminum Foil-Polyester Tape		

Outer Shield Drain Wire AWG:

AWG	Drain Wire Conductor Material
24	TC - Tinned Copper

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (in.)
PVC - Polyvinyl Chloride	.015

Overall Cable

Overall Nominal Diameter: 0.246 in.

Pair

Pair Color Code Chart:

Number	Color
1	Black & Red
2	Black & White
3	Black & Green
4	Black & Blue

Mechanical Characteristics (Overall)

Operating Temperature Range:	-20°C To +75°C
Bulk Cable Weight:	31.800 lbs/1000 ft.
Max. Recommended Pulling Tension:	78.300 lbs.
Min. Bend Radius (Install)/Minor Axis:	2.500 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

Page 1 of 3 01-06-2012

Detailed Specifications & Technical Data





5543FE Multi-Conductor - Commercial Applications

NEC	C/(UL) Specification:	CMR
CEC	C/C(UL) Specification:	CMG
EU (CE Mark:	Yes
EU I	Directive 2000/53/EC (ELV):	Yes
EU I	Directive 2002/95/EC (RoHS):	Yes
EU I	RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU I	Directive 2002/96/EC (WEEE):	Yes
EU I	Directive 2003/11/EC (BFR):	Yes
CA	Prop 65 (CJ for Wire & Cable):	Yes
MILO	Order #39 (China RoHS):	Yes
Flame 1	Test	
UL F	Flame Test:	UL1666 Vertical Shaft
CSA	A Flame Test:	FT4
Plenum/Non-Plenum		
Pler	num (Y/N):	No
Pler	num Number:	6543FE

Surface Printing (Overall)

Electrical Characteristics (Overall)

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)
31

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/ft) 55.8

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft) 16.3

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft) 13.9

Max. Operating Voltage - UL:

Voltage 300 V RMS

Max. Recommended Current:

Current
2 Amps per conductor @ 25°C

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
5543FE 0081000	1,000 FT	34.000 LB	GRAY	С	4 PR #22 PVC FS FRPVC

Notes:

C = CRATE REEL PUT-UP.

Page 2 of 3 01-06-2012

Detailed Specifications & Technical Data

ENGLISH MEASUREMENT VERSION



5543FE Multi-Conductor - Commercial Applications

Revision Number: 1 Revision Date: 05-14-2007

© 2012 Belden, Inc All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.