Detailed Specifications & Technical Data

ENGLISH MEASUREMENT VERSION



5584G1 Multi-Conductor - Water-Blocked for Indoor/Outdoor Use



For more Information please call

1-800-Belden1



Description:

22 AWG solid tinned copper conductors, PVC insulation, 1 pair with Beldfoil® shield and drain wire, inner waterblocking tape cabled with 2 unshielded pairs, overall waterblocking tape, overall PVC jacket.

Usage (Overall)

Suitable Applications: Low Voltage, Water Resistant, Water Block, Direct Burial, Moisture Resistant,

CM, A30 Intercom, Sound, Audio, Indoor/Outdoor

Physical Characteristics (Overall)

Conductor

AWG:

	AWG	Stranding	Conductor Material
3	22	Solid	TC - Tinned Copper

Insulation

Insulation Material:

Insulation Material	Wall Thickness (in.)
PVC - Polyvinyl Chloride	.010

Inner Shield

Inner Shield Material:

Inner Shield Trade Name	Type	Inner Shield Material	Coverage (%)	Stranding	Conductor Material	Description
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100	Solid	TC - Tinned Copper	Blk/Red Pair
Waterblocking Tape	Tape	Non-woven	100			Blk/Red Pair
		Unshielded				Blk/White Pair
		Unshielded				Blk/Green Pair

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (in.)
PVC - Polyvinyl Chloride	.025

Overall Cable

Overall Cabling Separator Material: Waterblocking Tape

Overall Nominal Diameter: 0.283 in.

Pair

Pair Color Code Chart:

Number	Color
1	Black & Red
2	Black & White
3	Black & Green

Mechanical Characteristics (Overall)

Operating Temperature Range:	-20°C To +105°C	
Bulk Cable Weight:	31.700 lbs/1000 ft.	
Max. Recommended Pulling Tension:	54 lbs.	
Min. Bend Radius (Install)/Minor Axis:	3 in.	

Page 1 of 3 01-06-2012

Detailed Specifications & Technical Data





5584G1 Multi-Conductor - Water-Blocked for Indoor/Outdoor Use

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CM
CEC/C(UL) Specification:	CM
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	07/18/2006
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test: UL1581 Vertical Tray

Plenum/Non-Plenum

Plenum (Y/N): No

Electrical Characteristics (Overall)

Nom. Capacitance Conductor to Conductor:

Description	Freq. (MHz)	Capacitance (pF/ft)
Blk/Red Pair	1	33
Other Pairs	1	18

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/ft) 88.600

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft) 15.7

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft) 11.3

Max. Operating Voltage - UL:

Voltage 300 V RMS

Max. Recommended Current:

Current
3.2 Amps per conductor @ 25°C

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
5584G1 0081000	1,000 FT	35.000 LB	GRAY	С	1 FS PR, 2 PR #22 PVC PVC
5584G1 0101000	1,000 FT	36.000 LB	BLACK		1 FS PR, 2 PR #22 PVC PVC

Notes:

C = CRATE REEL PUT-UP.

Page 2 of 3 01-06-2012

Detailed Specifications & Technical Data

ENGLISH MEASUREMENT VERSION



5584G1 Multi-Conductor - Water-Blocked for Indoor/Outdoor Use

Revision Number: 0 Revision Date: 01-07-2011

© 2012 Belden, Inc All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.