

6320UL Multi-Conductor - Commercial Applications - 2 Conductors Cabled

For more Information
please call

1-800-Belden1



Description:

18 AWG bare copper conductors, Flamarrest® insulation, cabled together, Flamarrest® jacket with ripcord, shielded version has overall Beldfoil® shield tape (foil side out) and drain wire, sequential footage marking every two feet.

Usage (Overall)

Suitable Applications: Fire Protection, Alarm, Signal, Monitor/Detection, Audio Circuits, Control Circuits, Initiating Circuits, Notification Circuits

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
2	18	Solid	BC - Bare Copper

Insulation

Insulation Material:

Insulation Trade Name	Insulation Material	Wall Thickness (in.)
Flamarrest®	LS PVC - Low Smoke Polyvinyl Chloride	0.008

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Trade Name	Outer Jacket Material	Nom. Wall Thickness (in.)
Flamarrest®	LS PVC - Low Smoke Polyvinyl Chloride	.015

Outer Jacket Ripcord: Yes

Overall Cable

Overall Cabling Lay Length & Direction:

Length (in.)	Twists (ft.)
2.75	4.4

Overall Cabling Color Code Chart:

Number	Color
1	Black
2	Red

Overall Nominal Diameter: 0.144 in.

Mechanical Characteristics (Overall)

Operating Temperature Range: 0°C To +75°C

UL Temperature Rating: 75°C

Bulk Cable Weight: 16 lbs/1000 ft.

Max. Recommended Pulling Tension: 39.200 lbs.

Min. Bend Radius (Install)/Minor Axis: 1.500 in.

6320UL Multi-Conductor - Commercial Applications - 2 Conductors Cabled

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: FPLP

NEC Articles: 760

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 04/01/2005

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

Other Specification: California State Fire Marshall

Flame Test

UL Flame Test: NFPA 262

Plenum/Non-Plenum

Plenum (Y/N): Yes

Non-Plenum Number: 5320UL

Electrical Characteristics (Overall)

Nom. Inductance:

Inductance (µH/ft)

0.150

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)

31.000

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

6.4

Max. Operating Voltage - UL:

Voltage

300 V RMS

Max. Recommended Current:

Current

5 Amps per conductor @ 25°C

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
6320UL D15C500	500 FT	7.500 LB	BLUE		2 #18 FLRST FLRST
6320UL 002U1000	1,000 FT	18.000 LB	RED		2 #18 FLRST FLRST
6320UL 002U500	500 FT	9.000 LB	RED		2 #18 FLRST FLRST
6320UL 0021000	1,000 FT	17.000 LB	RED	C	2 #18 FLRST FLRST
6320UL 003U1000	1,000 FT	17.000 LB	ORANGE		2 #18 FLRST FLRST
6320UL 0031000	1,000 FT	17.000 LB	ORANGE		2 #18 FLRST FLRST
6320UL 004U1000	1,000 FT	17.000 LB	YELLOW		2 #18 FLRST FLRST
6320UL 005U1000	1,000 FT	17.000 LB	GREEN, DARK		2 #18 FLRST FLRST

6320UL Multi-Conductor - Commercial Applications - 2 Conductors Cabled

6320UL 0051000	1,000 FT	17.000 LB	GREEN, DARK		2 #18 FLRST FLRST
6320UL 007C500	500 FT	7.500 LB	VIOLET		2 #18 FLRST FLRST
6320UL 007U1000	1,000 FT	17.000 LB	VIOLET		2 #18 FLRST FLRST
6320UL 009C500	500 FT	7.500 LB	WHITE		2 #18 FLRST FLRST
6320UL 009U1000	1,000 FT	17.000 LB	WHITE		2 #18 FLRST FLRST
6320UL 010C500	500 FT	7.500 LB	BLACK		2 #18 FLRST FLRST
6320UL 010U1000	1,000 FT	17.000 LB	BLACK		2 #18 FLRST FLRST
6320UL 0101000	1,000 FT	17.000 LB	BLACK		2 #18 FLRST FLRST
6320UL 012U1000	1,000 FT	17.000 LB	PINK		2 #18 FLRST FLRST

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 2 Revision Date: 06-25-2008

© 2012 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.