

6304UE Multi-Conductor - Commercial Applications



For more Information
please call

1-800-Belden1



Description:

18 AWG bare copper conductors, Flamarrest® insulation, conductors cabled, Flamarrest® jacket, ripcord. Sequential footage marking every two feet.

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
6	18	7	BC - Bare Copper

Insulation

Insulation Material:

Insulation Trade Name	Insulation Material	Wall Thickness (in.)
Flamarrest®	LS PVC - Low Smoke Polyvinyl Chloride	0.008

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Trade Name	Nom. Wall Thickness (in.)
Flamarrest®	.015

Outer Jacket Ripcord: Yes

Overall Cable

Overall Cabling Lay Length & Direction:

Length (in.)
3.75

Overall Cabling Color Code Chart:

Color
Black
Red
White
Green
Brown
Blue

Overall Nominal Diameter: 0.216 in.

Mechanical Characteristics (Overall)

Operating Temperature Range: 0°C To +75°C

Bulk Cable Weight: 43.300 lbs/1000 ft.

Max. Recommended Pulling Tension: 134.400 lbs.

Min. Bend Radius (Install)/Minor Axis: 2.250 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMP
CEC/C(UL) Specification:	CMP
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	NFPA 262
CSA Flame Test:	FT6

Plenum/Non-Plenum

Plenum (Y/N):	Yes
Non-Plenum Number:	5304UE

Electrical Characteristics (Overall)

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)

34.000

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

6.5

Max. Operating Voltage - UL:

Voltage

300 V RMS

Max. Recommended Current:

Current

3.5 Amps per conductor @ 25°C

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
6304UE 877U500	500 FT	23.500 LB	NATURAL		6 #18 Flrst first
6304UE 8771000	1,000 FT	45.000 LB	NATURAL	C	6 #18 FLRST FLRST
6304UE 877500	500 FT	23.000 LB	NATURAL		6 #18 FLRST FLRST

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 2 Revision Date: 06-02-2008

© 2012 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not

6304UE Multi-Conductor - Commercial Applications

ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.