

6626UG Multi-Conductor - Commercial Sound

For more Information
please call

1-800-Belden1

**Description:**

24 AWG solid bare copper conductors, FEP insulation, Flamarrest® jacket.

Usage (Overall)

Suitable Applications: Nurse Call, Commercial Sound, Annunciators, Voice Systems, Paging

Physical Characteristics (Overall)**Conductor****AWG:**

# Conductors	AWG	Stranding	Conductor Material
8	24	Solid	BC - Bare Copper

Insulation**Insulation Material:**

Insulation Material	Wall Thickness (in.)	Dia. (in.)
FEP - Fluorinated Ethylene Propylene	.007	.034

Outer Jacket**Outer Jacket Material:**

Outer Jacket Trade Name	Outer Jacket Material	Nom. Wall Thickness (in.)
Flamarrest®	LS PVC - Low Smoke Polyvinyl Chloride	.019

Overall Cable

Overall Nominal Diameter: 0.072 x 0.310 in.

Mechanical Characteristics (Overall)

Operating Temperature Range: -20°C To +75°C

Bulk Cable Weight: 24 lbs/1000 ft.

Max. Recommended Pulling Tension: 40 lbs.

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

NEC/(UL) Specification: CMP

NEC Articles: 800

CEC/C(UL) Specification: CMP

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 04/01/2005

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

6626UG Multi-Conductor - Commercial Sound**Flame Test**

UL Flame Test:	UL910 Steiner Tunnel
-----------------------	----------------------

C(UL) Flame Test:	FT6
--------------------------	-----

Plenum/Non-Plenum

Plenum (Y/N):	Yes
----------------------	-----

Non-Plenum Number:	5626UG
---------------------------	--------

Electrical Characteristics (Overall)**Nom. Capacitance Conductor to Conductor:**

Capacitance (pF/ft)

15

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

25.4

Max. Operating Voltage - UL:

Voltage

300 V RMS

Max. Recommended Current:

Current

1.4 Amps per conductor @ 25°C (10°C rise in temp)

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
6626UG F6H1000	1,000 FT	26.000 LB	GRAY, DARK PEARL	C	8 #24 FEP FLRST

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 05-14-2007

© 2012 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.