

## 6308UE Multi-Conductor - Commercial Applications



For more Information  
please call

1-800-Belden1

**Description:**

18 AWG bare copper conductors, Flamarrest® insulation, conductors cabled, Flamarrest® jacket, ripcord.  
Sequential footage marking every two feet.

**Physical Characteristics (Overall)****Conductor****AWG:**

# Conductors	AWG	Stranding	Conductor Material
10	18	7	BC - Bare Copper

**Insulation****Insulation Material:**

Insulation Trade Name	Insulation Material	Wall Thickness (in.)
Flamarrest®	LS PVC - Low Smoke Polyvinyl Chloride	0.008

**Outer Shield****Outer Shield Material:**

Outer Shield Material
Unshielded

**Outer Jacket****Outer Jacket Material:**

Outer Jacket Trade Name	Outer Jacket Material	Nom. Wall Thickness (in.)
Flamarrest®	LS PVC - Low Smoke Polyvinyl Chloride	.015

Outer Jacket Ripcord: Yes

**Overall Cable****Overall Cabling Lay Length & Direction:**

Length (in.)
5

**Overall Cabling Color Code Chart:**

Color
Black
Red
White
Green
Brown
Blue
Orange
Yellow
Purple
Gray

Overall Nominal Diameter: 0.278 in.

**Mechanical Characteristics (Overall)**

Operating Temperature Range: 0°C To +75°C

Bulk Cable Weight: 71.200 lbs/1000 ft.

Max. Recommended Pulling Tension: 224 lbs.

## 6308UE Multi-Conductor - Commercial Applications

Min. Bend Radius (Install)/Minor Axis:	2.750 in.
--	-----------

## Applicable Specifications and Agency Compliance (Overall)

## Applicable Standards &amp; Environmental Programs

NEC/(UL) Specification:	CMP
CEC/C(UL) Specification:	CMP
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

## Flame Test

UL Flame Test:	NFPA 262
CSA Flame Test:	FT6

## Plenum/Non-Plenum

Plenum (Y/N):	Yes
Non-Plenum Number:	5308UE

## Electrical Characteristics (Overall)

## Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)
32.500

## Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
6.5

## Max. Operating Voltage - UL:

Voltage
300 V RMS

## Max. Recommended Current:

Current
3.5 Amps per conductor @ 25°C

## Related Documents:

No related documents are available for this product

## Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
6308UE 8771000	1,000 FT	75.000 LB	NATURAL	C	10 #18 FLRST FLRST

## Notes:

C = CRATE REEL PUT-UP.

Revision Number: 2    Revision Date: 07-01-2008

© 2012 Belden, Inc.  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

## 6308UE Multi-Conductor - Commercial Applications

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.