


734C6 Coax - 734C Series

For more Information
please call

1-800-Belden1

**Description:**

20 AWG solid .032" silver-plated copper conductors, gas-injected FHDPE insulation, Duobond® + tinned copper braid shield (85% coverage), inner PVC jacket, overall PVC jacket with ripcord.

Usage (Overall)

Suitable Applications: Central Office wiring for DS3 transmissions.

Physical Characteristics (Overall)**Conductor**

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (in.)
6	20	Solid	SPC - Silver Plated Copper	0.032

Insulation

Insulation Material:

Insulation Material	Dia. (in.)
Gas-injected FHDPE - Foam High Density Polyethylene	0.148

Inner Shield

Inner Shield Material:

Layer #	Inner Shield Trade Name	Type	Inner Shield Material	Coverage (%)
1	Duobond®	Tape	Bonded Aluminum Foil-Polyester Tape-Aluminum Foil	100
2		Braid	TC - Tinned Copper	85

Inner Jacket

Inner Jacket Material:

Inner Jacket Material	Nom. Dia. (in.)
PVC - Polyvinyl Chloride	0.235

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Outer Jacket Ripcord: Yes

Overall Cable

Overall Nominal Diameter: 0.777 in.

Mechanical Characteristics (Overall)

Operating Temperature Range:	-40°C To +75°C
Bulk Cable Weight:	180 lbs/1000 ft.
Max. Recommended Pulling Tension:	362 lbs.
Min. Bend Radius (Each Coax):	2.400 in.

Min. Bend Radius (Overall):	7.750 in.
-----------------------------	-----------

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMR
CEC/C(UL) Specification:	CMG
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	10/17/2007
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Other Specification:	Telcordia Specification GF-139-CORE; SBC ENTERPRISE - SBC-002-316-019, ISSUE 4

Flame Test

UL Flame Test:	UL1666 Vertical Shaft
C(UL) Flame Test:	FT4

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)

75

Nom. Inductance:

Inductance (μH/ft)

0.097

Nom. Capacitance Conductor to Shield:

Capacitance (pF/ft)

16.800

Nominal Velocity of Propagation:

VP (%)

80.000

Nominal Delay:

Delay (ns/ft)

1.270

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

10.000

Nom. Inner Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

2.400

Max. Attenuation:

Freq. (MHz) Attenuation (dB/100 ft.)

1.000	0.280
5.000	0.590
10.000	0.800
22.500	1.180
50.000	1.820
100.000	2.600
150.000	3.220

Max. Operating Voltage - UL:

Voltage
300 V RMS

Other Electrical Characteristic 1: Impedance tested in accordance with ASTM D-4566 paragraph 48.2, option 2 using a 75 ohm fixed bridge and termination.

Other Electrical Characteristic 2: RL tested in accordance with ASTM D-4566 paragraph 50.3, using a 75 ohm fixed bridge and termination.

Other Electrical Characteristic 3: 100% sweep tested.

Minimum Return Loss:

Start Freq. (MHz)	Stop Freq. (MHz)	Min. RL (dB)
5.000	150.000	32.000

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
734C6 0081000	1,000 FT	275.000 LB	GRAY	C	6#20LDPE/GIFHDLDPESHFRPVCFRPVC
734C6 0082000	2,000 FT	576.000 LB	GRAY	C	6#20LDPE/GIFHDLDPESHFRPVCFRPVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 0 Revision Date: 04-15-2008

© 2012 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.