

7712A Coax - RG-6/U Type

For more Information
please call

1-800-Belden1

**Description:**

RG-6/U type, 18 AWG solid .040" bare copper conductors, gas-injected foam HDPE insulation, Duofoil® + tinned copper braid shield (95% coverage), overall PVC jacket.

Usage (Overall)

Suitable Applications: Video Mult.

Physical Characteristics (Overall)**Conductor****AWG:**

# Coax	AWG	Stranding	Conductor Material	Dia. (in.)
5	18	Solid	BC - Bare Copper	.040

Insulation**Insulation Material:**

Insulation Material	Dia. (in.)
Gas-injected FHDPE - Foam High Density Polyethylene	.180

Inner Shield**Inner Shield Material:**

Layer #	Inner Shield Trade Name	Type	Inner Shield Material	Coverage (%)
1	Duofoil®	Tape	Aluminum Foil-Polyester Tape-Aluminum Foil	100
2		Braid	TC - Tinned Copper	95

Inner Jacket**Inner Jacket Material:**

Inner Jacket Material	Nom. Dia. (in.)
PVC - Polyvinyl Chloride	.275

Inner Jacket Color Code Chart:

Number	Color
1	Red
2	Green
3	Blue
4	White
5	Yellow

Outer Jacket**Outer Jacket Material:**

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cable

Overall Nominal Diameter: 0.970 in.

Mechanical Characteristics (Overall)

Operating Temperature Range: -40°C To +75°C

UL Temperature Rating: 60°C

Non-UL Temperature Rating: 75°C

Bulk Cable Weight:	384 lbs/1000 ft.
--------------------	------------------

Max. Recommended Pulling Tension:	345 lbs.
-----------------------------------	----------

Min. Bend Radius (Install)/Minor Axis:	10 in.
--	--------

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMR
-------------------------	-----

CEC/C(UL) Specification:	CMG
--------------------------	-----

AWM Specification:	UL Style 1354 (each coax); UL Style 2688 (overall)
--------------------	--

EU CE Mark:	No
-------------	----

EU Directive 2000/53/EC (ELV):	Yes
--------------------------------	-----

EU Directive 2002/95/EC (RoHS):	Yes
---------------------------------	-----

EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
---------------------------------------	------------

EU Directive 2002/96/EC (WEEE):	Yes
---------------------------------	-----

EU Directive 2003/11/EC (BFR):	Yes
--------------------------------	-----

CA Prop 65 (CJ for Wire & Cable):	Yes
-----------------------------------	-----

MII Order #39 (China RoHS):	Yes
-----------------------------	-----

RG Type:	6/U
----------	-----

Flame Test

UL Flame Test:	UL1666 Vertical Shaft
----------------	-----------------------

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Suitability - Outdoor:	Yes
------------------------	-----

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)

75

Nom. Capacitance Conductor to Shield:

Capacitance (pF/ft)

16.2

Nominal Velocity of Propagation:

VP (%)

82

Nominal Delay:

Delay (ns/ft)

1.24

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

6.4

Nom. Inner Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

3.0

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100 ft.)
-------------	--------------------------

1.000	0.240
-------	-------

3.580	0.440
-------	-------

5.000	0.520
7.000	0.610
10.000	0.710
67.500	1.650
71.500	1.690
88.500	1.860
100.000	1.950
135.000	2.240
143.000	2.300
180.000	2.570
270.000	3.170
360.000	3.690
540.000	4.600
720.000	5.380
750.000	5.500
1000.000	6.420
1500.000	7.990
2000.000	9.370
2250.000	10.010
3000.000	11.780

Max. Operating Voltage - UL:

Voltage
300 V RMS

Other Electrical Characteristic 1:

Impedance tested in accordance with ASTM D-4566 paragraph 43.2, option 2 using a 75 Ohm fixed bridge and termination.

Other Electrical Characteristic 2:

Return Loss tested in accordance with ASTM D-4566 paragraph 45.3, using a 75 Ohm fixed bridge and termination.

Minimum Structural Return Loss:

Start Freq. (MHz)	Stop Freq. (MHz)	Min. SRL (dB)
5	440	23
440	520	15
520	850	23
851	3000	15

Sweep Test**Sweep Testing:**

Sweep tested 5 MHz to 3 GHz.

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
7712A B591000	1,000 FT	454.000 LB	BLACK, MATTE	C	5 #18 PE SH PVC FRTPE
7712A B59500	500 FT	216.500 LB	BLACK, MATTE	C	5 #18 PE SH PVC FRTPE

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 6 Revision Date: 09-30-2009

© 2012 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

7712A Coax - RG-6/U Type

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.