

7731SB Coax - Low Loss Serial Digital Coax



For more Information
please call

1-800-Belden1



Description:

14 AWG solid .064" bare copper conductor, gas-injected foam HDPE insulation, Duofoil® + tinned copper braid shield (95% coverage), LSZH jacket.

Usage (Overall)

Suitable Applications:

HDTV, SDI, Shipboard, AES3, ABS Type Approved, CMG-LS, IEEE 45 clause 23, IEC 60092-376 clause 17, 60092-351, 60754-1, 60754-2, 61034, UL1685 FT4 Loading, Limited Smoke, IEC 60332-3-22 (Category A), 60332-1, IEEE 1202

Physical Characteristics (Overall)

Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (in.)
1	14	Solid	BC - Bare Copper	.064

Insulation

Insulation Material:

Insulation Material	Dia. (in.)
Gas-injected FHDPE - Foam High Density Polyethylene	.280

Outer Shield

Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Duofoil®	Tape	Aluminum Foil-Polyester Tape-Aluminum Foil	100
2		Braid	TC - Tinned Copper	95

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
LSZH - Low Smoke Zero Halogen

Overall Cable

Overall Nominal Diameter: 0.400 in.

Mechanical Characteristics (Overall)

Operating Temperature Range: -30°C To +75°C

UL Temperature Rating: 75°C

Bulk Cable Weight: 93 lbs/1000 ft.

Max. Recommended Pulling Tension: 145 lbs.

Min. Bend Radius (Install)/Minor Axis: 4 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: CMG-LS

CEC/C(UL) Specification: CMG-LS

IEEE Specification: Std. 45 clause 23

7731SB Coax - Low Loss Serial Digital Coax

EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	08/04/2006
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Other Specification:	UL444, ABS Type Approval Certificate 06-HS184641A
RG Type:	11/U

Flame Test

UL Flame Test:	UL1685 FT4 Loading, Limited Smoke
C(UL) Flame Test:	FT4, Limited Smoke
IEC Flame Test:	60332-1, 60332-3-22 (Category A)
IEEE Flame Test:	1202

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Aerial:	Yes - Black only, when supported by messenger wire.

Electrical Characteristics (Overall)**Nom. Characteristic Impedance:**

Impedance (Ohm)
75

Nom. Inductance:

Inductance (μH/ft)
0.097

Nom. Capacitance Conductor to Shield:

Capacitance (pF/ft)
16.0

Nominal Velocity of Propagation:

VP (%)
85

Nominal Delay:

Delay (ns/ft)
1.21

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
2.5

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
1.5

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100 ft.)
1	0.16
3.58	0.29
5	0.34
7	0.39
10	0.46

7731SB Coax - Low Loss Serial Digital Coax

67.5	1.05
71.5	1.09
88.5	1.21
100	1.28
135	1.47
143	1.51
180	1.69
270	2.09
360	2.45
540	3.06
720	3.58
750	3.66
1000	4.30
1500	5.50
2000	6.40
2250	6.90
3000	8.20
4500	10.40

Max. Operating Voltage - UL:

Voltage
300 V RMS

Other Electrical Characteristic 1:

Impedance tested in accordance with ASTM D-4566 paragraph 43.2, option 2 using a 75 Ohm fixed bridge and termination.

Other Electrical Characteristic 2:

Return Loss tested in accordance with ASTM D-4566 paragraph 45.3, using a 75 Ohm fixed bridge and termination.

Minimum Return Loss:

Start Freq. (MHz)	Stop Freq. (MHz)	Min. RL (dB)
5	850	23
850	3000	21

Sweep Test**Sweep Testing:**

100% Sweep tested 5 MHz to 3 GHz.

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
7731SB 0101000	1,000 FT	98.000 LB	BLACK	C	#14 PE/GIFHDLDP SH FRNHPO

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 7 Revision Date: 02-20-2009

© 2012 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

7731SB Coax - Low Loss Serial Digital Coax

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.